



# **SNYPER-LTE+ Spectrum (EU)**

4G/LTE,3G/UMTS & 2G/GSM Network Signal Analyser with liveSCAN



### **General Description**


The SNYPER-LTE+ Spectrum (EU) is a high performance, multi-language network signal analyser dedicated to surveying the 4G/LTE(EU), 3G/UMTS & 2G/ GSM European networks.\*

The SNYPER-LTE+ Spectrum (EU) can save multiple surveys locally in memory and incorporates Siretta's leading liveSCAN feature which allows you to perform real time graphical site surveys on the full colour SNYPER display.\*

The SNYPER-LTE+ Spectrum is supplied with an omni-directional antenna to detect "hotspots" in buildings and perform site surveys and also includes a directional antenna kit to perform point-to-point antenna alignment.


The SNYPER can survey the local network and display results from all discovered cellular cell towers observed in the area. Results are ordered from highest to lowest "visible" base-station signal and the key network parameters of each are displayed

\*SNYPER-LTE+ Spectrum (EU) does not require a SIM in order to function.



### **Featured Applications**

- » Enhanced cellular surveying of new and existing installations on 4G, 3G and 2G networks
- » Establish most suitable operator for application
- » Evaluate your "preferred" MNO's performance
- » Use liveSCAN to determine antenna alignment to a selected base-station
- » Results are reported in CSV & graphical HTML format



Siretta Ltd Basingstoke Road Spencers Wood Reading Berkshire RG7 1PW sales

email

web

fax

+44(0)118 976 9000 +44(0)118 976 9020 sales@siretta.com www.siretta.com





# **SNYPER-LTE+ Spectrum (EU)**

4G/LTE,3G/UMTS & 2G/GSM Network Signal Analyser with liveSCAN

# **General Features**

- » 2 Supported Bands GSM | GPRS: 900/1800MHz
- » 2 Supported Bands UMTS/HSPA+: 900/2100MHz
- » 5 Supported Bands LTE: 800/900/1800/2100/2600MHz
- » Blue antenna for 700MHz to 2300 MHz
- » Silver/Grey Antenna for 2600MHz
- » liveSCAN feature for scanning selected base-stations
- » Large easy to read LCD display
- » No SIM required for operation
- » Saves multiple cellular surveys
- » Logical menus and operation
- » Long life rechargeable battery
- » 0.5m USB cable for download/charging
- » USB car charger included
- » Rugged and durable construction
- » Supplied in a hard carry case
- » Multiple language support (English/French/German/Italian/Spanish)

# Interfaces

- » 1 x USB 2.0 FS(12 MBits/s) for PC interface and for battery charging
- » 1 x SMA female cellular antenna connector
- » Red LED charging indicator
- » Display: 2.4" Diagonal QVGA 240 x 320 RGB TFT with LED backlight
- » Display: 80 degree viewing angle
- » Display Brightness: 500md/m2

### **Power Supply**

- » Mains Input: 100-240V 50/60Hz
- » Multi-region Heads: UK / EU /US / AU
- » Charger O/P: 5V DC 2000mA

# **Approvals and Compliance**

» CE

# Environmental

- Dimensions
  SNYPER: 141mm x 76mm x 36mm
  Antenna: 78mm x 11mm
- Weight
  Without antenna: 200 grams
  With supplied antenna: 207 grams
- » Operating Temperature Range: -10 to +50 deg C
- » Storage Temperature Range: -20 to +50 deg C
- » Operating Humidity Range: 20 to 85% RH Noncondensing
- » Battery: Lithium Ion 3.7V, 2000mAh
- » Life: 48 hours based on 20 surveys /day at room temperature with auto power off enabled
- » Warm up time: 2s

# Reporting

#### HTML Reporting

- » Graphical display ordered by signal strength
- » Listing of advanced cellular parameters
- » Complete summary breakdown for all recorded cells
- » Recorded survey date and time
- Integrated mapping portal enabled (registration required)

#### CSV Reporting

- » Complete survey breakdown for each recorded cell
- » Listing of advanced cellular parameters

Siretta Ltd Basingstoke Road Spencers Wood Reading Berkshire RG7 1PW +44(0)118 976 9000 +44(0)118 976 9020 sales@siretta.com www.siretta.com

sales

email

web

fax