

DESIGN KIT

WE-PDF SMD Shielded Power Inductor

**SIZE:**

1045 / 1064

TECHNICAL DATA:

L:	0.22 ~ 30.00 μ H
R _{DC} :	6.2 ~ 43.5 m Ω
I _R :	3.7 ~ 10.3 A
I _{sat} :	3.1 ~ 30 A

Order Code 744 779**Version 1.0**

WE-PDF

SMD Shielded Power Inductor



1045

744 779 702 2

L:	0.22 μ H
R _{DC} :	9.5 m Ω
I _R :	8.8 A
I _{sat} :	22 A

744 779 736 0

L:	3.6 μ H
R _{DC} :	17 m Ω
I _R :	6.8 A
I _{sat} :	9.7 A

744 779 705 0

L:	0.5 μ H
R _{DC} :	11 m Ω
I _R :	8.5 A
I _{sat} :	21 A

744 779 747 0

L:	4.7 μ H
R _{DC} :	23 m Ω
I _R :	5.8 A
I _{sat} :	8 A

744 779 711 0

L:	1.1 μ H
R _{DC} :	12.5 m Ω
I _R :	7.6 A
I _{sat} :	16 A

744 779 762 0

L:	6.2 μ H
R _{DC} :	25 m Ω
I _R :	5.5 A
I _{sat} :	7.5 A

744 779 718 0

L:	1.8 μ H
R _{DC} :	13 m Ω
I _R :	7.3 A
I _{sat} :	13.3 A

744 779 782 0

L:	8.2 μ H
R _{DC} :	30 m Ω
I _R :	4.8 A
I _{sat} :	5.8 A

744 779 725 0

L:	2.5 μ H
R _{DC} :	10.2 m Ω
I _R :	8.4 A
I _{sat} :	10.5 A

1064

744 779 802 2

L:	0.22 μ H
R _{DC} :	6.2 m Ω
I _R :	10.3 A
I _{sat} :	30 A

744 779 836 0

L:	3.6 μ H
R _{DC} :	9.8 m Ω
I _R :	7.9 A
I _{sat} :	8.6 A

744 779 811 1

L:	11 μ H
R _{DC} :	18.9 m Ω
I _R :	5.8 A
I _{sat} :	5.1 A

744 779 824 1

L:	24 μ H
R _{DC} :	38 m Ω
I _R :	4 A
I _{sat} :	3.55 A

744 779 805 0

L:	0.5 μ H
R _{DC} :	6.6 m Ω
I _R :	9.5 A
I _{sat} :	23 A

744 779 847 0

L:	4.7 μ H
R _{DC} :	11.7 m Ω
I _R :	7.5 A
I _{sat} :	7.6 A

744 779 813 1

L:	13 μ H
R _{DC} :	24 m Ω
I _R :	5.2 A
I _{sat} :	4.5 A

744 779 827 1

L:	27 μ H
R _{DC} :	40.5 m Ω
I _R :	3.9 A
I _{sat} :	3.4 A

744 779 811 0

L:	1.1 μ H
R _{DC} :	7.6 m Ω
I _R :	9.25 A
I _{sat} :	16 A

744 779 862 0

L:	6.2 μ H
R _{DC} :	13 m Ω
I _R :	7 A
I _{sat} :	6.7 A

744 779 815 1

L:	15 μ H
R _{DC} :	25.6 m Ω
I _R :	4.9 A
I _{sat} :	4.25 A

744 779 818 0

L:	1.8 μ H
R _{DC} :	8.5 m Ω
I _R :	9 A
I _{sat} :	12.8 A

744 779 872 0

L:	7.2 μ H
R _{DC} :	15.9 m Ω
I _R :	6.5 A
I _{sat} :	6 A

744 779 818 1

L:	18 μ H
R _{DC} :	27.5 m Ω
I _R :	4.7 A
I _{sat} :	4 A

744 779 825 0

L:	2.5 μ H
R _{DC} :	9.1 m Ω
I _R :	8.6 A
I _{sat} :	10.1 A

744 779 891 0

L:	9.1 μ H
R _{DC} :	17.2 m Ω
I _R :	6.2 A
I _{sat} :	5.6 A

744 779 822 1

L:	22 μ H
R _{DC} :	35.6 m Ω
I _R :	4.1 A
I _{sat} :	3.75 A

EMC COMPONENTS | INDUCTORS | TRANSFORMERS | RF COMPONENTS | CIRCUIT PROTECTION | EMC SHIELDING MATERIAL | CONNECTORS | SWITCHES | ASSEMBLY TECHNIQUE | POWER ELEMENTS

Important information: Würth Elektronik's design kits contain reference components. These components correspond with the current product development status on the day of supply. Exchange of the reference components to components with up-to-date product development status is not carried out automatically. No liability is taken for the use of these reference components. Therefore, please request new samples prior to releases for series production and product release.

Please check datasheets on www.we-online.com for specifications. Würth Elektronik eiSos GmbH & Co. KG, EMC & Inductive Solutions. © 2012

www.we-online.com

All products
in stock!