

Description

Thermal Grease 21-440 is grease-like thermal interface material, designed to perform low thermal resistance between high watt density chips like CPUs, GPUs, ASICS, Northbridge chipsets and heat sink. It provides outstanding reliability while remaining stable through all industry standard reliability testing.



Benefits

- Moderate Viscosity
- Non-Curing Material (No Need For Curing Oven)
- High Thermal Conductivity
- RoHS Compliant

Applications

CPUs (Notebooks, PCs, Servers)

- LED Solid State Lighting
- GPUs
- Northbridge Chipsets
- ASICS Chips

Thermal Grease 21-440


Version TDS.21-440.V.B.2

Technical Data Sheet

Typical Properties

| Properties | | 21-440 | Test Method |
|------------|---------------------------------------|----------|--|
| Thermal | Thermal Conductivity (W/m-K) | 3.8 | ASTM D5470 |
| | Thermal Resistance @40 psi (in^2°C/W) | 0.022 | ASTM D5470 |
| | Thermal Resistance @20 psi (in^2°C/W) | 0.024 | ASTM D5470 |
| | Continuous Use Temp. (°C) | -40~150 | JONES |
| Physical | Substrate | Silicone | - |
| | Color | Grey | Visual |
| | Viscosity (cP) | <200,000 | Brookfield Viscometer Tespindle @ 20rpm |
| | Specific Gravity (g/cc) | 2.4 | ASTM D792 |
| Electrical | Volume Resistivity (Ohm-cm) | >10^9 | ASTM D257 |
| Regulatory | Flammability Rating | V0 | UL 94 |
| | Self Life @25°C (Months) | 6 | JONES |
| | RoHS Compliant | YES | - |

Thermal Resistance vs Compression



21-440-001-001M =thermal grease 21-440-000CC can (1)

21-440-001-001G = thermal grease 21-440 1Gallon can (8kg)

Storage Requirement

Room Temperature Between 8 to 28 degree, R.H. 50% * Unopened Original Package

Declaimers

• The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the issuing date of this TDS. When using our products, no matter what type of equipment they might be used for, be sure to make a written agreement on the specifications with us in advance. The design and specifications in this TDS are subject to change without prior notice.

• Do not use the products beyond the specifications described in this TDS. This TDS explains the typical performance of the products as individual component. Before use, check and evaluate their operations when installed in your products.

• Install the following systems for a failsafe design to ensure safety if these products are to be used in equipment where a defect in these products may cause the loss of human life or other significant damage, such as damage to vehicles (automobile, train, vessel), traffic lights, medical equipment, aerospace equipment, electric heating appliances combustion/gas equipment, rotating equipment, and disaster/crime prevention equipment.

JONES TECH PLC 3 Dong Huan Zhong Road, BDA,Beijing 100176 China TEL: +86 10 6786 2636 FAX: +86 10 67860291 E-mail: sales@jones-corp.com

