Part Numbering

(Part Number)		DE B	B3 3D 102 K N2 A S S S S S S S		
1 Produce	t ID 🛛 S	eries Category			
Product ID Code		Outline	Contents		
	А	High Voltage	Class 1 (Char. SL) DC2k-3.15kV Rated		
DE	в		Class 2 DC2k-3.15kV Rated		
	с		Class 1, 2 DC6.3kV Rated		
	F		LCD Backlight Inverter Circuit 6.3kVp-p		
	н		High Temperature Guaranteed, Low-dissipation Factor (Char. R) DC2k-3.15kV Rated		

Lead Type Disc Ceramic Capacitors (2kV-6.3kV)

The first three digits (**1** Product ID and **2** Series Category) express "Series Name."

Temperature Characteristics

Code	Temperature Characteristics	Cap. Change or Temp. Coeff.	Temperature Range	
В3	В	±10%		
E3	E	+20%, -55%	–25 to +85°C	
F3	F	+30%, -80%		
R3	R	±15%	–25 to +85°C	
K5		+15%, –30%	+85 to +125°C	
D3	D	+20%, -30%	–25 to +125°C	
1X	SL	+350 to –1000ppm/°C	+20 to +85°C	
2C	СН	0±60ppm/°C	+20 to +85°C	

4 Rated Voltage

Code	Rated Voltage
ЗD	DC2kV
ЗF	DC3.15kV
ЗJ	DC6.3kV
LH	6.3kVp-p

GCapacitance

Expressed by three figures. The unit is pico-farad (pF). The first and second figures are significant digits, and the third figure expresses the number of zeros that follow the two numbers.

GCapacitance Tolerance

Code	Capacitance Tolerance
С	±0.25pF
D	±0.5pF
L	±5%
к	±10%
z	+80%, -20%

CLead Style

		Dimensions (mm)		
Code	Lead Style	Lead Spacing	Lead Diameter	Pitch of Components
A2	Vertical Crimer	5	ø0.6±0.05	_
A3	Vertical Crimp Long	7.5		
A4		10		
B2		5	ø0.6±0.05	-
B3/J3	Vertical Crimp Short	7.5		
В4	enere	10		
C1	Straight Long	5	ø0.5±0.05	
СЗ		7.5	ø0.6±0.05	-
C4	Straight Long	10		
CD		7.5	ø0.5±0.05	
D1		5	ø0.5±0.05	
D3	Straight Short	7.5	ø0.6±0.05	_
DD		7.5	ø0.5±0.05	
N2		5	ø0.6±0.05	12.7
N3	Vertical Crimp Taping	7.5		15
N7	, abing	7.5		30
P2	Straight Taping	5	ø0.6±0.05	12.7
P3	Straight Taping	7.5		15

8Packaging

Code	Packaging
А	Ammo Pack Taping
В	Bulk

Individual Specification Code

For part number that cannot be identified without "Individual Specification," it is added at the end of part number, expressed by three-digit alphanumerics.

muRata