

3.49 REF. -P Ø.375 .374 Ø.87 REF. 1.000±.015 1.020±.030 - .38 REF.

RATED VOLTAGE: 12 V DC ROTATION: CW (+ TO +) NO LOAD SPEED: 2.0 RPM NO LOAD CURRENT: 0.07 A LOADED SPEED @ 50 IN-LB: 1.6 RPM LOADED CURRENT @ 50 IN-LB: 0.20 A

MOTOR IS NOT DESIGNED FOR STALL

I/WE CERTIFY THAT SAMPLES OF THIS MOTOR HAVE BEEN FULLY TESTED BY THE UNDERSIGNED AND THAT ALL SPECIFICATIONS HAVE BEEN REVIEWED FOR PRODUCTION. MULTIPRODUCTS COMPANY, INC. IS NOT RESPONSIBLE FOR MOTORS THAT FAIL IN THE FIELD DUE TO INSUFFICIENT TESTING OF THE SAMPLE MOTORS.

I/WE AGREE TO PROVIDE MULTIPRODUCTS COMPANY, INC. WITH CURRENT DRAWINGS AND IN-HOUSE TEST PROCEDURES AS THEY BECOME AVAILABLE.

ANY CHANGES THAT I/WE MAY MAKE WHICH OCCUR AFTER THE DATE SHOWN ARE SUBJECT TO REVIEW AND MAY AFFECT UNIT PRICE AND/OR DELIVERY DATES.

SIGNATURE PRINT NAME DATE
IN ORDER TO BEGIN PRODUCTION, MULTIPRODUCTS
COMPANY, INC. MUST HAVE SIGNED APPROVAL.

В	Ø.375/.374 WAS Ø.3750/.3745	2/23/2016	3199
Α	REDRAWN WITH NEW CASTINGS	6/8/2015	
REV.	DESCRIPTION	DATE	ECO#

## TOLERANCES X.XX: ±.010 X.XXX: ±.005 PART NAME/DESCRIPTION: A A I

FRACTION: ±1/64

ANGLE: ±2°

UNLESS OTHERWISE SPECIFIED

## MULTI PRODUCTS Company, Inc.

PART NAME/DESCRIPTION: MULTIPRODUCTS CO. INC.

 DRAWN BY: DAB
 DATE: 1/28/2014
 SCALE: 0.75:1

 CHK'D BY: DMR
 DATE: 1/28/2014
 PART NUMBER:

 APPR'D BY: RP
 DATE: 1/28/2014

SCALE: 0.75:1 | MATERIAL: VARIOUS

MOD-9902-DC