


Vishay High Power Products

Hyperfast Rectifier, 15 A FRED Pt[™]



PRODUCT SUMMARY					
t _{rr} 40 ns					
I _{F(AV)}	15 A				
V _R	300 V				

FEATURES

- Hyperfast recovery time
- · Low forward voltage drop
- · Low leakage current
- 175 °C operating junction temperature
- Designed and qualified for industrial level

DESCRIPTION/APPLICATIONS

300 V series are the state of the art hyperfast recovery rectifiers designed with optimized performance of forward voltage drop and hyperfast recovery time.

The planar structure and the platinum doped life time control guarantee the best overall performance, ruggedness and reliability characteristics.

These devices are intended for use in the output rectification stage of SMPS, UPS, dc-to-dc converters as well as freewheeling diodes in low voltage inverters and chopper motor drives.

Their extremely optimized stored charge and low recovery current minimize the switching losses and reduce over dissipation in the switching element and snubbers.

ABSOLUTE MAXIMUM RATINGS					
PARAMETER	SYMBOL	TEST CONDITIONS	MAX.	UNITS	
Repetitive peak reverse voltage	V _{RRM}		300	V	
Average rectified forward current	I _{F(AV)}	T _C = 142 °C	15	٨	
Non-repetitive peak surge current	I _{FSM}	T _J = 25 °C	140	A	
Operating junction and storage temperatures	T _J , T _{Stg}		- 65 to 175	°C	

ELECTRICAL SPECIFICATIONS (T _J = 25 °C unless otherwise specified)						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Breakdown voltage, blocking voltage	V _{BR} , V _R	I _R = 100 μA	300	-	-	
Forward valtage	VF	I _F = 15 A	-	1.05	1.25	V
Forward voltage	۷F	I _F = 15 A, T _J = 125 °C	-	0.85	1.00	
		$V_{R} = V_{R}$ rated	-	0.05	40	
Reverse leakage current	I _R	$T_J = 125 \ ^{\circ}C, \ V_R = V_R \ rated$	-	12	400	μΑ
Junction capacitance	CT	V _R = 300 V	-	45	-	pF
Series inductance	L _S	Measured lead to lead 5 mm from package body	-	8	-	nH

15ETH03S/15ETH03-1

Vishay High Power Products

Hyperfast Rectifier, 15 A FRED Pt[™]



DYNAMIC RECOVERY CHARACTERISTICS ($T_J = 25 \text{ °C}$ unless otherwise specified)							
PARAMETER	SYMBOL	TEST CONDITIONS		MIN.	TYP.	MAX.	UNITS
		$I_F = 1.0 \text{ A}, dI_F/dt = 50 \text{ A}/\mu \text{s}, V_R = 30 \text{ V}$		-	-	40	
Reverse recovery time	t _{rr}	T _J = 25 °C		-	32	-	ns
		T _J = 125 °C		-	45	-	
Peak recovery current		T _J = 25 °C	I _F = 15 A dI _F /dt = - 200 A/μs	-	2.4	-	Α
Feak recovery current	nt I _{RRM}	T _J = 125 °C	$V_{\rm R} = 200 \text{ V}$	-	6.1	-	
Reverse recovery charge Q _{rr}	0	T _J = 25 °C		-	38	-	nC
	T _J = 125 °C		-	137	-	nc	

THERMAL - MECHANICAL SPECIFICATIONS						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Maximum junction and storage temperature range	T _J , T _{Stg}		- 65	-	175	°C
Thermal resistance, junction to case per leg	R _{thJC}		-	1.02	2.0	
Thermal resistance, junction to ambient per leg	R _{thJA}	Typical socket mount	-	-	70	°C/W
Thermal resistance, case to heatsink	R _{thCS}	Mounting surface, flat, smooth and greased	-	0.2	-	
Weight			-	2.0	-	g
Weight			-	0.07	-	oz.
Mounting torque			6.0 (5.0)	-	12 (10)	kgf ⋅ cm (lbf ⋅ in)
Marking davias		Case style D ² PAK		15ETH03S		•
Marking device		Case style TO-262		15ETH03-1		





Fig. 4 - Maximum Thermal Impedance Z_{thJC} Characteristics


15ETH03S/15ETH03-1


Vishay High Power Products

Hyperfast Rectifier, 15 A FRED Pt[™]









Note

 $\begin{array}{l} \mbox{(1)} \mbox{ Formula used: } T_C = T_J - (Pd + Pd_{REV}) \ x \ R_{thJC}; \\ \mbox{Pd} = \mbox{Forward power loss} = I_{F(AV)} \ x \ V_{FM} \ at \ (I_{F(AV)}/D) \ (see \ fig. \ 6); \\ \mbox{Pd}_{REV} = \ Inverse \ power \ loss = V_{R1} \ x \ I_R \ (1 - D); \ I_R \ at \ V_{R1} = \ Rated \ V_R \end{array}$





Fig. 7 - Typical Reverse Recovery Time vs. dl_F/dt





Hyperfast Rectifier, 15 A FRED Pt[™]

Vishay High Power Products






Fig. 9 - Reverse Recovery Parameter Test Circuit

Π




Fig. 10 - Reverse Recovery Waveform and Definitions


15ETH03S/15ETH03-1

VISHAY

Vishay High Power Products

Hyperfast Rectifier, 15 A FRED Pt[™]

ORDERING INFORMATION TABLE



LINKS TO RELATED DOCUMENTS				
Dimensions http://www.vishay.com/doc?95014				
Part marking information http://www.vishay.com/doc?95008				
Packaging information	http://www.vishay.com/doc?95032			



Vishay

Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.