


# SMD CRYSTAL UNITS



## • E3SB Series 3.2\*2.5 Seam Sealing Crystal



#### **FEATURES**


- Compact and thin (3.2X2.5X0.75mm max.)
- Excellent electrical performance, ideal for OA (office automation),
  AV (audiovisual), Bluetooth and Wireless LAN applications
- Excellent heat resistance and shock resistance.
- Lead-free. Meets the requirements for re-flow profiling using lead -free solder


### **Electrical Specifications**


Item	Туре	E3SB				
Frequency Range	F0	10 to 11.999MHz	12 to 19.999MHz	20 to 23.999MHz	24 to 62.500MHz	60 to 114.285MHz
Mode of Vibration		Fundamental				3RD
Load Capacitance	CL	6 to 20pF				
Frequency Tolerance	△F/ F0	±10ppm,±15ppm,±30ppm(At 25°C)				
Equivalent Series Resistance	ESR	150Ω max.	100Ω max.	70 Ω max.	50 Ω max.	100 Ω max.
Temperature Stability	TC	$\pm 10$ ppm, $\pm 15$ ppm, $\pm 30$ ppm(Refer to 25°C)				
Operating Temperature Range	Topr	<b>-</b> 20~+70°C, <b>-</b> 30~+85°C Option				
Storage Temperature Range	Tstg	-55~+125℃				
Shunt Capacitance	C0	3pF max.				
Insulator Resistance	IR	500M Ω min. (At 100Vpc)				
Drive Level	DL	100μW <b>(</b> 200μW max.)				
Aging	Fa	$\pm 2$ ppm max. (At 25°C, First year)				
Packing Unit		3000pcs/reel				

<sup>\*\*</sup>Please contact us for inquiries regarding other Specifications

### **Mechanical Dimensions(mm)**







#### Recommended Solder Pattern

