

DATASHEET

LAMP 334-15/X1C2-1UWA/EU



Features

- •Popular T-1 3/4 round package
- •High luminous power
- •Typical chromaticity coordinates x=0.40, y=0.39 according to CIE1931
- •Bulk, available taped on reel.
- •ESD-withstand voltage: up to 4KV
- •The product itself will remain within RoHS compliant version
- Compliance with EU REACH
- Compliance Halogen Free .(Br <900 ppm ,Cl <900 ppm , Br+Cl < 1500 ppm)

Description

- •The series is designed for application required high luminous intensity.
- •The phosphor filled in the reflector converts the blue emission of InGaN chip to warm white.

Applications

- Message panels
- Optical Indicators
- Backlighting
- Marker Lights



Device Selection Guide

Chip Materials	Emitted Color	Resin Color
InGaN	Warm White	Water Clear

Absolute Maximum Ratings (Ta=25 $^{\circ}$ C)

Parameter	Symbol	Rating	Unit
Continuous Forward Current	I _F	30	mA
Peak Forward Current (Duty 1/10 @ 1KHZ)	I _{FP}	100	mA
Reverse Voltage	V_R	5	V
Power Dissipation	P_d	110	mW
Operating Temperature	T _{opr}	-40 ~ +85	$^{\circ}\!\mathbb{C}$
Storage Temperature	T _{stg}	-40 ~ +100	$^{\circ}$
ESD	ESD _{HBM}	4K	V
Zener Reverse Current	l _z	100	mA
Soldering Temperature	T _{sol}	2	60 °C for 5 sec.

Electro-Optical Characteristics (Ta=25°C)

Parameter	Symbol	Min.	Тур.	Max.	Unit	Condition
Forward Voltage	V _F	2.8		3.6	V	I _F =20mA
Zener Reverse Voltage	Vz	5.2			V	Iz=5mA
Reverse Current	I _R			50	μΑ	V _R =5V
Luminous Intensity	I _V	9000		18000	mcd	I _F =20mA
Viewing Angle	201/2		20		deg	I _F =20mA
Chromoticity Coordinates	Х		0.40			I _F =20mA
Chromaticity Coordinates	У		0.39			1;-2011A



Bin Range of Luminous Intensity

Bin Code	Min.	Max.	Unit	Condition
U	9000	11250		
V	11250	14250	mcd	IF =20mA
W	14250	18000		

Note:

Tolerance of Luminous Intensity: ±10%

Forward Voltage Combination

Bin Code	Min.	Max.	Unit	Condition
0	2.8	3.0		
1	3.0	3.2	V	I _F =20mA
2	3.2	3.4		
3	3.4	3.6		

Note:


Measurement Uncertainty of Forward Voltage: ±0.1V

Color Combination (at 20mA)

Group	Bins
1	D1+D2+E1+E2+F1+F2



CIE Chromaticity Diagram



Color Ranks (I_F=20mA, Ta=25°C)


Color Ranks		CIE			
D4	Х	0.357	0.361	0.398	0.389
D1	Υ	0.361	0.385	0.411	0.382
Do	X	0.354	0.357	0.389	0.382
D2	Υ	0.340	0.361	0.382	0.358
E4	X	0.389	0.398	0.439	0.425
E1	Υ	0.382	0.411	0.431	0.400
F2	X	0.382	0.389	0.425	0.412
E2	Υ	0.358	0.382	0.400	0.372
F4	X	0.425	0.439	0.497	0.477
F1	Υ	0.400	0.431	0.466	0.413
Го	X	0.412	0.425	0.477	0.458
F2	Υ	0.372	0.400	0.413	0.383


Note:


Measurement uncertainty of the color coordinates : ±0.01



Typical Electro-Optical Characteristics Curves










Package Dimension



Note: Note:


1.All dimensions are in millimeters, and tolerance is 0.25mm except being specified.

2.Lead spacing is measured where the lead emerges from the package.

3.Protruded resin under flange is 1.5mm Max. LED.



Moisture Resistant Packing Materials Label Explanation



- · CPN: Customer's Production Number
- P/N : Production Number
- QTY: Packing Quantity
- · CAT: Ranks of Luminous Intensity and Forward Voltage
- HUE: Color Rank · REF: Reference · LOT No: Lot Number

Packing Specification

■ Inner Carton Outside Carton ■ Anti-electrostatic bag Label

- Packing Quantity
- 1. Min 200 to Max 500 PCS/1 Bag, 5 Bags/1 Inner Carton
- 2. 10 Inner Cartons/1 Outside Carton



Production Designation

334-15/X1C2-	
-	Voltage Group Luminous Intensity Bins
	Color Group

Notes

Lead Forming

- During lead formation, the leads should be bent at a point at least 3mm from the base of the epoxy bulb.
- Lead forming should be done before soldering.
- Avoid stressing the LED package during leads forming. The stress to the base may damage the LED's characteristics or it may break the LEDs.
- Cut the LED leadframes at room temperature. Cutting the leadframes at high temperatures may cause failure of the LEDs.
- When mounting the LEDs onto a PCB, the PCB holes must be aligned exactly with the lead position of the LED. If the LEDs are mounted with stress at the leads, it causes deterioration of the epoxy resin and this will degrade the LEDs.

2. Storage

- The LEDs should be stored at 30°C or less and 70%RH or less after being shipped from Everlight and the storage life limits are 3 months. If the LEDs are stored for 3 months or more, they can be stored for a year in a sealed container with a nitrogen atmosphere and moisture absorbent material.
- Please avoid rapid transitions in ambient temperature, especially, in high humidity environments where condensation can occur.


Soldering

- Careful attention should be paid during soldering. When soldering, leave more then 3mm from solder joint to epoxy bulb, and soldering beyond the base of the tie bar is recommended.
- Recommended soldering conditions:

Hand Soldering		DIP Soldering		
Temp. at tip of iron	300°C Max. (30W Max.)	Preheat temp.	100°C Max. (60 sec Max.)	
Soldering time 3 sec Max.		Bath temp. & time	260 Max., 5 sec Max	
Distance	3mm Min.(From solder joint to epoxy bulb)	Distance	3mm Min. (From solder joint to epoxy bulb)	



Recommended soldering profile



- Avoiding applying any stress to the lead frame while the LEDs are at high temperature particularly when Time(sec) soldering.
- Dip and hand soldering should not be done more than one time
- After soldering the LEDs, the epoxy bulb should be protected from mechanical shock or vibration until the LEDs return to room temperature.
- A rapid-rate process is not recommended for cooling the LEDs down from the peak temperature.
- Although the recommended soldering conditions are specified in the above table, dip or handsoldering at the lowest possible temperature is desirable for the LEDs.
- Wave soldering parameter must be set and maintain according to recommended temperature and dwell time in the solder wave.


Cleaning

- When necessary, cleaning should occur only with isopropyl alcohol at room temperature for a duration of no more than one minute. Dry at room temperature before use.
- Do not clean the LEDs by the ultrasonic. When it is absolutely necessary, the influence of ultrasonic cleaning on the LEDs depends on factors such as ultrasonic power and the assembled condition. Ultrasonic cleaning shall be pre-qualified to ensure this will not cause damage to the LED

Circuit Protection

- Below the zener reference voltage Vz, all the current flows through LED and as the voltage rises to Vz, the zener diode "breakdown." If the voltage tries to rise above Vz current flows through the zener branch to keep the voltage at exactly Vz.
- When the LED is connected using serial circuit, if either piece of LED is no light up but current can't flow through causing others to light down. In new design, the LED is parallel with zener diode, if either piece of LED is no light up but current can flow through causing others to light up.





6. Heat Management

- Heat management of LEDs must be taken into consideration during the design stage of LED application. The current should be de-rated appropriately by referring to the de-rating curve found in each product specification.
- The temperature surrounding the LED in the application should be controlled. Please refer to the data sheet de-rating curve.

7. ESD (Electrostatic Discharge)

- The products are sensitive to static electricity or surge voltage. ESD can damage a die and its reliability. When handling the products, the following measures against electrostatic discharge are strongly recommended:
 - Eliminating the charge
 - Grounded wrist strap, ESD footwear, clothes, and floors
 - Grounded workstation equipment and tools
 - ESD table/shelf mat made of conductive materials
- Proper grounding is required for all devices, equipment, and machinery used in product assembly.
 Surge protection should be considered when designing of commercial products.
- If tools or equipment contain insulating materials such as glass or plastic, the following measures against electrostatic discharge are strongly recommended:
 - Dissipating static charge with conductive materials
 - Preventing charge generation with moisture
 - Neutralizing the charge with ionizers

狀態:Approved(正式發行)



DISCLAIMER

- 1. EVERLIGHT reserves the right(s) on the adjustment of product material mix for the specification.
- 2. The product meets EVERLIGHT published specification for a period of twelve (12) months from date of shipment.
- 3. The graphs shown in this datasheet are representing typical data only and do not show guaranteed values.
- 4. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from the use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- 5. These specification sheets include materials protected under copyright of EVERLIGHT. Reproduction in any form is prohibited without obtaining EVERLIGHT's prior consent.
- 6. This product is not intended to be used for military, aircraft, automotive, medical, life sustaining or life saving applications or any other application which can result in human injury or death. Please contact authorized Everlight sales agent for special application request.

