

# Harvatek Surface Mount CHIP LEDs Data Sheet B1931TW--20P000314U1930

Official Product	HT Part No. B1931TW20P000314U1930					
Tentative Product	********					
Specifications are subject notice. Proprietary data, dr	04/16/2021	Version 1.3	Page 1/15			



DISCLAIMER	3
LIFE SUPPORT POLICY	3
PRODUCT SPECIFICATIONS	4
ATTENTION: ELECTROSTATIC DISCHARGE (ESD) PROTECTION	4
LABEL SPECIFICATIONS	5
SPECIFICATIONS RANGE	6
PRODUCT FEATURES	8
ELECTRO-OPTICAL CHARACTERISTICSPACKAGE OUTLINE DIMENSION AND RECOMMENDED SOLDERING PATTERN FOR REFLOW	
Soldering	8
ABSOLUTE MAXIMUM RATINGS	8
CHARACTERISTICS OF B1931TW	9
PRECAUTION FOR USE	10
PACKAGING	11
TAPE DIMENSION	11
REEL DIMENSION	12
Packing	12
DRY PACK	13
Baking	13
Precautions	13
REFLOW SOLDERING	14
Reworking	14
CLEANING	14
CAUTIONS OF PICK AND PLACE	15
REVISE HISTORY	15

Official Product	HT Part No. B1931TW20P000314U1930				
Tentative Product	********				
Specifications are subject notice. Proprietary data, dr	04/16/2021	Version 1.3	Page 2/15		



#### **DISCLAIMER**

HARVATEK reserves the right to make changes without further notice to any products herein to improve reliability, function or design. HARVATEK does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights, nor the rights of others.

## **Life Support Policy**

HARVATEK's products are not authorized for use as critical components in life support devices or systems without the express written approval of the President of HARVATEK or HARVATEK INTERNATIONAL. As used herein:

- 1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- 2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Official Product	HT Part No. B1931TW20P000314U1930				
Tentative Product	*******				
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		04/16/2021	Version 1.3	Page 3/15	



### **Product Specifications**

Item	Specification	Material	Quantity
Luminous	285.0-715.0 mcd		
Intensity(Iv)	@20 mA/ $T_S$ = 25°C; Tolerance: ±10%		
Chromaticity	As page 6 & 7		
Coordinate	@20 mA/ $T_S = 25^{\circ}C$ ; Tolerance: ±0.007		
Vf	2.7-3.9 V		
	@20 mA/ $T_S = 25^{\circ}C$ ; Tolerance: ±0.05V		
Ir	< 10 μA @ V <sub>R</sub> = 5 V		
Resin	Yellow	Ероху	
Carrier tape	EIA 481-1A specs	Conductive black tape	
Reel	EIA 481-1A specs	Conductive black	
Label	HT standard	Paper	
Packing bag	220x240mm	Aluminum laminated bag/ no-zipper	One reel per bag
Carton	HT standard	Paper	Non-specified

#### Others:

Each immediate box consists of 5 reels. The 5 reels may not necessarily have the same lot number or the same bin combinations of Iv, CIE and Vf. Each reel has a label identifying its specification; the immediate box consists of a product label as well.

Note: This is shipped test conditions

\*Remarks: This product should be operated in forward bias. If a reverse voltage is continuously applied to the product, such operation can cause migration resulting in LED damage.

#### ATTENTION: Electrostatic Discharge (ESD) protection



The symbol to the left denotes that ESD precaution is needed. ESD protection for GaP and AlGaAs based chips is necessary even though they are relatively safe in the presence of low static-electric discharge. Parts built with AlInGaP, GaN, or/and InGaN based chips are **STATIC SENSITIVE devices**. ESD precaution must


be taken during design and assembly.

If manual work or processing is needed, please ensure the device is adequately protected from ESD during the process.


Official Product	HT Part No. B1931TW20P000314U1930				
Tentative Product	********				
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		04/16/2021	Version 1.3	Page 4/15	



# **Label Specifications**



#### Harvatek P/N:



## Lot No.:

1	2	3	4	5	6	7	8	9	10
E	1	A	1	Α	2	2	L	1	2
Cod	le 1 2	Code 3	Code 4	Code 5	Code 6	Code 7	Code 8	Code 9	Code 10
		Mfg. Year	Mfg. Month	Mfg. Date	Consecuti	ve number		Special cod	e
		2010-A		1:A					
		2011-B		2:B					
		2012-C	1:Jan.	3:C					
			2:Feb.	***					
Internal Te	saine Cada	2018-I/J	11444	26:Z	01	77		000 777	
internal ir	acing Code	2019-K	A:Oct.	27:7	01-	-ZZ		000~ZZZ	
			B:Nov.	28:8					
	2022-N	C:Dec.	29:9						
	2023-P	120/1000	30:3						
		444		31:4					

Official Product	HT Part No. B1931TW20P000314U1930				
Tentative Product	*******				
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		04/16/2021	Version 1.3	Page 5/15	



# **Specifications Range**

# ■Luminous Intensity (Iv) Bin:

Color	Bin Code	Spec. Range
	Т	285.0-360.0 mcd
	U	360.0-450.0 mcd
TW	V	450.0-560.0 mcd
	w	560.0-715.0 mcd

Note: It maintains a tolerance of ±10% on Luminous Intensity

## **■**Color Bin:


Color	Bin Code	Spec.	Range	Bin Code	Spec. Range		
TW	C1	X 0.2500 0.2500 0.2700 0.2700	Y 0.2050 0.2500 0.2775 0.2325	C2	X 0.2700 0.2700 0.2900 0.2900	Y 0.2325 0.2775 0.3050 0.2600	
	D1	X 0.2900 0.2900 0.3100 0.3100	Y 0.2600 0.3050 0.3330 0.2880	D2	X 0.3100 0.3100 0.3300 0.3300	Y 0.2875 0.3325 0.3600 0.3150	

Note: It maintains a tolerance of x,y ±0.007

Official Product	HT Part No. B1931TW20P000314U1930					
Tentative Product	*********					
Specifications are subject notice. Proprietary data, dr	04/16/2021	Version 1.3	Page 6/15			



# **■**Chromaticity Coordinate



# ■Forward Voltage (Vf) Bin:

Color	Bin Code	Spec. Range	Bin Code	Spec. Range
	G4	2.7-2.8 V	H1	2.8-2.9 V
	H2	2.9-3.0 V	Н3	3.0-3.1 V
TW	H4	3.1-3.2 V	J1	3.2-3.3 V
1 44	J2	3.3-3.4 V	J3	3.4-3.5 V
	J4	3.5-3.6 V	K1	3.6-3.7 V
	K2	3.7-3.8 V	К3	3.8-3.9 V

Note: It maintains a tolerance of ±0.05V on forward voltage measurements

Official Product	HT Part No. B1931TW20P000314U1930				
Tentative Product	********	******			
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		04/16/2021	Version 1.3	Page 7/15	




#### **Product Features**

## **Electro-Optical Characteristics**

						(1)	Soldering , $25^{\circ}$ C)
Series	Emitting Color	Material	V <sub>F</sub> (V)		Chromaticity Coordinate	I <sub>V</sub> (mcd)	Viewing
			typ	max	x,y	Typical	Angle $2\theta \frac{1}{2}$
D1021TW 20	T\\\/	In CoN	3.2	3.9	v 0 2000 v 0 2050	420	X : 120
B1931TW20	TW InGaN		3.2	3.9	x=0.2900,y=0.2850	420	Y: 135

# Package Outline Dimension and Recommended Soldering Pattern for Reflow Soldering

(Unit: mm Tolerance: +/-0.1)



## **Absolute Maximum Ratings**

(T<sub>Soldering</sub> ,25°C)


Series	P <sub>D</sub> (mW)	I <sub>F</sub> (mA)	I <sub>FP</sub> (mA)*	T <sub>OP</sub> (℃)	T <sub>ST</sub> (℃)
Color	Power Dissipation	Forward Current	Pulse Forward	Operating	Storage
Color	Power Dissipation	Forward Current	Current	Temperature	Temperature
TW	68	20	80	-40~+85	-40~+100

<sup>\*</sup> Condition for I<sub>FP</sub> is pulse of 1/10 duty and 0.1msec width

Official Product	HT Part No. B1931TW20P000314U1930				
Tentative Product	********	******			
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		04/16/2021	Version 1.3	Page 8/15	



## **Characteristics of B1931TW**



Official Product	HT Part No. B1931TW20P000314U1930				
Tentative Product	********	******			
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		04/16/2021	Version 1.3	Page 9/15	




#### **Precaution for Use**

- 1. The chips should not be used directly in any type of fluid such as water, oil, organic solvent, etc.
- 2. When the LEDs are illuminating, the maximum ambient temperature should be first considered before operation.
- 3. LEDs must be stored in a clean environment. A sealed container with a nitrogen atmosphere is necessary if the storage period is over 3 months after shipping.
- 4. The LEDs must be used within 4 weeks after unpacked. Unused products must be repacked in an anti-electrostatic package, folded to close any opening and then stored in a dry and cool space.
- 5. The appearance and specifications of the products may be modified for improvement without further notice.
- 6. The LEDs are sensitive to the static electricity and surge. It is strongly recommended to use a grounded wrist band and anti-electrostatic glove when handling the LEDs.If a voltage over the absolute maximum rating is applied to LEDs, it will damage LEDs.Damaged LEDs will show some abnormal characteristics such as remarkable increase of leak current, lower turn-on voltage and getting unlit at low current.

Official Product	HT Part No. B1931TW20P000314U1930				
Tentative Product	********				
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		04/16/2021	Version 1.3	Page 10/15	




# Packaging Tape Dimension



Dim. A	Dim. B	Dim. C	Q'ty/Reel
1.80±0.05	0.94±0.05	0.60±0.05	4K


Unit: mm




Official Product	HT Part No. B1931TW20P000314U1930				
Tentative Product	********				
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		04/16/2021	Version 1.3	Page 11/15	



## **Reel Dimension**



# **Packing**



5 or 10 boxes per carton is available depending on shipment quantity.

Official Product	HT Part No. B1931TW20P000314U1930				
Tentative Product	********	******			
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		04/16/2021	Version 1.3	Page 12/15	




### **Dry Pack**

All SMD optical devices are **MOISTURE SENSITIVE**. Avoid exposure to moisture at all times during transportation or storage. Every reel is packaged in a moisture protected anti-static bag. Each bag is properly sealed prior to shipment.

A humidity indicator will be included in the moisture protected anti-static bag prior to shipment.

The packaging sequence is as follows:



## **Baking**

Baking before soldering is recommended when the package has been unsealed for 4 weeks. The conditions are as followings:

- 1.  $60\pm3^{\circ}$ C ×(12~24hrs)and<5%RH, taped reel type.
- 2.  $100\pm3^{\circ}$ C × (45min~1hr), bulk type.
- 3.  $130\pm3^{\circ}$ C ×(15min~30min), bulk type.

#### **Precautions**

- 1. Avoid exposure to moisture at all times during transportation or storage.
- 2. Anti-Static precaution must be taken when handling GaN, InGaN, and AllnGaP products.
- 3. It is suggested to connect the unit with a current limiting resistor of the proper size. Avoid applying a reverse voltage beyond the specified limit.
- 4. Avoid operation beyond the limits as specified by the absolute maximum ratings.
- 5. Avoid direct contact with the surface through which the LED emits light.
- 6. If possible, assemble the unit in a clean room or dust-free environment.

Official Product	HT Part No. B1931TW20P000314U1930				
Tentative Product	*******				
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		04/16/2021	Version 1.3	Page 13/15	




### **Reflow Soldering**

Recommend soldering paste specifications:

- 1. Operating temp.: Above 217°C ,60~150sec
- 2. Peak temp.:260°C Max.,10sec Max.
- 3. Reflow soldering should not be done more than two times.
- 4. Never take next process until the component is cooled down to room temperature after reflow.
- 5. The recommended reflow soldering profile (measuring on the surface of the LED terminal) is as following:

Lead-free Solder Profile



#### Reworking

- Rework should be completed within 5 seconds under 260°C.
- The iron tip must not come in contact with the copper foil.
- Twin-head type is preferred.

## Cleaning

Following are cleaning procedures after soldering:

- An alcohol-based solvent such as isopropyl alcohol (IPA) is recommended.
- Temperature x Time should be 50°C x 30sec. or <30°C x 3min</li>
- Ultra sonic cleaning: < 15W/ bath; bath volume ≤ 1liter</li>
- Curing: 100<sup>o</sup>C max, <3min</li>

Official Product	HT Part No. B1931TW20P000314U1930				
Tentative Product	*******				
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		04/16/2021	Version 1.3	Page 14/15	



## **Cautions of Pick and Place**

- Avoid stress on the resin at elevated temperature.
- Avoid rubbing or scraping the resin by any object.
- Electric-static may cause damage to the component. Please ensure that the equipment is properly grounded. Use of an ionizer fan is recommended.

# **Revise History**

Rev.	Descriptions	Date	Page
1.0		11/04/2014	-
1.1	Renew Form	04/28/2017	-
1.2	Renew Form	09/04/2017	-
1.3	Add Customer Product Code and Renew Form	04/16/2021	P.5

Official Product	HT Part No. B1931TW20P000314U1930			
Tentative Product	********	******		
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.		04/16/2021	Version 1.3	Page 15/15