



1100 Series FlashPacs from Excelitas are ideal sources for UV-VIS-NIR applications.

1100 Series FlashPacs from Excelitas Technologies have been designed to combine state-of-the-art circuitry and components into a packaged light source which provides microsecond-duration pulses of broadband light with exceptional arc stability. 1100 Series FlashPacs utilize the PS-1110 and PS-1120 variable output power supplies in conjunction with the appropriate Lite-Pac[®] trigger module to operate several types of flashlamps.

A fully shielded steel case and EMI suppression circuitry combine to diminish the radiated and conducted noise normally associated with high peak discharge currents.

FlashPacs can be ordered with a wide range of discharge capacitance values and several types of the 1100 Series flashlamps. These systems make ideal sources of pulsed light for ultraviolet-visible absorption spectroscopy, HPLC, blood analyzers, colorimetry, machine vision and ultraviolet applications.

Key Features

- Compact
- 10 or 20 Watts average power
- High radiant intensity
- Continuous spectrum UV-VIS-NIR
- User adjustable charge voltage
- Selection of flashlamps
- Selection of discharge capacitors
- Microsecond flash duration
- Simple fiber optic coupling

Applications

- Absorption analysis
- Immunoassay modules
- Fluorimetry
- Spectroradiometry
- Liquid and gas chromatography
- Colorimetry
- UV-VIS-NIR applications
- Machine vision



1100 Series FlashPacs

Electrical Inputs			
	LS-1102	LS-1130	
Voltage	11-28 VDC 15-28 VDC		
DC Current	1.3 Amps @ 12 VDC	1.4 Amps @ 24 VDC	
Peak Current	3.5 Amps @ 12 VDC	3.5 Amps @ 24 VDC	
Trigger	+5V, 20-50mA peak input, 10-100μs pulse width, leading edge trigger. Optically isolated internal series resistor = 150Ω.		
V _{ref} (V ₀ /V _{ref} = 100)	4.5 – 6.0 VDC	4-10 VDC	
EMI Supression	Yes ¹	Yes ²	

¹ Inductor and filter capacitor for power input. All inputs through shielded 9-PIN "D" connector.

² Common-mode inductor and filter capacitor in power input. All inputs through shielded 9-PIN "D" connector.

Electrical Outputs (Discharge)				
	LS-1102	LS-1130		
Voltage (V ₀)	450-600 ± 2% VDC	400-1000 ± 2% VDC		
Power Output	10 Watts max.	20 Watts max.		
Charge Rate, minimum	10j/sec (12V input , 600V output)	20j/sec (24V input , 600V output)		
Line Regulation	1%			
Ripple ¹	0.5%			
Internal Discharge Capacitor	0.1µF Standard. See charts following for other vaules availavble			
Recharge Delay	200µsec			


 1 Peak to peak maximum with 0.10 μF internal discharge capacitor at maximum output.


LS-1102 FlashPac Specifications				
Model Number	Discharge Capacitor	Maximum Input Energy Per Flash	Maximum Flash Rate @ 600 VDC	
LS-1102-1	0.10 μF - Standard	18 mJ	550 Hz	
LS-1102-2	0.22 μF	40 mJ	250 Hz	
LS-1102-3	0.47 μF	85 mJ	118 Hz	
LS-1102-4	1.0 μF	180 mJ	55 Hz	
LS-1102-5	2.0 μF	360 mJ	28 Hz	


LS-1130 FlashPac Specifications				
Model Number	Discharge Capacitor	Maximum Input Energy Per Flash	Maximum Flash Rate @ 1000 VDC	
LS-1130-1	0.10 μF - Standard	50 mJ	400 Hz	
LS-1130-2	0.22 μF	110 mJ	180 Hz	
LS-1130-3	0.47 μF	235 mJ	85 Hz	
LS-1130-4	1.0 μF	500 mJ	40 Hz	

Environmental				
	LS-1102 LS-1130			
Operating Temperature	+32°F to +104°F (0°C to +40°C)			
Storage Temperature	-40°F to +194°F (-40°C to +90°C)			


Mechanical Dimensions







Туре	Arc Length (mm)	Spectral Distribution (nm)	Window Material	Average Power (watts)	Life (flashes)	Stability
Flashlamps a	Flashlamps available for LS-1102 FlashPacs (Order flashlamps separately)					
FX-1101		225-1100+	Borosilicate			
FX-1102	1.5	190-1100+	UV Glass	10	>1x10 ⁹	<1%CV
FX-1103		120-1100+	MgF ₂			
FX-1104		225-1100+	Borosilicate			
FX-1105	3.0	190-1100+	UV Glass	10	>1x10 ⁹	<1%CV
FX-1106		120-1100+	MgF ₂			
Flashlamps available for LS-1130 FlashPacs (Order flashlamps separtely)						
FX-1150		225-1100+	Borosilicate			
FX-1151	1.5	190-1100+	UV Glass	20	>1x10 ⁹	<1%CV
FX-1152		120-1100+	MgF ₂			
FX-1153		225-1100+	Borosilicate			
FX-1154	3.0	190-1100+	UV Glass	20	>1x10 ⁹	<1%CV
FX-1155		120-1100+	MgF ₂			
High output	reflector flashlan	nps available for LS-113	80 FlashPacs (Order	flashlamps separtely)		
FX-1160		225-1100+	Borosilicate			
FX-1161	1.5	190-1100+	UV Glass	20	>1x10 ⁹	<1%CV
FX-1162	1	120-1100+	MgF ₂			
FX-1163		225-1100+	Borosilicate			
FX-1164	3.0	190-1100+	UV Glass	20	>1x10 ⁹	<1%CV
FX-1165	1	120-1100+	MgF ₂			



NOTE: All values are nominal; specifications subject to change without notice.

About Excelitas Technologies

Excelitas Technologies is a global technology leader focused on delivering innovative, customized solutions to meet the lighting, detection and other highperformance technology needs of OEM customers.

From medical lighting to analytical instrumentation, clinical diagnostics, industrial, safety and security, and aerospace and defense applications, Excelitas Technologies is committed to enabling our customers' success in their specialty end-markets. Excelitas Technologies has approximately 3,000 employees in North America, Europe and Asia, serving customers across the world.

Excelitas Technologies

35 Congress Street Salem, Massachusetts 01970 USA Telephone: (+1) 978.745.3200 Toll free: (+1) 800.950.3441 Fax: (+1) 978.745.0894 Excelitas Technologies LED Solutions, Inc. 160 E. Marquardt Drive Wheeling, Illinois 60090 USA Telephone: (+1) 847.537.4277 Fax: (+1) 847.537.4785 Excelitas Technologies Illumination, Inc. 44370 Christy Street Fremont, California

Telephone: (+1) 510.979.6500

Toll-free: (+1) 800.775.6786

Fax: (+1) 510.687.1140

94538-3180 USA

Excelitas Technologies Elcos GmbH Luitpoldstrasse 6 Pfaffenhofen, 85276 Germany Telephone: (+49) 8441.8917.0 Fax: (+49) 8441.7191.0 Excelitas Technologies Shenzhen Co., Ltd. Wearnes Technology Center No.10 Kefa Road, Science & Industry Park Nanshan District, Shenzhen, Guangdong P.R. of China 518057 Telephone: +86 2655 3861 Fax: +86 755 2661 7311

For a complete listing of our global offices, visit www.excelitas.com/ContactUs

© 2011 Excelitas Technologies Corp. All rights reserved. The Excelitas logo and design are registered trademarks of Excelitas Technologies Corp. All other trademarks not owned by Excelitas Technologies or its subsidiaries that are depicted herein are the property of their respective owners. Excelitas reserves the right to change this document at any time without notice and disclaims liability for editorial, pictorial or typographical errors.

