

ROHS

Micro Commercial Components 130 W Cochran St, Unit B Simi Valley, CA 93065 Tel:818-701-4933

MF200C12F2


Features

- Lead Free Finish/RoHS Compliant (NOTE 1)("P" Suffix designates RoHS Compliant. See ordering information)
- Soft Reverse Recovery Characteristics
- Ultrafast Reverse Recovery Time
- Low Reverse Recovery Loss
- Low Forward Voltage
- High Surge Current Capability
- Low Inductance Package

Applications


- Inversion Welder
- Uninterruptible Power Supply (UPS)
- Plating Power Supply
- Ultrasonic Cleaner and Welder
- Power Factor Correction (PFC) Circuit
- Converter & Chopper

200 Amp FRED Modules 1200 Volts



DIMENSIONS					
DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	NOIL
Α	0.886	0.925	22.50	23.50	
В	1.161	1.201	29.50	30.50	
С	0.335	0.374	8.50	9.50	
D	0.315	0.350	8.00	8.90	
E	1.043	1.083	26.50	27.50	
F	1.122	1.161	28.50	29.50	
G	3.130	3.169	79.50	80.50	
Н	0.492	0.531	12.50	13.50	
I	2.500	2.539	63.50	64.50	
J	3.681	3.720	93.50	94.50	
K	0.256		6.50		Ø
L	0.492	0.531	12.50	13.50	
M	1.319	1.358	33.50	34.50	







MF200C12F2

Maximum Ratings

Symbol	Conditions	Values	Units
V _R		1200	V
V_{RRM}		1200	V
I _{F(AV)}	T _C =110°C, Per Diode	200	А
I _{F(RMS)}	T _C =110°C, Per Diode	280	Α
	1/2 Cycle , 50Hz, Sine	1800	Α
I _{FSM}	1/2 Cycle , 60Hz, Sine	1950	Α
I ² t	T _J =45°C, t=10ms, 50Hz, Sine	16200	A ² s
11	T _J =45°C, t=8.3ms, 60Hz, Sine	19000	A ² s
P _D		920	W
Visol	AC, Ton=1min	3000	V
TJ		-40 to +150	°C
T _{STG}		-40 to +125	°C
Torque	Recommended (M6)	4.5	N·m
Torque	Recommended (M6)	4.5	N·m
Weight		160	g

Thermal Characteristics

Symbol	Conditions	Values	Units
Rth(i-c)	Per diode	0.22	°C/W

Electrical Characteristics

Symbol	Conditions	Values			Units
Symbol	Conditions		Тур.	Max.	Units
I _{RM}	V _R =1200V			1	mA
	V _R =1200V, T _J =125°C			5	mA
V _F	I _F =200A		2.1	2.5	V
	I _F =200A, T _J =125°C		1.9		V
trr	I_F =1A, V_R =30V, di_F/dt =-200A/ μ s		57		ns
trr	V =600V L =200A di (dt= 200A/us T =25°C		110		ns
I _{RRM}	V_R =600V, I_F =200A, di_F/dt =-200A/ μ s, T_J =25°C		9		Α
trr	V =600V I =200A di /dt= 200A/us T =125°C		500		ns
I _{RRM}	V_R =600V, I_F =200A, di_F/dt =-200A/ μ s, T_J =125°C		21		Α

MF200C12F2



Performance Curves




Fig1. Forward Voltage Drop vs Forward Current




Fig3. Reverse Recovery Current vs di_F/dt




Fig2. Reverse Recovery Time vs di_F/dt




Fig4. Reverse Recovery Charge vs di_F/dt



Ordering Information:

Device	Packing
Part Number-BP	Bulk: 8PCS/BOX;80PCS/CTN

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. **Micro Commercial Components Corp.** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp.** and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.