
# MTi-3

- Smallest form factor on the market
- Easy integration
- Development Kit available

The MTi-3 is the smallest self-contained Attitude Heading and Reference System (AHRS) on the market. The Xsens optimized strapdown algorithm (AttitudeEngine ™) performs high-speed, dead-reckoning calculations at 1 kHz, accurately capturing high-frequency motions. Xsens' industry-leading sensor fusion algorithm provides high accuracy and sensor auto-calibration in this cost-effective module for a wide range of (embedded) applications. It relieves you of the work of designing, integrating and maintaining gyroscopes, accelerometers and other sensors.

The MTi-3 is part of the MTi 1-series supported by the MT Software Suite, which includes MT Manager (GUI for Windows/Linux), SDK, example codes and drivers for many platforms.



- 3D models available on request
- Available online via Digi-Key, Mouser, Farnell and local distributors
- For full specifications: please refer to the MTi-series datasheet available at <a href="mailto:mtidocs.xsens.com">mtidocs.xsens.com</a>

# Sensor fusion performance Roll, Pitch

Roll, Pitch ————————————————————————————————————	0.5 deg RMS
Yaw/Heading	2 deg RMS
Strapdown Integration (SDI) ————	Yes

#### **Gyroscope**

Standard full range —————	2000 deg/s
In-run bias stability	10 deg/h
Bandwidth (-3dB)	230 Hz
Noise Density	0.003 °/s/√Hz
g-sensitivity (calibr.)	0.001 º/s/g

# Accelerometer Standard full range

Staridara rail railige	10 9
In-run bias stability	30 µg
Bandwidth (-3dB)	230 Hz
Noise Density	70 ug/s/F

#### Magnetometer

Standard full range	+/- 8 G
Total RMS noise	0.5 mG
Non-linearity	0.2%
Resolution	0.25 mG

### **GNSS Receiver**

GNSS receiver interface	n/a
GNSS precision	n/a
RTCM input port	n/a

## Barometer

Barometer interface	n/a

### **Mechanical**

IP-rating	IP00
Operating Temperature ————	-40 to 85 °C
Casing material	PCB
Mounting orientation	No restriction, full 360° in all axes
Dimensions —	12.1 x 12.1 x 2.55 mm
Connector	SMD, footprint compatible with JEDEC
	PLCC-28
Weight	0.6 g

# **Electrical**

Input voltage	2.19 to 3.6V
Power consumption (typ)	44 mW @ 3V

# Interfaces / IO

Interfaces	UART, SPI, I <sup>2</sup> C
Sync Options	Yes
Protocols	Xbus
Clock drift	10 ppm
Output Frequency	Up to 1 kHz, 100 Hz SDI
Built-in-self test	Gyr, Acc, Mag

#### **Software Suite**

GUI (Windows/Linux)	MT Manager Firmware updater,
	Magnetic Field Mapper
SDK (Example code)	C++, C#, python, Matlab, Nucleo,
	public source code
Drivers	LabVIEW, ROS, GO
Support —	BASE by XSENS: online manuals,
	community and knowledge base



