


# 2EHDP-XXP

PCB Terminal Blocks > PCB Connector-Socket

Date:2022-06-09Version:V1



The web catalog is for reference only. Dinkle remains the right of product modification and engineering change of the design.

The final product is made according to engineering drawing.

### **Product Description**

Pitch: 5.08 mm, 300V, 15A

#### General information

| Short description                      | PCB Connector – Socket, Iron Soldering |
|--|--|
| Category                               | PCB Connector – Socket                 |
| Pitch (mm)                             | 5.08                                   |
| Color                                  | Green (default)                        |
| Type of locking                        | With threaded flange                   |
| Soldering method                       | Iron Soldering                         |
| Length (mm)                            | 5.08*(P/2-1)+25.4                      |
| Width (mm)                             | 17.5                                   |
| Height (mm)                            | 17.2                                   |
| Pin demensions (Thickness x Width)(mm) | 0.8x2.9                                |
| Number of positions                    | 02P~24P                                |
| Level                                  | Single level                           |

#### Material information

| Insulation material       | PA |
|---------------------------|----|
| Insulation material group | I  |




| Flame retardant rating , compliant with UL94 | VO                |
|--|-------------------|
| Insulation resistance                        | □500MΩ at DC 500V |
| Conductor material                           | COPPER ALLOY      |
| Plating of conductor surface                 | Tin PLATED        |
| Connection data-IEC                          |                   |
| Rated voltage (V)                            | 630               |
| Rated current (A)                            | 18                |
| Rated voltage (II/2)(V)                      | 630               |
| Rated voltage (III/2) (V)                    | 320               |
| Rated voltage (III/3)(V)                     | 320               |
| Rated impulse voltage (II/2)(KV)             | 4                 |
| Rated impulse voltage (III/2)(KV)            | 4                 |
| Rated impulse voltage (III/3)(KV)            | 4                 |
| Connection data-UL                           |                   |
| Rated voltage (UL/CUL Group B)(V)            | 300               |
| Rated current (UL/CUL Group B)(A)            | 15                |
| Rated voltage (UL/CUL Group D)(V)            | 300               |
| Rated current (UL/CUL Group D)(A)            | 10                |
| Environment & Safety                         |                   |
| Finger protection (YES or NO)                | YES               |
| Operating temperature. max (°C)              | 120               |
| Operating temperature. min (°C)              | -40               |
| JL Recognized                                |                   |
| Rated voltage (Group B)(V)                   | 300               |
| Rated current (Group B)(A)                   | 15                |
| Rated voltage (Group D)(V)                   | 300               |
| Rated current (Group D)(A)                   | 10                |
| CUL Recognized                               |                   |
| Rated voltage (Group B)(V)                   | 300               |
|  |                   |


| Rated voltage (Group D)(V) | 300 |
|----------------------------|-----|
| Rated current (Group D)(A) | 10  |

### **VDE** Approval

| Rated voltage (V) | 630 |
|-------------------|-----|
| Rated current (A) | 18  |

## Drawings





## Approvals







