# FA-0805SB2-S SHOCK ABSORBER - FIXED

# Bansbach easylift



| Model                  |   | Stroke<br>mm                                      | Max Absorption<br>Energy<br>J(kgf⋅m) |                              | Max Equivalent<br>Mass<br>kg(kgf) |           |  |
|------------------------|---|---|--------------------------------------|------------------------------|-----------------------------------|-----------|--|
| FA-0805SB2-S           | , | 5   | 0.68(0.07)                           |                              | 5(5)                              |           |  |
| Max<br>Drag<br>N (kgf) |   | Absorption<br>Energy per min.<br>J/min(kgf∙m/min) |                                      | Extension<br>Force<br>N(kgf) |                                   | Mass<br>g |  |
| 588(60)                |   | 22.5(2.3)   |                                      | 4.9(0.5)<br>or lower         |                                   | 8.6       |  |

**SPECIFICATIONS** 

The thread pitch P1.0 is supplied as well

## **COMMON SPECIFICATIONS**

| Range of Impact Rate  | m/s       | 0.3~1 |  |
|-----------------------|-----------|-------|--|
| Maximum Cycle Rate    | cycle/min | 45    |  |
| Operating Temperature | C°        | -5~70 |  |


## **PRECAUTIONS FOR USE**


- Do not use this product without carefully reading the attached owner's manual.
- Ensure that an external stopper (Stopper nut OP-020SB) is also used.
- Do not turn the oil inlet screw located at the bottom of the main unit.
- Ensure that sufficient mounting strength is secured for this product. (As a guideline, it should be 2 to 3 times the maximum drag listed in the catalogue.)
- Do not use this product in a vacuum or a location where it may come in contact with oil.
- Ensure that an eccentric load is not applied to the soft absorber. (Allowable eccentric angle: within ±2.5°)

# **OPTIONAL PARTS**

#### Eccentric angle adaptor OP-010MB


- Screw the eccentric angle adaptor into the main unit until the cap for the eccentric angle and the piston rod form a tight connection. While maintaining this position, fasten the main unit's nut until it is secured.
- Use the eccentric angle adaptor when the eccentric angle is 2.5° or larger.
- The main unit can also be used as a stopper.
- Use it with a capless soft absorber.
- The maximum operating eccentric angle with an eccentric angle adaptor is ±10°.
- The caps and the guides for inclined use are not unbundled.






#### Stopper nut OP-020SB

 Adjust so that it stops 1 mm before the stroke end, and fasten with the main unit's nut until secured.






Mass 7g

Note: When attaching, make sure that the side without a bearing chamfer is the impact surface.

#### Standard nuts are sold separately as well - M08 Nut

#### Square flange OP-040SB

 Once the attachment site is determined, use the main unit's nut to securely fasten in place.



#### Holder with a switch OP-030SB-2

 Although a holder with a switch can be ordered on its own, we strongly recommend ordering one with the main unit. Please include the main unit's model number when placing an order.

