ITV9550 30A/45A/60A Series Surface Mount





Agency Approvals

Agency	Agency File Number	Ampere Range
c FL us	E10480	30 A, 45 A
\mathbf{A}	TA 50461285	30 A, 45 A

Thermal Derating Characteristics

Ambient Ope	25°C	40°C	60°C	
Recommend	ITV9550 30A Series	34.0	30.0	25.0
	ITV9550 45A Series	49.0	44.5	37.0
Rated Current (A)	ITV9550 60A Series	67.0	60.0	49.0

Description

ITV9550 Series is a chip type surface mountable device that can protect against both overcurrent and overcharging. It comprises a fuse element to ensure stable operation under normal electrical current and to cut off the current when overcurrent occurs. It also comprises a resistive heating element that could be used in combination with a voltage detecting means, such as IC and FET. When overvoltage is detected, the heating element is electrically excited to generate heat to blow the fuse element to achieve overvoltage protection.

Features & Benefits

- Halogen Free
- Surface Mount
- Fast response

Applications

- Vacuum cleaner
- Power tools
- E-scooter

- Protection for both overcurrent and overcharging
- E-bike UPS

Electrical Characteristics

David Nicorali a	Ondering Code	I _{rated}	Cells in	V _{max}	I _{break}	V _{OP}	Resista	ance	Agency Approvals	
Part Number	Ordering Code	(A)	Series	(Vdc)	(A)	(Ŭ)	R _{heater} (Ω)	R _{fuse} (mΩ)	c RL 'us	A
ITV9550L1230	ITV9550L1230MR	30	3	85	80	8.4 ~ 13.2	3.2 ~ 5.2	0.5 ~ 2.5	X	X
ITV9550L1430	ITV9550L1430MR	30	4	85	80	11.1 ~ 18.4	6.3 ~ 9.3	0.5 ~ 2.5	Х	Х
ITV9550L1830	ITV9550L1830MR	30	4~5	85	80	10.5 ~ 23.5	4.8 ~ 8.0	0.5 ~ 2.5	Х	Х
ITV9550L2030	ITV9550L2030MR	30	5	85	80	14.0 ~ 23.4	10.0 ~ 15.0	0.5 ~ 2.5	Х	Х
ITV9550L3030	ITV9550L3030MR	30	6~7	85	80	20.2 ~ 31.5	18.8 ~ 31.2	0.5 ~ 2.5	Х	Х
ITV9550L4030	ITV9550L4030MR	30	9~10	85	80	28.0 ~ 46.9	40.0 ~ 60.0	0.5 ~ 2.5	Х	Х
ITV9550L5030	ITV9550L5030MR	30	12~14	85	80	39.6 ~ 62.0	72.4 ~ 120.6	0.5 ~ 2.5	Х	Х
ITV9550L1245	ITV9550L1245MR	45	3	85	120	9.8 ~ 13.5	1.9 ~ 3.4	0.4 ~ 2.0	Х	Х
ITV9550L1445	ITV9550L1445MR	45	4	85	120	13.0 ~ 18.4	3.4 ~ 6.0	0.4 ~ 2.0	Х	Х
ITV9550L2045	ITV9550L2045MR	45	5	85	120	16.7 ~ 23.5	5.6 ~ 9.9	0.4 ~ 2.0	Х	Х
ITV9550L3045	ITV9550L3045MR	45	6~7	85	120	22.3 ~ 31.5	10.0 ~ 17.7	0.4 ~ 2.0	Х	Х
ITV9550L4045	ITV9550L4045MR	45	9~10	85	120	33.0 ~ 46.9	22.0 ~ 38.7	0.4 ~ 2.0	Х	Х
ITV9550L5045	ITV9550L5045MR	45	12~14	85	120	43.7 ~ 62.0	38.5 ~ 68.0	0.4 ~ 2.0	Х	Х
ITV9550L1260	ITV9550L1260MR	60	3	85	160	9.6 ~ 13.5	1.83 ~ 3.70	≤ 2.0	Pending	Pending
ITV9550L1460	ITV9550L1460MR	60	4	85	160	13.0 ~ 18.4	3.4 ~ 6.7	≤ 2.0	Pending	Pending
ITV9550L2060	ITV9550L2060MR	60	5	85	160	16.7 ~ 23.5	5.6 ~ 11.1	≤ 2.0	Pending	Pending
ITV9550L3060	ITV9550L3060MR	60	6~7	85	160	22.3 ~ 31.5	10.0 ~ 19.9	≤ 2.0	Pending	Pending
ITV9550L4060	ITV9550L4060MR	60	9~10	85	160	33.0 ~ 46.9	22.0 ~ 43.5	≤ 2.0	Pending	Pending
ITV9550L5060	ITV9550L5060MR	60	12~14	85	160	43.7 ~ 62.0	38.5 ~ 77.0	≤ 2.0	Pending	Pending
Current Capacity		100% x	I _{rated} , No N	/lelting						
Cut Time		200% >	cl _{rated} , < 1 r	min						
Interrupting Current		100A, power on 5 ms, power off 995 ms, 10000 cycles (ITV9550 30A series), No Melting 150A, power on 5 ms, power off 995 ms, 10000 cycles (ITV9550 45A series), No Melting 250A, power on 5 ms, power off 995 ms, 10000 cycles (ITV9550 60A series), No Melting								
Over Voltage Operatio	on	In opera	ation voltag	ge range,	the fusin	g time is <1m	n.			
tes: and = Current carrying capacity the set = The current that the fuse ele tar = The maximum voltage that c μ = Range of operation voltage canter = The resistance of the heat: me = The resistance of the fuse ele	can be cut off by fuse	ibrium conditio	nc		 Value spe glass epoxy Value spe glass epoxy Value spe 	cified is determined by PCB for ITV9550 30A S cified is determined by PCB for ITV9550 45A S	vusing the PWB with 25 eries using the PWB with 25	nm*2oz copper trac 5mm*2oz copper tra	es, AWG10 coveren	l wire, and 0.6m I wire, and 0.6m







Specifications are subject to change without notice.

Cut Time by Heater Operation (ITV9550 30A Series)

Various heater wattage at 25°C ambient temperature





Constant heater wattage at various ambient temperature



Cut Time by Heater Operation (ITV9550 45A Series)

Various heater wattage at 25°C ambient temperature






Ambient Temperature (°C)


Constant heater wattage at various ambient temperature

Cut Time by Heater Operation (ITV9550 60A Series)

Various heater wattage at 25°C ambient temperature




Constant heater wattage at various ambient temperature




🛃 Littelfuse

Cut Time by Current Operation (ITV9550 30A Series)

Various interrupting current at 25°C ambient temperature





Constant 2x rated current at various ambient temperature



Cut Time by Current Operation (ITV9550 45A Series)

Various interrupting current at 25°C ambient temperature







Constant 2x rated current at various ambient temperature

Cut Time by Current Operation (ITV9550 60A Series)

Various interrupting current at 25°C ambient temperature



Constant 2x rated current at various ambient temperature







ITV9550 30A/45A/60A Series Surface Mount

Environmental Specifications

Storage Temperature	0~35°C, ≤70%RH, 3 months after shipment
Operating Temperature	-10°C to +65°C
Hot Passive Aging	100±5°C, 250 hours No structural damage and functional failure
Humidity Aging	60°C±2°C, 90~95% R.H. 250 hours No structural damage and functional failure
Cold Passive Aging	-20±3°C, 500 hours No structural damage and functional failure
Thermal Shock	MIL-STD-202 Method 107G +125°C/-55°C, 100 times No structural damage and functional failure




Board and Solder Layout Recommend (mm)



Symbol	Dimensions
A1	1.30 ± 0.1
A2	1.52 ± 0.1
A3	7.60 ± 0.1
B1	3.10 ± 0.1
B2	0.75 ± 0.1
B3	1.95 ± 0.1
B4	2.50 ± 0.1
B5	2.00 ± 0.1
B6	2.50 ± 0.1

Physical Dimension (mm)






Battery Protector Datasheet

ITV9550 30A/45A/60A Series Surface Mount

Soldering Parameters

Average Ramp-Up Rate (7	3°C/second max.	
	Temperature Min (Ts _{min})	150°C
Preheat	Temperature Max (Ts _{max})	200°C
	Time (Ts _{min} to Ts _{max})	60-120 seconds
Time maintained above:	217°C	
	Time (t _L)	60-105 seconds
Peak Temperature (T _P)	255°C	
Time within 5°C of actual	5 seconds max.	
Ramp-Down Rate	6°C/second max.	
Time 25°C to Peak Tempe	8 minutes max.	




-- All temperature refer to topside of the package, measured on the package body surface -- If reflow temperature exceeds the recommended profile, devices may not meet the performance requirements

Physical Specifications

Material	Glass Epoxy PCB
Base Thickness	0.6mm
CommonThiskmoor	0.07mm for ITV9550 30A&45A Series
Copper Thickness	0.105mm for ITV9550 60A Series
	AWG10 (ITV9550 30A Series)
Covered Wire	AWG8 (ITV9550 45A Series)
	AWG6 (ITV9550 60A Series)

Typical Application Circuit Diagram




Installation and Handling Guidelines

- Before and after mounted, the ultrasonic-cleaning or immersioncleaning must not be done to ITV device. The flux on element would flow, and it would not be satisfied its specification when cleaning is done. In addition, a similar influence happens when the product comes in contact with cleaning solution. These products after cleaning will not be guaranteed.
- Silicone-based oils, oils, solvents, gels, electrolytes, fuels, acids, and similar will adversely affect the properties of ITV devices, and shall not be used or applied.
- Please DO NOT reuse the ITV device removed by the soldering process.
- ITV devices are secondary protection devices and are used solely for sporadic, accidental overcurrent or overtemperature error condition, and shall NOT be used if or when constant or repeated fault conditions (such fault conditions may be caused by, among others, incorrect pin-connection of a connector) or over-extensive trip events may occur.
- Operation over the maximum rating or other forms of improper use may cause failure, arcing, flame and/or other damage to the ITV devices.

- The performance of ITV devices will be adversely affected if they are improperly used under electronic, thermal and/or mechanical procedures and/or conditions non-conformant to those recommended by manufacturer.
- Customers shall be responsible for determining whether it is necessary to have back-up, failsafe and/or fool-proof protection to avoid or minimize damage that may result from extra-ordinary, irregular function or failure of ITV devices.
- There should be minimum of 0.1mm spacing between ITV and surrounding compounds, to maintain the product characteristics and avoid damage other surrounding compounds.
- This product is designed and manufactured only for general-use of electronics devices. We do not recommend that it is used for the applications military, medical and so on which may cause direct damages on life, bodies or properties.

Tape and Reel Specifications (mm)



Pa	nbering 9550		XX	MR
Series				
Device Size L: 9.5mm (0.38") W: 5.0mm (0.20")				
Company Symbol	 			
Operation Voltage 12V				
Rated Current 30 = ITV9550 30A series 45 = ITV9550 45A series 60 = ITV9550 60A series	 	 		
Tape/Reel 1000/Reel		 		


Symbol	Dimension
W	16.0 ± 0.30
F	7.50 ± 0.10
E1	1.75 ± 0.10
D0	1.50 ± 0.10
D1	1.50 ± 0.10
PO	4.00 ± 0.10
P1	8.00 ± 0.10
P2	2.00 ± 0.10
A0	5.40 ± 0.10
B0	9.85 ± 0.10
т	0.30 ± 0.05
КО	2.48 ± 0.10
Н	21.4 ± 1.0
W	17.4 ± 1.0
D	Ø99.0 ± 0.5
C	Ø330 ± 1.0

Packaging


Part Number	Tape and Reel Quantity
ITV9550LXXXX	1,000

Part Marking System

Marking System for ITV9550 30A&45A Series



Marking System for ITV9550 60A Series



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

