SAVE 40% IN PANEL SPACE AND COST: Packaged in a 72mm² DINsize housing, the 356 occupies 40% less panel space than previous IC timers. Modern production and assembly techniques have substantially reduced manufacturing costs resulted in a 45% cost saving.

LOW INVENTORY COSTS: Each Shawnee 356 covers the active count range of 1 to 9,999, easily satisfying the vast majority of industrial requirements and thus greatly reducing inventory.

DIMENSIONS (INCHES/MILLIMETERS)



MODEL NUMBER

MODEL NUMBER	356C			30	Ρ	
RANGE						
9,999 Counts		350				
99,990 Counts (units digit b	lind)	353				
Special		000				
VOLTAGE & FREQUENCY						
120 VAC 50-60 Hz			Q			
240 VAC, 50-60 Hz			R			
ARRANGEMENT						
With Display (On-Delay)				30		
FEATURES						
Basic plug-in unit					Р	
Standard unit						Х
Special						K

ACCESSORIES

Surface mounting bracket kit	0353-260-27-00
Retrofit kit	0305-265-61-70

The 356C Directly Replaces 356B & 356A.



Shawnee II Digital Counter

A compact version of the 336 counter, the ATC 356 is its exact functional duplicate. Packaged in a 72mm² DIN-size housing, it occupies 40% less panel space and costs proportionately less. Modern production and assembly techniques have all but eliminated hand wiring, enhancing the reliability and life expectancy of the 356.

FAST, ACCURATE AND BOUNCE-PROOF: The repeat accuracy of the 356 is 100%. It maintains full accuracy even at pulse rates up to 4,000/minute, even with pulses that are as brief as 1 millisecond, and even in the face of severe contact bounce, which it ignores by virtue of an extremely effective anti-bounce circuit.

EASY TO SET AT ALL TIMES: The Shawnee counter is easily and accurately set even with work gloves on. Push any of its four toggle levers in any sequence until the number you want appears above it. You can decrease as well as increase each number by pushing the levers up or down. You can change the setting at any time, even during a cycle.

PLUG-IN AND DUST-TIGHT: All 356 counters feature true plug-in design and can be replaced in seconds without disturbing the housing or disconnecting the wiring. The dial assembly is gasketed so that the counter body is dust-tight from the front of panel.

CYCLE PROGRESS INDICATION: The Shawnee 356 indicating counter provides cycle progress indication on the four-digit display located immediately above the digital setting number wheels. When the counter is in the reset condition, the VFD display is blank. During the cycle, the display counts up from 0, thus always indicating the number of counts that have elapsed since the start of cycle. At count-out, the display shows the total elapsed count and thus equals the numbers on the digital setting wheels.

COMPUTER-TESTED RELIABILITY: The solid-state 356 is manufactured from a series of computer-tested plug-in circuit boards and assembled virtually without hand wiring. Because it has no moving parts in its logic circuits, its life expectancy is practically unlimited. Even the load relay – the 356's only significant mechanical component – has a life expectancy of 10,000,000 operations (no load). As a result the 356 achieves an overall reliability that surpasses even that achieved by previous Shawnee counters.

NOISE IMMUNITY: The 356 does not have to be shielded: its transformer power supply, full-wave bridges, buffered logic and other design characteristics render it immune to the electrical noise that is sometimes encountered in industrial environments thus eliminating false starts and reset due to voltage spikes.

OPERATION

The Shawnee 356 operates on a digital logic circuit with three main elements: a pulse circuit; a read-only-memory (ROM) whose output is set by the counter's digital setting number wheels; and a comparator that continuously examines the outputs of the pulse circuit and ROM.

When power is applied (start signal on), two things happen simultaneously; the instantaneous DPDT relay is energized transferring both sets of contacts, and the pulse circuit begins to count each input pulse whose duration is at least 1 millisecond. The pulse circuit accumulates the count and feeds the total continuously to the comparator. When pulse circuit output exactly equals the output of the ROM, the comparator causes the 356 to count out.

At this point, (1) the DPDT delay relay is energized, immediately transferring both sets of contacts and (2) the pulse circuit turns itself off automatically. Since the pulse circuit stops counting even if the start signal remains on, it is not necessary to tie up one of the 356's delayed contacts to do this job.

To reset the 356, power must be removed from terminal 1 (L1) for 75 milliseconds or more. The 356 operates in the on-delay mode only, always resetting whenever there is a power outage and starting a new cycle when power is restored.

		Switching Sequence*		
RELAY	CONTACTS	Before Start	During Timing	End of Cycle
Instantaneous	14-9/6-8			
	14-10/6-7			
Delayed (D2)	11-12/4-5			
	11-13/4-3			

*Assumes a sustained closed start signal (i.e. longer than the setting on the digital display)



RANGE	1 to 9999 counts or 10 to 99,990, presettable in 10 count increments.			
COUNT INPUT	2300/MIN with 1:1 on-off time			
	4000/MIN with 1 mSEC on: 13 mSEC off			
	500/MIN with 20 mSEC on and 100 mSEC off			
	Wired for count and repeat operation			
	Min. Pulse ON Time: 1 mSEC			
	Min. Pulse OFF Time: 13 mSEC			
	Ready-To-Count	10 mSEC after application of		
	Time	power to terminals 1 and 2		
	Bounce Immunity	6 mSEC		
	(max_bounce_oper	n time)		
	Pulse Contact Reg. 30mA (at line voltage)			
LICLE PROGRESS	4 digit, 0.3 inch, h	igh intensity, blue display.		
REPEAT	100%			
ACCURACY				
RESET TIME	75 mSEC minimum			
SETTING	i count			
	Single Cycle	internal on deleved		
COUNT MODES	Single Cycle	Interval or delayed		
CONTROL MODES	Repeat Cycle	pulses		
LOAD RELAYS	Number	two, one instantaneous and one		
		delayed; both plug-in, DPDT		
	Operate Time	20 mSEC max.		
	Release Time	instantaneous –20 mSEC, max.		
		delayed—75 mSEC, max.		
	Contact Rating	5A at 120 VAC.		
	5	2A at 240 VAC.		
		0.1A at 125 VDC		
	Life	100 million operations (no load		
TEMDEDATIIDE	32° to 140°E (0°	to 60°C)		
RATING	52 10 140 1 (0	10 00 C)		
DOWER	120V 0E 122V			
POWER	1200 95-1320	at 50 or 60 Hz		
KEQUIKEMENIS	inrush -0.	4A		
	running –	-0.08A		
	240V 190-264V	at 50 or 60Hz		
	inrush - 0	.2A		
	running—	-0.04A		
TERMINALS	16 screw terminals accessible at rear; into			
	diagram on housin	ıg.		
HOUSING	Plug-in design; completely gasketed. dust			
	panel-mounted.			
	Standard	Hardware is provided to mount		
MOUNTING				
MOUNTING		timer so that it is dust-tight		
MOUNTING ACCESSORIES		timer so that it is dust-tight		
MOUNTING ACCESSORIES See Accessory	Ontional	timer so that it is dust-tight from front of panel.		
MOUNTING ACCESSORIES See Accessory section of catalog	Optional	timer so that it is dust-tight from front of panel. Surface mounting without and with front-facing terminals		
MOUNTING ACCESSORIES See Accessory section of catalog	Optional	timer so that it is dust-tight from front of panel. Surface mounting without and with front-facing terminals.		

356C Series





All timers shown in "before start" position. Diagrams shown with power off unless otherwise marked.

Maximum load current through any load carrying contact is 5 amperes.

Pilot light leads are brought out to terminal block. Pilot light can be wired to show practically any desired function; unit energized, cycle running, instantaneous or delayed switch closed, etc.

ON DELAY-Reset on power failure.

(F) INSTANTANEOUS CONTACTS Contacts are transferred when power supply is energized;

d transferred back, as shown when de-energized.

SUSTAINED START



MOMENTARY START/SUSTAINED START



COUNT, PULSE AND REPEAT CYCLE





356C Series