


Our Hybrid Stepper Motors are a precise motion control solution providing excellent holding torque. They come in a various sizes and step angles. With endless performance combinations, we have a fully tailor solution for you.




View Alternative Solutions!

Specifications	
Gearhead Type:	Planetary
Motor Type:	Hybrid Stepper
Rated Voltage:	4.32V DC
Number of Phases:	2
Rated Current:	0.8 A
Number of Leads:	4

Step Angle:	1.8 °
Phase Inductance:	1.5 mH (+/- 20%) @ 1kHz
Holding Torque:	15.86 kg.cm
Phase Resistance:	5.4 Ω
Insulation Class:	В
Reduction Ratio:	71:1



Wiring Diagram





© 2022 ISL Products International Ltd. Specifications subject to change without notice.

ISL Products International Ltd. • 572 Walt Whitman Rd. ,Ste 100 • Melville, NY 11747 • T 516-937-3475 • www.islproducts.com