

# ST8812FX

# High voltage fast-switching NPN Power transistor

#### **Features**


- High voltage capability
- Very high switching speed
- Tight hfe control
- Large R.B.S.O.A.
- Fully insulated Package U.L. compliant for easy mounting

### **Applications**


■ Switch mode power supplies for crt TV

### **Description**

The ST8812FX is manufactured using latest Multi Epitaxial Planar technology with high voltage capability. It shows wide R.B.S.O.A. and high switching speed thanks to its Cellular Emitter structure with planar edge termination and deep base diffusion.



### Internal schematic diagram



#### Order codes

Part Number	Marking	Package	Packing
ST8812FX	ST8812FX	ISOWATT218FX	TUBE

ST8812FX Electrical ratings

#### **Electrical ratings** 1

Table 1. **Absolute maximum rating** 

Symbol	Parameter	Value	Unit
V <sub>CBO</sub>	Collector-Base Voltage (I <sub>E</sub> = 0)	1150	V
V <sub>CEO</sub>	Collector-Emitter Voltage (I <sub>B</sub> = 0)	600	V
V <sub>EBO</sub>	Emitte-Base Voltage (I <sub>C</sub> = 0)	15	V
I <sub>C</sub>	Collector Current	7	Α
I <sub>CM</sub>	Collector Peak Current (t <sub>P</sub> < 5ms)	12	Α
Ι <sub>Β</sub>	Base Current	4	Α
P <sub>TOT</sub>	Total dissipation at T <sub>c</sub> = 25°C	50	W
V <sub>isol</sub>	Insulation Withstand Voltage (RMS) from All Three Leads to External Heatsink	2500	V
T <sub>STG</sub>	Storage Temperature	-65 to 150	°C
TJ	Max. Operating Junction Temperature	150	°C

Table 2. Thermal data

Obsolete Product(s)

Table 2.	Thermal data	34			
Symbol	Parameter	7/8,	Value	Unit	
R <sub>thJ-case</sub>	Thermal Resistance Junction-Case	Max	2.5	°C/W	

ST8812FX Electrical characteristics

# 2 Electrical characteristics

(T<sub>CASE</sub> = 25°C; unless otherwise specified)

Table 3. Electrical characteristics

Symbol	Parameter	Test Conditions	Min.	Тур.	Max.	Unit
I <sub>CES</sub>	Collector Cut-off Current (V <sub>BE</sub> = 0)	V <sub>CE</sub> = 1150V V <sub>CE</sub> = 1150V T <sub>c</sub> = 125°C			1 2	mA mA
I <sub>EBO</sub>	Emitter Cut-off Current $(I_C = 0)$	V <sub>EB</sub> = 14V			1	mA
V <sub>CEO(sus)</sub> Note: 1	Collector-Emitter Sustaining Voltage (I <sub>B</sub> = 0)	I <sub>C</sub> = 100mA	600		119	V
V <sub>CE(sat)</sub> Note: 1	Collector-Emitter Saturation Voltage	$I_{C} = 4A \qquad \qquad I_{B} = 0.8 A$ $I_{C} = 4A \qquad \qquad I_{B} = 1.2 A$		917	3 1.5	V V
V <sub>BE(sat)</sub> Note: 1	Base-Emitter Saturation Voltage	$I_C = 4A$ $I_B = 0.8A$	101	)	1.3	V
h <sub>FE</sub>	DC Current Gain	$I_{C} = 1A$ $V_{CE} = 5V_{CE} = 10$ $I_{C} = 5A$ $V_{CE} = 10$ $I_{C} = 5A$ $V_{CE} = 5V_{CE} $	/	25 5	9	
t <sub>s</sub>	INDUCTIVE LOAD Storage Time Fall Time	$I_{C} = 4A$ $R_{BB} = 6$ $V_{Clamp} = 480V$ $V_{BE(off)} = -5V$ $I_{B1} = 0.8A$ $L_{C} = 220 \mu F$ (See Figure 8)	/	1 60	1.6 120	μs ns

Note: 1 Pulsed duration = 300 μs, duty cycle ≤1.5%.

**57**/

Electrical characteristics ST8812FX

# 2.1 Typical characteristics test circuit

Figure 1. DC current gain




Figure 2. DC current gain





Figure 3. Collector emitter saturation voltage Figure 4. Base emitter saturation voltage








Figure 5. Inductive load storage time


Figure 6. Inductive load fall time






ST8812FX Electrical characteristics

Figure 7. Reverse biased S.O.A.



Electrical characteristics ST8812FX

Figure 8. Inductive load switching test circuit




# 3 Package mechanical data

In order to meet environmental requirements, ST offers these devices in ECOPACK® packages. These packages have a Lead-free second level interconnect . The category of second Level Interconnect is marked on the package and on the inner box label, in compliance with JEDEC Standard JESD97. The maximum ratings related to soldering conditions are also marked on the inner box label. ECOPACK is an ST trademark. ECOPACK specifications are available at: www.st.com.

Obsolete Product(s).

#### **ISOWATT218FX MECHANICAL DATA**

DIM.	mm		inch			
DIM.	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.
Α	5.30		5.70	0.209		0.224
С	2.80		3.20	0.110		0.126
D	3.10		3.50	0.122		0.138
D1	1.80		2.20	0.071		0.087
E	0.80		1.10	0.031		0.043
F	0.65		0.95	0.026		0.037
F2	1.80		2.20	0.071		0.087
G	10.30		11.50	0.406		0.453
G1		5.45			0.215	$AU^{i}$
Н	15.30		15.70	0.602		0.618
L	9.0		10.20	0.354	210	0.402
L2	22.80		23.20	0.898		0.913
L3	26.30		26.70	1.035		1.051
L4	43.20		44.40	1.701		1.748
L5	4.30		4.70	0.169		0.185
L6	24.30		24.70	0.957		0.972
L7	14.60	<del></del>	15.00	0.575		0.591
N	1.80		2.20	0.071		0.087
R	3.80	<del></del>	4.20	0.150		0.165
DIA	3.40		3.80	0.134		0.150



ST8812FX Revision History

# 4 Revision History

Table 4. Revision history

Date	Revision	Changes
23-Feb-2006	1	Initial release.

Obsolete Product(s). Obsolete Product(s)

#### Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

UNLESS EXPRESSLY APPROVED IN WRITING BY AN AUTHORIZE REPRESENTATIVE OF ST, ST PRODUCTS ARE NOT DESIGNED, AUTHORIZED OR WARRANTED FOR USE IN MILITARY, AIR CRAFT, SPACE, LIFE SAVING, OR LIFE SUSTAINING APPLICATIONS, NOR IN PRODUCTS OR SYSTEMS, WHERE FAILURE OR MALFUNCTION MAY RESULT IN PERSONAL INJURY, DEATH, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2006 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com