MTi-1

- Smallest form factor on the market
- Easy integration
- Development Kit available

The MTi-1 is the smallest industrial grade self-contained Inertial Measurement Unit (IMU) available on the market. The Xsens optimized strapdown algorithm (AttitudeEngine™) performs high-speed dead-reckoning calculations at 1 kHz, accurately capturing high-frequency motions. The MTi-1 is a cost-effective module for a wide range of (embedded) applications. It relieves you of the work of designing, integrating and maintaining gyroscopes, accelerometers and other sensors.

The MTi-1 is part of the MTi 1-series supported by the MT Software Suite, which includes MT Manager (GUI for Windows/Linux), SDK, example codes and drivers for many platforms.

12.10 mm
2.55 mm

- 3D models available on request
- Available online via Digi-Key, Mouser, Farnell and local distributors
- For full specifications: please refer to the MTi-series datasheet available at mtidocs.xsens.com

U Performance	Mec
· · · · · · · · · · · · · · · · · · ·	1-100

IMU Performance	
Accelerometer	Calibrated
Gyroscope —————————	Calibrated
Strapdown Integration (SDI)	Yes
Gyroscope	
Standard full range	2000 deg/s
In-run bias stability	10 deg/h
Bandwidth (-3dB)	230 Hz
Noise Density	0.003 º/s/√Hz
g-sensitivity (calibr.)	0.001 °/s/g
Accelerometer	
Standard full range	16 g
In-run bias stability	30 μg
Bandwidth (-3dB)	230 Hz
Noise Density	70 μg/√Hz
Magnetometer	
Standard full range	+/- 8 G
Total RMS noise	0.5 mG
Non-linearity	0.2%
Resolution ————————————————————————————————————	0.25 mG
GNSS Receiver	
GNSS receiver interface	n/a
GNSS precision	n/a
RTCM input port ————————————————————————————————————	n/a
Barometer	
Barometer interface	n/a

hanical

IP-rating	IP00
Operating Temperature ———	-40 to 85 °C
Casing material	PCB
Mounting orientation	No restriction, full 360° in all axes
Dimensions ————————————————————————————————————	12.1 x 12.1 x 2.55 mm
Connector	SMD, footprint compatible with JEDEC
	PLCC-28
Weight	0.6 g

Electrical

Input voltage	2.19 to 3.6V
Power consumption (typ)	44 mW @ 3V

Interfaces / IO

Interfaces	UART, SPI, I ² C
Sync Options	Yes
Protocols	Xbus
Clock drift	10 ppm
Output Frequency	Up to 2kHz
Built-in-self test	Gyr, Acc, Mag

Software Suite

GUI (Windows/Linux)	MT Manager Firmware updater,
	Magnetic Field Mapper
SDK (Example code)	C++, C#, python, Matlab, Nucleo,
	public source code
Drivers	LabVIEW, ROS, GO
Support	BASE by XSENS: online manuals,
	community and knowledge base



