

(SKC0410-P01,02,140701)


Specifications						Ver.2
Product Name	Name PIR MOTION SENSOR "Pa		aPIRs"	Model No.	EKMB430111[	]K Page: 2
4.Charact	eristics	<u>i</u>				
		erformance for measuring: Am	bient te	mperature=2	25°C(77°F) Operatii	ng voltage=3VDC
		Temperature difference		/alue	Conditions conce	
``	te1)	4°C(7.2°F)	up to 7m		1.Movement speed: 1.0m/s 2.Target concept is human body (Object size:Around 700×250mm)	
	tection nge	2°C(3.6°F)	up to 5m			
Note1		ding on the temper ion range will chan		ifference bet	ween the target and	the surroundings,
				Value	Note	es
		Horizontal	94	°(±47°)		
	ection rea	Vertical	82	°(±41°)	Refer to the section 4-5.	
		Detection zones		64		
4-2 Ma	ximum	Rated Values				
				Va	lue	Unit
F	Power Supply Voltage		-0.3~4.5		VDC	
Usa	Usable Ambient Temperature		-20 $\sim$ +60°C (-4 $\sim$ +140°F) Do not use in a freezing or condensation environment		a freezing or	


### 4-3 Electrical Characteristics


Conditions for Measuring: Ambient temperature: 25°C(77°F)

	Symbol	Min	Avg.	Max	Unit	Special mention
Operating Voltage	Vdd	2.3	_	4.0	VDC	_
Electrical Current Consumption	Iw	_	6	12	μA	lout=0
Output Current	lout	_	_	100	μA	Vout≧Vdd-0.5
Output Voltage	Vout	Vdd-0.5		_	VDC	_
Circuit Stability Time (when voltage is applied)	Twu	_	_	10	S	This is when temperature of the sensor is stable.

Issued on Jul. 1<sup>st</sup>,2019







Specifications				
Product Name	PIR MOTION SENSOR "PaPIRs"	Model No.	EKMB430111∐K	Page: 6
				•

#### 5. Safety Precautions


Head the following precautions to prevent injury or accidents.

- Do not use these sensors under any circumstance in which the range of their ratings, environment conditions or other specifications are exceeded. Using the sensors in any way which causes their specifications to be exceeded may generate abnormally high levels of heat, emit smoke, etc., resulting in damage to the circuitry and possibly causing an accident.
- 2) Our company is committed to making products of the highest quality and reliability. Nevertheless, all electrical components are subject to natural deterioration, and durability of a product will depend on the operating environment and conditions of use. Continued use after such deterioration could lead to overheating, smoke or fire. Always use the product in conjunction with proper fire-prevention, safety and maintenance measures to avoid accidents, reduction in product life expectancy or break-down.
- Before connecting, check the pin layout by referring to the connector wiring diagram, specifications diagram, etc., to verify that the connector is connected properly. Mistakes made in connection may cause unforeseen problems in operation, generate abnormally high levels of heat, emit smoke, etc., resulting in damage to the circuitry.
- 4) Do not use any motion sensor which has been disassembled or remodeled.
- 5) Failure modes of sensors include short-circuiting, open-circuiting and temperature rises. If this sensor is to be used in equipment where safety is a prime consideration, examine the possible effects of these failures on the equipment concerned, and ensure safety by providing protection circuits or protection devices. Example :
  - ·Safety equipments and devices
  - Traffic signals
  - ·Burglar and disaster prevention

	Ver.2.1					
Product Name	Product Name PIR MOTION SENSOR "PaPIRs" Model No. EKMB430111 K Page: 7					
6.Operating	Precautions		L			
6-1 Basic F	Principles					
However, heat sour	a pyroelectric infrared sensor th it may not detect in the following ce. Besides, it could also detect t and reliability of the system may	cases: lack o he presence	of movement, no temperatu of heat sources other than	a human body.		
1) Detect	ing heat sources other than the h	iuman body, s	such as:			
b) When beam c) Sudd	I animals entering the detection a n a heat source for example sun hit the sensor regardless inside o len temperature change inside or HVAC, or vapor from the humidifi	light, incande or outside the around the d	detection area.			
2) Difficul	Ity in sensing the heat source					
a cor b) Non-	s, acrylic or similar materials stan rect transmission of infrared rays movement or quick movements o se refer to 4-1 for details about m	, of the heat so	urce inside the detection ar	-		
3) Expan	sion of the detection area					
	of considerable difference in the on area may be wider apart from t			dy temperature,		
4) Malfun	ction / Detection error					
output o	essary detection signal might be o due to the nature of pyro-electric o n strictly, please implement the o	element. Whe	en the application does not	accept such		
6-2 Optima	al Operating Environment Condition	ons				
2) Humid 3) Pressu 4) Overhe 5) This se	erature : Please refer to the ma ity Degree :15~85% Rh (Avoid ire : 86~106kPa eating, oscillations, shocks can ca ensor is not waterproof or dustpro re, condensation, frost, containing	condensation ause the sens pof. Avoid use	n or freezing of this product sor to malfunction. e in environments subject to			
	use in environments with corrosiv					

Issued on Jul. 1<sup>st</sup>,2019

	Specifications				
Product Nam	e PIR MOTION SEN	ISOR "PaPIRs"	Model No.	EKMB430111□K	Page: 8
6-3 Ha	ndling Cautions		,		- <b>·</b>
	o not solder with a sol his sensor should be h	-	ove 350°C (662	2°F), or for more than 3 se	conds.
2) To	o maintain stability of	the product, alv	ways mount o	n a printed circuit board.	
,	o not use liquids to wa erformance.	ash the sensor.	If washing flu	id gets through the lens, it	can reduce
4) De	o not use a sensor aft	er it fell on the	ground.		
	ne sensor may be dan e pins and be very ca			c electricity. Avoid direct h duct.	and contact with
,	hen wiring the produc	t, always use s	shielded cable	s and minimize the wiring	length to prevent
is	highly recommended urge resistance : be	ł.		age surge. Use of surge at le value indicated in the ma	
N	Please use a stabilized power supply. Power supply noise can cause operating errors. Noise resistance : $\pm 10V$ or less (Square waves with a width of 50ns or 1µs) To reduce the effect of power supply noise, install a capacitor on the sensor's power supply pin.				
	perating errors can be dio, broadcasting offic		ise from static	electricity, lightning, cell p	bhone, amateur
10) D	etection performance	can be reduce	d by dirt on th	e lens, please be careful.	
		•	• • •	Please avoid adding weight or reduced performance.	or impacts that
n h tł	ot guarantee durability umidity levels will acc	y or environme elerate the det	ntal resistance erioration of e	uggested to prolong usage e. Generally, high tempera lectrical components. Plea ne expected reliability and	tures or high se consider both
	Do not attempt to clean this product with any detergent or solvent, such as benzene or alcohol, as these can cause shape or color alterations.				
er	Avoid storage in high, low temperature or liquid environments. As well, avoid storage in environments containing corrosive gas, dust, salty air etc. It could cause performance deterioration and the sensor's main part or the metallic connectors could be damaged.				
	torage conditions Temperature: Humidity: lease use within 1 yea	+5 ~ +40°C (- 30 ~ 75% ar after product		<sup>-</sup> )	
Issued on	Jul. 1 <sup>st</sup> ,2019	6	Panaso	nic Corpora	tion



<sup>(</sup>SKC0410-P01,02,140701)

	Ver.2.1			
Product Name	PIR MOTION SENSOR "PaPIRs"	Model No.	EKMB430111 K	Page: 10

#### **8.Special Notice**

As improvements are continually being made, the specifications or design of this product are subject to change without notice.

Please strictly follow the "Safety Precautions" and "Operating Precautions" on the specifications sheet. Normal functioning cannot be expected if used in environments or conditions other than those specified above.

We are deeply committed to providing the highest quality control for this product. Nevertheless:

- For issues not addressed above, we invite you to share your suggestions, or details about your company's usage conditions, installation, specifications, needs of end users, and applications for this sensor.
- 2) To reduce the risk of harm caused by product failure to human life or assets, this product should always be used in conjunction with other safety measures, such as protective circuitry, double layered circuit boards, etc., and used within the guaranteed performance, efficiency or special characteristics values stated in the specification sheet.
- 3) This product is warranted for a period of one year, from date of delivery, applicable only if the product is used in accordance with the precautions mentioned above and the specifications sheet. We will replace or repair at the delivery location any malfunctioning or defective part or entire product if such defect or malfunction is caused by us.

However, the above warranty shall be void in the following circumstances:

- a) Damage caused to something else than the product itself.
- b) Damage or loss resulting during transportation, storage or handling after the date of supply.
- c) Phenomenon unforeseeable in the state of the technology as of the supply date.
- d) Damage caused by natural or unnatural events such as fire, earthquake, flood, or conflicts beyond our control.