


3UWC1.030W

- Industry Standard 3mm (T1) Package
- RoHS Compliant
- Water Clear Lens
- 3100K Color Temperature
- Multiple Intensity and Viewing Angle Options
- Available in Flange and Standard LED Body styles
- Ideal for Status Indication and Display

Bivar's 3mm T1 Package 3UWC Series LED may be used in almost any application. They are offered in 3100K color temperature and come in multiple intensity, viewing angle, and body styles. Bivar offers a water clear LED lens for maximum light output. The Standard LED is ideal for vertical spacer and holder assemblies.

Part Number	Material	Emitted Color	Color Temperature	Lens Appearance	Viewing Angle		
3UWC1.030W	InGaN/Sapphire	WHITE	3100K	Water Clear	30°		

Part Number Designation






Bivar reserves the right to make changes at any time without notice.



Outline Dimensions



Recommended Mounting							
Hole Size = Ø.032 ^{+.003} 002							

Outline Drawings Notes: 1. All dimensions are in inches [millimeters]. 2. Standard tolerance: ±0.010" unless otherwise noted. 3. Tolerance of overall epoxy outline: ±0.020" unless otherwise noted. 4. Epoxy meniscus may extend to 0.060" max.



Absolute Maximum Ratings

 $T_A = 25^{\circ}C$ unless otherwise noted

Power Dissipation	120 mW
Forward Current (DC)	30 mA
Peak Forward Current ¹	100mA
Reverse Voltage	5 V
Operating Temperature Range	-25 ~ +80°C
Storage Temperature Range	-30 ~ +80°C
Lead Soldering Temperature (3 mm from the base of the epoxy bulb) ²	260°C

Notes: 1. 10% Duty Cycle, Pulse Width \leq 0.1 msec. 2. Solder time less than 5 seconds at temperature extreme.


Electrical / Optical Characteristics


 $T_A = 25^{\circ}C \& I_F = 20 \text{ mA}$ unless otherwise noted

Part Number	Forward Voltage (V) ¹			Recommend Forward Current (mA)		Reverse Current (µA)	rent CCT		CT (Kelvin)		uminou sity lv (Viewing Angle 2 O ½ (deg)		
	MIN	ΤΥΡ	MAX	MIN	ΤΥΡ	MAX	MAX	MIN	TYP	MAX	MIN	ΤΥΡ	MAX	ТҮР
3UWC1.030W	2.7	3.2	3.6	/	20	/	10	/	3100	/	3000	5000	8000	30

Notes: 1. Tolerance of forward voltage : ±0.05V.

Directivity Radiation — Relative Luminous Intensity vs. Radiation Angle Ta = 25°C unless other noted






livar reserves the right to make changes at any time without notice.



Typical Electrical / Optical Characteristics








Fig.2 Relative Luminous Intensity vs. Forward Current







Fig.3 Reverse Current vs.Reverse Voltage









Bivar reserves the right to make changes at any time without notice.



Recommended Soldering Conditions



Packaging and Labeling Plan



Bivar reserves the right to make changes at any time without notice.