

#### Datasheet

DS000XXX



#### **Analog Frontend for Vital Sign Monitoring**

v3-00 • 2022-Mar-17



7

8

9

## **Content Guide**

1	General Description 3	
1.1 1.2 1.3	Key Benefits & Features4 Applications4 Block Diagram5	
2	Ordering Information6	
3	Absolute Maximum Ratings7	
3 4	Absolute Maximum Ratings 7 Electrical Characteristics 8	
-	· ·	

- Soldering & Storage Information 13
- Revision Information ......14
- Legal Information......15

## **1** General Description

The AS7050 Biosignal Sensor Analog Frontend is the next generation Vital Sign Sensor. It enables the user to detect biosignals such as photoplethysmogram (PPG), electrocardiogram (ECG) and galvanic skin resistance (GSR). PPG is the most used HRM method. It measures the pulse rate by sampling light modulated by the blood vessels, which expand and contract as blood pulses through them. ECG is the reference for any measurement of the biopotential generated by the heart.

Compared to the previous ams-OSRAM biosignal sensor generation, AS7050 is a biosignal converting unit. The AS7050 provides up to 8 LED driver outputs, samples up to 6 photodiode inputs and supports external electrodes. This enables the highest flexibility for several LED and photodiode arrangements in different applications. Furthermore, the AS7050 Biosignal Sensor Analog Frontend provides 2 ADC channels for simultaneous PPG and ECG measurements and an automatic photodiode offset control.

The embedded ECG analog front-end satisfies IEC 60601-2-47 requirements.

The AS7050's low-power design and small form factor are particularly well suited to application in fitness bands, smartwatches, sports watches, smart patches and earbuds. In these cases, board space is limited, and users look for extended, multi-day intervals between battery recharges. Thin package dimension makes the AS7050 suitable for height constrained solution likes earbuds

#### 1.1 Key Benefits & Features

The benefits and features of AS7050, Analog Frontend for Vital Sign Monitoring are listed below:

Figure 1:

Added Value of Using AS7050

Benefits	Features
High flexible LED/photodiode configuration.	Up to 8 LED drivers and 6 photodiode input pins.
Allows smallest application size e.g. narrow HRM measurement band.	Small Wafer-Level-Chip-Scale-Package (WLCSP).
Electrocardiogram ECG with dry electrodes.	Embedded low noise analog front-end for ECG signals acquisition.
Enables blood pressure measurements.	Synchronized PPG and ECG acquisition.
Excellent HRM measurement quality.	Low noise analog front-end for PPG acquisition
Additional information for end user.	Analog electrical front-end (e.g. for temperature sensing using a NTC or galvanic skin resistivity (GSR)).
Long operating time.	Hardware sequencer to offload processor. Adjustable LED driver with current control.
Ready for blood oxygen measurement	2 PPG channels useable in simultaneous mode available
Acquiring several bio signals in parallel	ECG and PPG channels separated and simultaneous useable

#### 1.2 Applications


- Optical sensor platform
- Fitness band
- Smart watch
- Smart patches
- Heart rate monitor
- Hearables
- ECG monitoring
- Cuff-less blood pressure measurements

#### 1.3 Block Diagram

The functional blocks of this device are shown below:

Figure 2 :

Functional Blocks of AS7050



# 2 Ordering Information

Ordering Code	Package	Marking	Delivery Form	Delivery Quantity
AS7050-BWLM	WLCSP	n.a.	Tape & Reel	500 pcs/reel
AS7050-BWLT	WLCSP	n.a.	Tape & Reel	10000 pcs/reel

#### 3 Absolute Maximum Ratings

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only. Functional operation of the device at these or any other conditions beyond those indicated under "Operating Conditions" is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

#### Figure 3

Absolute Maximum Ratings of AS7050

Symbol	Parameter	Min	Мах	Unit	Comments
Electrical Parameters					
V <sub>DD</sub>	Digital Supply Voltage		1.98	V	
V <sub>DDA</sub>	Analog Supply Voltage		1.98	V	
V <sub>DDIO</sub>	IO Supply Voltage		6	V	
V <sub>GNDA-PGND</sub>	Analog to Power Ground Voltage Difference		±0.3	V	
$V_{\text{GNDA-GND}}$	Analog to Digital Ground Voltage Difference		±0.3	V	
I <sub>SCR</sub>	Input Current (latch-up immunity)		±100	mA	Norm: JEDEC JESD78 Connect specified capacitor on SIGREF and V_LDO during latch-up test.
ILEDON	Average LED ON Current		35	mA	DC current with all LEDs ON during all time slots
Electrostati c Discharge					
ESDHBM	Electrostatic Discharge HBM		±2.0	kV	JS-001-2017
Temperatur e Ranges and Storage Conditions					
T <sub>STRG</sub>	Storage Temperature Range	-40	125	°C	
Т <sub>АМВ</sub>	Operating Free-air Temperature	-30	85	°C	
T <sub>BODY</sub>	Package Body Temperature		260	°C	IPC/JEDEC J-STD-020 <sup>(1)</sup>
RH <sub>NC</sub>	Relative Humidity (non-condensing)	5	85	%	
MSL	Moisture Sensitivity Level		1		Maximum floor life time unlimited @ 30°C/85% RH <sub>max</sub>

(1) The reflow peak soldering temperature (body temperature) is specified according to IPC/JEDEC J-STD-020 "Moisture/Reflow Sensitivity Classification for Non-hermetic Solid State Surface Mount Devices."

## **4 Electrical Characteristics**

All limits are guaranteed. The parameters with Min and Max values are guaranteed with production tests or SQC (Statistical Quality Control) methods.

#### Figure 4:

**Electrical Characteristics of AS7050** 


Symbol	Parameter	Conditions	Min	Тур	Max	Unit
V <sub>DD</sub>	Supply voltage		1.7	1.8	1.98	V
Vdda	Analog positive supply voltage		1.7	1.8	1.98	V
Vddio			Vdd	3.3	6	V
fextclk	External clock frequency		2		4	MHz
f <sub>Sampling,ECG</sub>	Sampling frequency				8	kHz
fSampling,PPG	Sampling frequency				1	kHz
Photodiode						
los	DAC offset current full scale range				128	μA
Срд	Total photodiode capacitance connected	0 V reserve voltage		60	300	pF
I <sub>PD</sub>	Photo current input	RTIA (TIA gain) values 9.375 kΩ- 1.2 MΩ; (Σ signal range 1 μA- 64 μA)	0		64	μΑ
ECG						
Vin_sig	Input signal ECG	Max ECG input signal according to IEC 60601-2-47, chapter 201.12.4.4.101	-10		10	mV

Symbol	Parameter	Conditions	Min	Тур	Мах	Unit
Vin_dc_off	Input DC offset	Max ECG DC Offset voltage according to IEC60601-2-47, chapter 201.12.4.4.101	-300		300	mV
VNoise, p-v	Input-related peak to valley noise	Measured at the output of ECG amplifier in the frequency range of f <sub>IN</sub> according to IEC 60601-2-47, chapter 201.12.4.4.106			50	μV
Rın	Input Impedance	According to IEC 60601-2-47, chapter 201.12.4.4.102		100		MΩ
ECG-MODE DSM Interface						
ECG_CR	ECG conversion rate	19-bit resolution		8		kSps
ECG_P_TOTAL	Power consumption			5		mA
ECG_RES	ECG Resolution		19			bits
ECG_ENOB	ENOB			17		bits
Vecgadc_refp	Positive reference voltage			1.6		V
LED Driver						
VLED	LED pad voltage				5	V
LED Driver 1-6						
Iled	Allowed operating LED output current				300	mA
V <sub>Compl_1</sub>	Compliance voltage				0.85	V
LED Driver 7-8						
ILED	Allowed operating LED output current				50	mA
VCompl_1	Compliance voltage				0.3	V

Symbol	Parameter	Conditions	Min	Тур	Мах	Unit
Reference Block						
Vecg_vcm	Reference voltage	at T=27 °C		0.8		V
VREF_ADC	Reference voltage	Trimmed reference voltage, at T=27 °C		1.6		V
V <sub>PPG_VCM</sub>	Reference voltage	at T=27 °C		0.8		V
TSEN_OUT	Temperature sensor output voltage	At room temperature		636		mV
TSEN_TK	Temperature sensor temperature coefficient of the output voltage	-40 °C to 105 °C		-2.03		mV/°C
Analog Front Er	nd					
Vout_dac	Output voltage DAC			1.6		V
Vout_afe	Output voltage range AFE		0.3		1.4	V
R <sub>range</sub>	Bias resistor trimming range	Across process and voltage corners, 25 °C		500		kΩ
Cgpio	Load capacitance GPIO1/2				50	pF
LDO						
VLDO		HV power supply	2.3		5.5	V
VLDO1V8	Output voltage	Output voltage in operating mode		1.8		V
CLDO	Output capacitance	External blocking capacitance		1		μF

# 5 Package Drawings & Markings

#### Figure 5: Package Outline Drawing




- (2) All dimensions are in micrometers. Angles in degrees.
- (3) Dimensioning and tolerancing conform to ASME Y14.5M-1994.
- (4) This package contains no lead (Pb).
- (5) This drawing is subject to change without notice.

## 6 Tape & Reel Information

#### Figure 6:


**Tape Dimensions** 



## 7 Soldering & Storage Information

#### Figure 7:

Solder Reflow Profile Graph



#### Figure 8: Solder Reflow Profile

Parameter	Reference	Device
Average temperature gradient in preheating		2.5 °C/s
Soak time	t <sub>soak</sub>	2 to 3 minutes
Time above 217 °C (T1)	t1	Max 60 s
Time above 230 °C (T2)	t2	Max 50 s
Time above T <sub>peak</sub> – 10 °C (T3)	t3	Max 10 s
Peak temperature in reflow	T <sub>peak</sub>	260 °C
Temperature gradient in cooling		Max −5 °C/s

## 8 **Revision Information**

Document Status	Product Status	Definition
Product Preview	Pre-Development	Information in this datasheet is based on product ideas in the planning phase of development. All specifications are design goals without any warranty and are subject to change without notice
Preliminary Datasheet	Pre-Production	Information in this datasheet is based on products in the design, validation or qualification phase of development. The performance and parameters shown in this document are preliminary without any warranty and are subject to change without notice
Datasheet	Production	Information in this datasheet is based on products in ramp-up to full production or full production which conform to specifications in accordance with the terms of ams AG standard warranty as given in the General Terms of Trade
Datasheet (discontinued)	Discontinued	Information in this datasheet is based on products which conform to specifications in accordance with the terms of ams AG standard warranty as given in the General Terms of Trade, but these products have been superseded and should not be used for new designs

Changes from previous version to current revision v3-00

Page

• Page and figure numbers for the previous version may differ from page and figure numbers in the current revision.

• Correction of typographical errors is not explicitly mentioned.

#### 9 Legal Information

#### **Copyrights & Disclaimer**

Copyright ams AG, Tobelbader Strasse 30, 8141 Premstaetten, Austria-Europe. Trademarks Registered. All rights reserved. The material herein may not be reproduced, adapted, merged, translated, stored, or used without the prior written consent of the copyright owner.

Devices sold by ams AG are covered by the warranty and patent indemnification provisions appearing in its General Terms of Trade. ams AG makes no warranty, express, statutory, implied, or by description regarding the information set forth herein. ams AG reserves the right to change specifications and prices at any time and without notice. Therefore, prior to designing this product into a system, it is necessary to check with ams AG for current information. This product is intended for use in commercial applications. Applications requiring extended temperature range, unusual environmental requirements, or high reliability applications, such as military, medical life-support or life-sustaining equipment are specifically not recommended without additional processing by ams AG for each application. This product is provided by ams AG "AS IS" and any express or implied warranties, including, but not limited to the implied warranties of merchantability and fitness for a particular purpose are disclaimed.

ams AG shall not be liable to recipient or any third party for any damages, including but not limited to personal injury, property damage, loss of profits, loss of use, interruption of business or indirect, special, incidental or consequential damages, of any kind, in connection with or arising out of the furnishing, performance or use of the technical data herein. No obligation or liability to recipient or any third party shall arise or flow out of ams AG rendering of technical or other services.

#### **RoHS Compliant & ams Green Statement**

**RoHS Compliant:** The term RoHS compliant means that ams AG products fully comply with current RoHS directives. Our semiconductor products do not contain any chemicals for all 6 substance categories plus additional 4 substance categories (per amendment EU 2015/863), including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, RoHS compliant products are suitable for use in specified lead-free processes.

ams Green (RoHS compliant and no Sb/Br/Cl): ams Green defines that in addition to RoHS compliance, our products are free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material) and do not contain Chlorine (Cl not exceed 0.1% by weight in homogeneous material).

**Important Information:** The information provided in this statement represents ams AG knowledge and belief as of the date that it is provided. ams AG bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. ams AG has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. ams AG and ams AG suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

Headquarters	Please visit our website at www.ams.com
ams AG	Buy our products or get free samples online at www.ams.com/Products
Tobelbader Strasse 30	Technical Support is available at www.ams.com/Technical-Support
8141 Premstaetten	Provide feedback about this document at www.ams.com/Document-Feedback
Austria, Europe	For sales offices, distributors and representatives go to www.ams.com/Contact
Tel: +43 (0) 3136 500 0	For further information and requests, e-mail us at ams_sales@ams.com