

Specific Lighting

Product Data Sheet

LTW-006DCG-5

Created Date: 11 / 30 / 2010 Revision: D, 06 / 12 / 2019



1. Description

The LTW (LiteOn White PLCC LED) is a revolutionary, energy efficient and ultra compact new light source, combining the lifetime and reliability advantages of Light Emitting Diodes with the brightness of conventional lighting. It gives you total design freedom and unmatched brightness, creating a new opportunities for solid state lighting to displace conventional lighting technologies..


1. Features

- Package in 12mm tape on 7" diameter reels.
- Compatible with automatic placement equipment.
- Compatible with infrared and vapor phase reflow solder process.
- EIA STD package.
- I.C. compatible.
- Meet green product and Pb-free(According to RoHS)

1.2. Applications

- Portable (flashlight, bicycle)
- Decorative/Entertainment
- Bollards/Security/Garden
- Cove/Undershelf/Task
- Traffic signaling/Beacons/ Rail crossing and Wayside
- Indoor/Outdoor Commercial and Residential Architectural
- Edge lit signs (Exit, point of sale)

2. Outline Dimensions



Part No.	Lens Color	Light Color
LTW-006DCG-5	Yellow	InGaN White

Notes:

- 1. All dimensions are in millimeters (inches).
- 2. Tolerance is ±0.1 mm (.004") unless otherwise noted.



3. Absolute Maximum Ratings at Ta=25 $^{\circ}$ C


Parameter	LTW-006DCG-5	Unit	
Power Dissipation	120	mW	
Peak Forward Current (1/10 Duty Cycle, 0.1ms Pulse Width)	100	mA	
DC Forward Current	30	mA	
Reverse Voltage	5	V	
Operating Temperature Range	-30°C to + 85°C		
Storage Temperature Range	-40°C to + 100°C		
Reflow Soldering Condition	260°C For 10 S	Seconds	

Notes:

Operating the LED (in an application) under reverse bias condition might result in damage or failure of the component

Suggest IR Reflow Condition:

R-Reflow Soldering Profile for lead free soldering (Acc. to J-STD-020D)





4. Electro-Optical Characteristics at Ta=25°C

Parameter	Symbol	Min.	Тур.	Max.	Unit	Test Condition
Luminous Intensity	IV	450		750	mcd	IF = 5mA Note 1, 2, 5
Viewing Angle	201/2		110		deg	Fig.6
	х		0.277			IF = 5mA
Chromaticity Coordinates	у		0.255			Note 3, 5 Fig.1
Forward Voltage	VF	2.45		3.15	V	IF = 5mA
ESD-Withstand Voltage	ESD	200			V	НВМ

Notes:

- 1. Luminous Intensity is measured with a light sensor and filter combination that approximates the CIE eye-response curve.
- 2. Lm classification code is marked on each packing bag.
- 3. The chromaticity coordinates (x, y) is derived from the 1931 CIE chromaticity diagram.
- 4. Caution in ESD:

Static Electricity and surge damages the LED. It is recommend to use a wrist band or anti-electrostatic glove when handling the LED. All devices, equipment and machinery must be properly grounded.

- 5. CAS140B is the test standard for the chromaticity coordinates (x, y) & IV.
- 6. The chromaticity coordinates (x, y) guarantee should be added +/- 0.007 tolerance.



5. Bin Code List

V _F Spec. Table						
V Din	Forward Voltage	(volts) at I _F = 5mA				
V _F Bin	Min.	Max.				
VY	2.45	2.55				
VZ	2.55	2.65				
V0	2.65	2.75				
V1	2.75	2.85				
V2	2.85	2.95				
V3	2.95	3.05				
V4	3.05	3.15				

Tolerance on each Forward Voltage bin is +/- 0.10 V


Luminous Intensity Spec. Table						
	Luminous Intensity	y (mcd) at IF = 5mA				
IV Bin	m	mcd				
	Min.	Max.				
S41	450	500				
S42	500	550				
S51	550	600				
S52	600	650				
S61	650	700				
S62	700	750				

Tolerance on each Luminous Intensity bin is +/- 10%




	Color bin limits at IF = 5mA										
	CIE 1931Chromaticity coordinates										
C12	х	0.265	0.270	0.270	0.265	B12	х	0.265	0.270	0.270	0.265
012	у	0.237	0.245	0.258	0.250	БΙΖ	у	0.224	0.232	0.245	0.237
C21	х	0.270	0.275	0.275	0.270	B21	х	0.270	0.275	0.275	0.270
021	у	0.245	0.253	0.266	0.258	D21	у	0.232	0.240	0.253	0.245
C22	Х	0.275	0.280	0.280	0.275	B22	Х	0.275	0.280	0.280	0.275
022	у	0.253	0.261	0.274	0.266	DZZ	у	0.240	0.248	0.261	0.253
C31	Х	0.280	0.285	0.285	0.280	B31	Х	0.280	0.285	0.285	0.280
031	у	0.261	0.269	0.282	0.274	DOT	у	0.248	0.256	0.269	0.261
C32	Х	0.285	0.290	0.290	0.285	B32	Х	0.285	0.290	0.290	0.285
032	у	0.269	0.277	0.290	0.282	532	у	0.256	0.264	0.277	0.269

Tolerance on each Hue (x, y) bin is +/- 0.01





6. Typical Electrical / Optical Characteristics Curves (25°C Ambient Temperature Unless Otherwise Noted)





7. User Guide

7.1 Cleaning

Do not use unspecified chemical liquid to clean LED they could harm the package.


If cleaning is necessary, immerse the LED in ethyl alcohol or isopropyl alcohol at normal temperature for less than one minute.

7.2 Recommend Printed Circuit Board Attachment Pad

Infrared / vapor phase
Reflow Soldering

1.5 2.1 1.5


7.3 Package Dimensions of Tape




Note: All dimensions are in mm.



7.4 Package Dimensions of Reel



Note: 01. The tolerance unless mentioned is ±0.1mm 02. The measured unit is "mm"



Notes:

- 1. Empty component pockets sealed with top cover tape.
- 2. 7 inch reel- maximum 2000 pieces per reel.
- 3. Minimum packing quantity is 500 pieces for remainders.
- 4. The maximum number of consecutive missing lamps is two.
- 5. In accordance with EIA-481-1-E1 specifications.



8. CAUTIONS

8.1 Application

The LEDs described here are intended to be used for ordinary electronic equipment (such as office equipment, communication equipment and household applications). Consult Liteon's Sales in advance for information on applications in which exceptional reliability is required, particularly when the failure or malfunction of the LEDs may directly jeopardize life or health (such as in aviation, transportation, traffic control equipment, medical and life support systems and safety devices).

8.2 Storage

This product is qualified as Moisture sensitive Level 3 per JEDEC J-STD-020 Precaution when handing this moisture sensitive product is important to ensure the reliability of the product.

The package is sealed:

The LEDs should be stored at 30°C or less and 90%RH or less. And the LEDs are limited to use within one year, while the LEDs is packed in moisture-proof package with the desiccants inside.

The package is opened:

The LEDs should be stored at 30°C or less and 60%RH or less. Moreover, the LEDs are limited to solder process within 168hrs. If the Humidity Indicator shows the pink color in 10% even higher or exceed the storage limiting time since opened, that we recommended to baking LEDs at 60°C at least 48hrs. To seal the remainder LEDs return to package, it's recommended to be with workable desiccants in original package.

8.3 Cleaning

Use alcohol-based cleaning solvents such as isopropyl alcohol to clean the LED if necessary.

8.4 Soldering

Recommended soldering conditions:


Reflow soldering		Soldering iron		
Pre-heat	120~150°C	Temperature	300°C Max.	
Pre-heat time	120 sec. Max.	Soldering time	3 sec. Max.	
Soldering Temp. Soldering time	260°C Max.		(one time only)	
	30 sec. Max.			




8.5 Drive Method

An LED is a current-operated device. In order to ensure intensity uniformity on multiple LEDs connected in parallel in an application, it is recommended that a current limiting resistor be incorporated in the drive circuit, in series with each LED as shown in Circuit A below.

Circuit model A







- (A) Recommended circuit.
- (B) The brightness of each LED might appear different due to the differences in the I-V characteristics of those LEDs.

8.6 ESD (Electrostatic Discharge)

Static Electricity or power surge will damage the LED.

Suggestions to prevent ESD damage:

- Use of a conductive wrist band or anti-Electrostatic glove when handling these LEDs.
- All devices, equipment, and machinery must be properly grounded.
- Work tables, storage racks, etc. should be properly grounded.
- Use ion blower to neutralize the static charge which might have built up on surface of the LED's plastic lens as a result of friction between LEDs during storage and handling.

ESD-damaged LEDs will exhibit abnormal characteristics such as high reverse leakage current, low forward voltage, or "no lightup" at low currents.

To verify for ESD damage, check for "lightup" and Vf of the suspect LEDs at low currents.

The Vf of "good" LEDs should be >2.0V@0.1mA for InGaN product



8.7 Reliability Test

Test Item	Test Condition	Reference Standard	Note	Number of Damaged
Resistance to Soldering Heat (Reflow Soldering)	Tsld=260°C, 10sec.	JEITA ED-4701 300 301	2 times	0/50
Solderability (Reflow Soldering)	Tsld=245±5°C, 3sec. (Lead Free Solder)	JEITA ED-4701 300 303	1 time Over 95%	0/50
Thermal Shock	-30°C ~ 85°C 30min. 30min.	JEITA ED-4701 300 307	100 cycles	0/50
Temperature Cycle	-40°C ~ 25°C ~ 100°C ~ 25°C 30min. 5min. 30min. 5min.	JEITA ED-4701 100 105	100 cycles	0/50
High Temperature Storage	Ta=100°C	JEITA ED-4701 200 201	1000 hrs.	0/50
Temperature Humidity Storage	Ta=60°C, RH=90%	JEITA ED-4701 100 103	1000 hrs.	0/50
Low Temperature Storage	Ta=-40°C	JEITA ED-4701 200 202	1000 hrs.	0/50
Steady State Operating Life Condition 1	Ta=25°C, IF=20mA		1000 hrs.	0/50
Steady State Operating Life Condition 2	Ta=25°C, IF=30mA		500 hrs.	0/50
Steady State Operating Life of High Temperature	Ta=85°C, IF=5mA		1000 hrs.	0/50
Steady State Operating Life of High Humidity Heat	60°C, RH=90% , IF=15mA		500 hrs.	0/50

Criteria for Judging the Damage

Item	Cumbal	Test Conditions	Criteria for	Judgment
item	Symbol	rest Conditions	Min.	Max.
Forward Voltage	VF	IF=20mA	-	U.S.L. × 1.1
Luminous Intensity	IV	IF=20mA	U.S.L. × 0.7	-



8.8 Others

The appearance and specifications of the product may be modified for improvement without prior notice.

8.9 Suggested Checking List

Training and Certification

- 1. Everyone working in a static-safe area is ESD-certified?
- 2. Training records kept and re-certification dates monitored?

Static-Safe Workstation & Work Areas

- 1. Static-safe workstation or work-Sreas have ESD signs?
- 2. All surfaces and objects at all static-safe workstation and within 1 ft measure less than 100V?
- 3. All ionizer activated, positioned towards the units?
- 4. Each work surface mats grounding is good?

Personnel Grounding

- 1. Every person (including visitors) handling ESD sensitive (ESDS) items wear wrist strap, heel strap or conductive shoes with conductive flooring?
- 2. If conductive footwear used, conductive flooring also present where operator stand or walk?
- 3. Garments, hairs or anything closer than 1 ft to ESD items measure less than 100V*?
- 4. Every wrist strap or heel strap/conductive shoes checked daily and result recorded for all DLs?
- 5. All wrist strap or heel strap checkers calibration up to date?

Note: *50V for Blue LED.

Device Handling

- 1. Every ESDS items identified by EIA-471 labels on item or packaging?
- 2. All ESDS items completely inside properly closed static-shielding containers when not at static-safe workstation?
- 3. No static charge generators (e.g. plastics) inside shielding containers with ESDS items?
- 4. All flexible conductive and dissipative package materials inspected before reuse or recycle?

Others

- 1. Audit result reported to entity ESD control coordinator?
- 2. Corrective action from previous audits completed?
- 3. Are audit records complete and on file?