



N=NUMBER OF CONTACTS



RECOMMENDED PCB LAYOUT



N = Number of poles  
 Dim A=Nx5.08  
 Dim B=(N-1)x5.08

	Dim A	Dim B
2-6p	±0.15	±0.10
7-12p	±0.20	±0.20
13-18p	±0.30	±0.25
19-24p	±0.40	±0.30

SIGN	DATE	DESCRIPTION	APPROVER
△	02/09'06	Part No. is changed.	Marvin
△	06/23'06	Touque standard is changed from 3.5 Lb-In to 2.6 Lb-In	Marvin
△	06/23'06	Added cULus logo	Marvin
△	04/03'10	Part No. is changed.	Tason

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Terminal body  
(metal housing): Brass(CuZn)
- Terminal screw: Steel Zinc plating "-" slot type
- Wire guard: Stainless steel
- Surface of solder tail: Tin plated
- Insulator (housing): Thermoplastic (UL94V-0)

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 15A
- Wire range:
- Solid wire(AWG): 14-22
- Stranded wire(AWG): 14-22
- △ Torque: 2.6Lb-In
- Screw: M2.6
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- △ Safety Approval: cULus

TC <sup>△</sup>xx 2 3 x x <sup>△</sup>xxxx G <sup>△</sup> <sup>△</sup>

POLES	COLOR	DIM C Length	000 0 Standard
02 02 CONTACTS	0 BLACK	0 4.4mm	Any special item by
03 03 CONTACTS	5 GREEN(RAL6018/T)	1 3.8mm	customer request,
...	6 BLUE	2 3.5mm	please contact sales
24 24 CONTACTS			department.

**ANYTEK**

**CUSTOMER COPY**

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		TC-5.08 Series 2-Interlock				
PART NO.		TCxx23xxxxxxG <sup>△</sup>		DWG NO.		8TC0603
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.	
		Tason	Tason			
		2010.04.03	2010.04.03			
				UNIT: mm		X. ±0.50
				SCALE: NONE		X.X ±0.30
		SHEET: 01/01		REV.: B		X.XX ±0.10
						X° ±1°