SLLS344 - OCTOBER 1999

- Flatlink Interface Utilizes Low Power Differential Signalling(LVDS)
- Suitable for Notebook Application
- **XGA** Resolution
- Six Bit System Interface
- **Support Mainstream Data and Gate Drivers**
- **Optional Configurable Pins**

- Low Voltage CMOS 3.3 V Technology
- 65 MHz Phase-Lock Input
- 100-pin TQFP Package for Compact LCD Module
- Tolerates 4 kV HBM ESD for LVDS Pins and 2 kV HBM for Others
- **Improved Jitter Tolerance**


### description

The SN75LVDS88 (LVDS panel timing controller) integrates a Flatlink signal interface with a TFT LCD timing controller. It resides in the LCD panel and provides interface between the graphic controller and a TFT LCD panel.

The SN75LVDS88 accepts host data through 3 pairs of inputs (18-bits) making up the LVDS bus, which is a low-EMI high-throughput interface. SN75LVDS88 then reformats the received image data into a specific data format and synchronous timing suitable for driving LCD panel column and row drivers. This device supports XGA resolution.

The SN75LVDS88 is easily configured by several selection terminals and is equipped with default timing specifications to support mainstream gate and source drivers on the market.

### block diagram





Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty Production processing does not necessarily include testing of all parameters.



Copyright © 1999, Texas Instruments Incorporated

#### pin assignment

MODE1 MODE0 DBS VSS VSS CSS GNDA GNDA GND1 NC CLKP A2P A2P GNDD SHTDN VDDD TEST1 A2M A1M AOM AOP ЯN A MODE2 1 75 TP1 C CPV C 2 D OPOL 74 3 73 🗅 VSS VSS 🗆 4 72 OB0(OR0) STV 5 71 OE1 OB1(OR1) 6 70 REV\_E 7 69 OB2(OR2) VDD [ 8 68 🛛 VSSIO REV\_O 67 OB3(OR3) 9 OE2 [ 10 66 🛛 OB4(OR4) TP2 🗆 11 65 VDDIO VS<u>SIO</u> □ CLK □ 12 64 OB5(OR5) 13 SN75LVDS88 OG0 63 VDDIO [ 14 62 TEST2 🗆 OG1 15 61 ER5(EB5) 🗅 OG2 16 60 VSSIO [ 🗅 VDDIO 17 59 ER4(EB4) 58 🗆 OG3 18 57 🗅 OG4 ER3(EB3) [ 19 VDDIO 20 56 ER2(EB2) [ 21 ER1(EB1) [ 22 VSSIO [ 23 55 🗋 OG5 54 OR0(OB0) 53 VDDIO ER0(EB0) 24 52 OR1(OB1) EG5 🗆 25 51 OR2(OB2) OR5(OB3) [ VSSIO [ OR4(OB4) [ OR3(OB3) [ 

TQFP PACKAGE (TOP VIEW)



### **Terminal Functions**

TERMIN	AL		DECODIDEION				
NAME	NO.	1/0	DESCRIPTION				
A0M/A0P	81,82	1	Flatlink 1 <sup>st</sup> data pair				
A1M/A1P	83, 84	1	Flatlink 2 <sup>nd</sup> data pair				
A2M/A2P	85, 86	1	Flatlink 3 <sup>rd</sup> data pair				
CLK	44	0	) bus clock				
CLK	13	0	CD bus clock (180 degree out of phase)				
CLKM/CLKP	87, 88	1	Flatlink clock pair				
CPV	3	0	Gate driver clock				
DBS	97	1	Data bus sequence				
EPOL	42	0	Even RGB data stream polarity indicator				
ER0ER5	24,22,21	0	Even red (blue) data bus, controlled by DBS Pin, 0 = red, 1 = blue				
(EB0)(EB5)	19,18,16						
(ER0)(ER5) EB0EB5	41,39,38 36,35,33	0	Even blue (red) data bus, controlled by DBS Pin, 0 = blue, 1 = red				
GND1	91	Р	PLL ground for LVDS				
MODE0	98	1	Default timing selection pin 0				
MODE1	99	1	Default timing selection pin 1				
MODE2	1	1	Default timing selection pin 2				
NC	76, 77, 89, 90	NC	NC terminals <sup>†</sup>				
OE1, OE2	6, 10	0	Gate driver output enable				
OG0OG5	63,61,60 58,57,55	0	Odd green data bus				
OPOL	74	0	Odd RGB data stream polarity indicator				
OR0OR5 (OB0)(OB5)	54,52,51 50,49,47	0	Odd red (blue) data bus, controlled by DBS Pin, 0 = red, 1 = blue				
(OR0)(OR5) OB0OB5	72,70,69 67,66,64	0	Odd blue (red) data bus, controlled by DBS Pin, 0 = blue, 1 = red				
POLEN	95	1	Output data polarity control enable /disable				
REV_E	7	0	CD line/dot inversion control signal				
REV_O	9	0	CD line/dot inversion control signal (180 degree of phase)				
RSTZ	93	1	Reset, active low				
SHTDN	79	I	System shutdown control, active low				
SP	46	0	Data bus starting pulse				
STV	5	0	Gate driver starting pulse				
TEST1, TEST2	100, 15	1	Test points <sup>†</sup>				
TP1, TP2	2, 11	0	CD output control signal				
VDDA	94	Р	PLL power for LVDS				
GNDA	92	Р	Analog ground for LVDS				
VDDD	78	Р	Digital power supply for LVDS				
GNDD	80	Р	Digital power ground for LVDS				
VDD	8,71,75	Р	Digital power				
VSS	4,73,96	Р	Digital ground				
VDDIO		Р	I/O power				
VSSIO		Р	I/O ground				

<sup>†</sup> Terminals must be connected to ground.

SLLS344 – OCTOBER 1999

### options

#### output control

	PIN NO.	INTERNAL C	ONNECTION	DESCRIPTION		
FININAME		REQUIRED	SUGGESTED	DESCRIPTION		
MODE0 MODE1 MODE2	98 99 1	Pull-up Pull-up Pull-down		Default timing selection pin 0 Default timing selection pin 1 Default timing selection pin 2		
POLEN		Pull-down		0 = Output data reverse disable 1 = Output data reverse enable		
DBS	97	Pull-down		Data bus sequence 0 = normal (RGB) 1 = reverse (BGR)		

NOTE: DBS and POLEN functions must not be enabled together. The option pins must be connected to ground or VDD.

### absolute maximum ratings over operating free-air temperature (unless otherwise noted)<sup>†</sup>

Supply voltage range, V <sub>CC</sub> ‡	
Voltage range at any terminal	
Continuous power dissipation	See Dissipation Rating Table
Storage temperature range, T <sub>stg</sub>	
Electrostatic discharge: Class 3 A	
Class 2 B	
Lead temperature 1,6 mm (1/16 inch) from case for 10 seconds	

<sup>†</sup> Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

<sup>‡</sup> All voltage values are with respect to the GND terminals unless otherwise noted.

#### **DISSIPATION RATING TABLE**

PACKAGE	T <sub>A</sub> ≤ 25°C	OPERATING FACTOR <sup>§</sup>	T <sub>A</sub> = 70°C
	POWER RATING	ABOVE T <sub>A</sub> = 25°C	POWER RATING
PFD	1.548 W	12 mW	1.012 W

§ This is the inverse of the junction-to-ambient thermal resistance when board-mounted and with no air flow.



### recommended operating conditions

		MIN	NOM	MAX	UNIT
Supply voltage, V <sub>CC</sub>	3	3.3	3.6	V	
High-level input voltage, VIH	SHTDN	2			V
Low-level input voltage, VIL	SHIDN			0.8	v
Magnitude of differential input voltage, $ V_{ID} $		0.1		0.6	V
Common–mode input voltage, VIC		$\frac{ V_{ID} }{2}$		$2.4 - \frac{ V_{ID} }{2}$	V

### electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

	PARAMETER	TEST CONDITIONS	MIN	TYP†	MAX	UNIT
VIT+	Positive-going differential input voltage threshold				100	mV
V <sub>IT</sub>	Negative-going differential input voltage threshold		-100			mV
		Disabled, all inputs to ground			360	μA
I <sub>CC</sub> Quiesc		Enabled, AnP at 1 V and AnM at 1.4 V, $t_{\rm C}$ = 15.38 ns		80		
	Quiescent current (average)	Enabled, $C_L = 8 \text{ pF}$ , Grayscale pattern , $t_C = 15.38 \text{ ns}$		100		mA
		Enabled, $C_L = 8 \text{ pF}$ , Worst-case pattern , $t_C = 15.38 \text{ ns}$		120		
IIН	High-level input current (SHTDN)	VIH = VCC			±20	μA
Ι <sub>Ι</sub>	Low-level input current (SHTDN)	$V_{IL} = 0 V$			±20	μΑ
I <sub>IN</sub>	Input current (A inputs)	$0 V \leq V_{I} \leq 2.4 V$			±20	μA
IOZ	High-impendance output current	$V_{O} = 0 V \text{ or } V_{CC}$			±10	μΑ

<sup>†</sup> All typical values are at V<sub>CC</sub> = 3.3 V, T<sub>A</sub> = 25°C. <sup>‡</sup> The algebraic convention, in which the less-positive (more-negative) limit is designated minimum, is used in this data sheet for the negative-going input voltage threshold only.

#### timing requirements

		MIN	TYP MAX	UNIT
t <sub>c</sub> §	Input clock period	14.7	31.25	ns
t <sub>su</sub> /t <sub>h</sub>	Input set up or hold time	550		ps

 $t_c$  is defined as the mean duration of a minimum of 32,000 clock periods.

### output buffer rating

	MIN	TYP	MAX	UNIT
STV, SP		4		mA
CLK, CLK		12		mA
Data bus and remaining outputs		8		mA



SLLS344 – OCTOBER 1999

### switching characteristics

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
<sup>t</sup> dr1	Input clock rising to output clock rising delay	$C_{1} = 100 \text{ pc}$	10		40	ns
<sup>t</sup> df1	Input clock rising to output clock falling delay	$-C_{L} = 100 \text{ pF}$	10		40	ns
<sup>t</sup> su1	Data set up time, E/O RGB to CLK↑	0. 400 - 5	10		20	ns
<sup>t</sup> h1	Data hold time, CLK↑ to E/O RGB	- C <sub>L</sub> = 100 pF	10		20	ns
<sup>t</sup> (RSKM)	Receiver input skew margin, See Note 4	$t_{C}$ = 15.38 ns (±0.2%), Input clock jitter  < 50 ps, See Note 5	550	700		ps
t <sub>en</sub>	Enable time, SHTDN to phase lock			1		ms
<sup>t</sup> dis	Disable time, SHTDN to off state			250		ns
<sup>t</sup> su2	SP setup time	0 15 -5	10		20	ns
<sup>t</sup> h2	SP pulse hold time	C <sub>sp</sub> = 15 pF	10		20	ns

NOTES: 1. tRSKM is the timing margin available to allocate to the transmitter and interconnection skews and clock jitter. The value of this

parameter at clock periods other than 15.38 ns can be calculated from  $t_{RSKM} = \frac{t_c}{14}$ -300 ps.

2. |Input clock jitter | is the magnitude of the change in the input clock period.




Figure 1. Output Setup and Hold Time



**REFERENCE TIMING DIAGRAM** 




Figure 2. Typical Output Waveform



## PARAMETER MEASUREMENT INFORMATION

### functional description

### Flatlink

The core of the Flatlink is TIs original 86A LVDS receiver which has three data channels for the 18-bit color plus one clock channel.

#### data alignment

The data alignment block supports dual bus dual port column driver configuration. When interfacing a 2-port column driver, the controller arranges pixels in odd and even order, then distributes them to odd and even buses and each connects to either of the driver ports. Under this setup, the controller outputs one clock, one or two data polarities (depends on driver), and one inverse ( support line inversion) signal to the drivers.

### output formatting

The output formatting provides several functions to reduce EMI, noise, and timing delay arrangement. These functions are controllable through some optional pins. See the registers and options section for reference.

- Reverse Polarity Generation
   When enable this function generates polarity indication signals. This occurs when the number of transitions in the output data bus exceeds 18-bits compared to the previous output under normal polarity. The polarity signal will be active and the output will be the opposite polarity to reduce transition
- Line Inversion
   When enabled, the REV\_O and REV\_E terminals will output the same line inversion control signals but in opposite polaritys.

### timing control

- Source Shifted Clock(SSC)
   The master data clock could be arranged to have an intentional phase delay relative to the output data, which helps the system engineer tune the clock to latch the data correctly regardless of the characteristics presented by the PCB and the layout.
- Horizontal Starting pulses ESP and OSP terminals are used as the horizontal starting pulses outputs pins. Their output are one HCLK period ahead of the RGB data stream
- Horizontal Clock ECLK and OCLK terminals are responsible for the clock pulses, based on the XGA resolution when its frequency is at 32.5 MHz.
- CD Data Latch Pulse TP1 and TP2 provide the column driver input latch and output enable signals.
- Gate Driver Clock The CPV terminal output the clock pulses to the gate drivers as the horizontal sync timing in its CRT counter part.
- Gate Driver Starting Pulse The vertical starting pulse automatically generates at the start of every frame.
- Gate Driver Output Enable The OE1 and OE2 terminals provide the gate output enabale signals.



## PARAMETER MEASUREMENT INFORMATION


### functional description (continued)

#### vertical/horizontal reference generator

This block provides vertical and horizontal reference points for timing control. Vsync, Hsync, and ENAB signals along with the auto detection function determine when the video from the host is valid.


#### power-up procedure

Due to the uncertainty of registers and counters in the driver, SN75LVDS88 combines the input from both reset and Vsync to blank the output and simultaneously resets the content of drivers (see Figure 3).



### Figure 3. Reset Waveform

It is recommended that the following circuit be used to ensure the device is reset for more than 5 ms after power up.





ORGB

ERGB







Figure 5. Data Output Format



SLLS344 – OCTOBER 1999

**MECHANICAL DATA** 



NOTES: A. All linear dimensions are in millimeters.

- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion.
- D. The package thermal performance may be enhanced by attaching an external heatsink to the thermal pad. This pad is electrically and thermally connected to the backside of the die and possibly selected leads.
- E. Falls within JEDEC MS-026

PowerPAD is a trademark of Texas Instruments Incorporated.



### PACKAGING INFORMATION

Orderable Device	Status <sup>(1)</sup>	Package Type	Package Drawing	Pins Package Qty	Eco Plan <sup>(2)</sup>	Lead/Ball Finish	MSL Peak Temp <sup>(3)</sup>
SN75LVDS88PFD	OBSOLETE	HTQFP	PFD	100	TBD	Call TI	Call TI

<sup>(1)</sup> The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS) or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details. TBD: The Pb-Free/Green conversion plan has not been defined.

**Pb-Free (RoHS):** TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

<sup>(3)</sup> MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

**Important Information and Disclaimer:**The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

#### **IMPORTANT NOTICE**

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Amplifiers	amplifier.ti.com	Audio	www.ti.com/audio
Data Converters	dataconverter.ti.com	Automotive	www.ti.com/automotive
DSP	dsp.ti.com	Broadband	www.ti.com/broadband
Interface	interface.ti.com	Digital Control	www.ti.com/digitalcontrol
Logic	logic.ti.com	Military	www.ti.com/military
Power Mgmt	power.ti.com	Optical Networking	www.ti.com/opticalnetwork
Microcontrollers	microcontroller.ti.com	Security	www.ti.com/security
		Telephony	www.ti.com/telephony
		Video & Imaging	www.ti.com/video
		Wireless	www.ti.com/wireless

Mailing Address:

Texas Instruments

Post Office Box 655303 Dallas, Texas 75265

Copyright © 2005, Texas Instruments Incorporated