
Data sheet | Item number: 890-254 Plug; 4-pole; 1,50 mm<sup>2</sup>; gray www.wago.com/890-254





Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com



Item description

### Male connector/plug WINSTA® MINI 4-pole

Use effective pluggable connections instead of laborious screw connections: With the *WINSTA®* MINI male connector/plug with protection against mismating. On PCBs, in control cabinets or for connecting lights – pluggable installation connectors from WAGO allow you to establish connections according to various requirements in no time flat.

The color coding and mechanical coding of the pluggable installation connector ensure error-free installation of the individual components – including protection against mismating. Pluggable installation connectors with B coding from the *WINSTA®* MINI line are available in pink, light grey, or grey, allowing you to distinguish different circuits, for example for light, pumps or, sun blinds. Your own pole marking is possible as well. Especially where space is tight, our smallest pluggable connection system, *WINSTA®* MINI, consistently displays its advantages. It is very compact, and, with Push-in CAGE CLAMP® spring pressure connection technology, it also can be installed quickly, since the connection is low-maintenance and requires no screw connections.

### WINSTA® MINI solutions for your electrical installation – protected against mismating and maintenance-free

The WINSTA® Pluggable Connection System allows pluggable electrical installation. This significantly reduces the need for servicing and lowers costs. Choose durability and quality – the *WINSTA®* MINI pluggable installation connector with marking from WAGO makes the installation of electrical components noticeably easier.

- effective protection against mismating
- easy tool-free operation, a wide range of coding options
- with B coding for use in automation of processes, such as lighting technology, among other examples
- exact dimensions
- quick replacement of defective units during ongoing operation

# Data

### Notes

Other versions (or variants) can be requested from WAGO Sales or	Other pole markings
configured at https://configurator.wago.com/.	

### Electrical data

Note on contact resistance	approx. 1 m $\Omega$ of contact resistance	
	approx. 0.25 m $\Omega$ contact transition plug/socket	

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com

www.wago.com/890-254



Ratings per	IEC/EN 60664-1
Nominal voltage (III/3)	400 V
Rated surge voltage (III/3)	6 kV
Rated current	16 A
Note on rated current 1	13 A for 3-pole load 10 A for 4-pole load
Legend (ratings)	(III / 3) ≙ Overvoltage category III / Pollution degree 3
Hinweis für den amerikanischen Markt	Application note for the U.S. market (USR): Some versions may also be used for current interruption in accordance with the UL certificate in select applications with currents below 5 A and voltages up to 600 V. For further information, please contact your local sales office.
Rated voltage UL 1977	600 V
Rated current UL 1977	12 A

### **Connection data**

Total number of connection points	4
Total number of potentials	4
Connection technology	Push-in CAGE CLAMP <sup>®</sup>
Actuation type	Operating tool Push-in
Nominal cross-section	1.5 mm²
Solid conductor	0.25 1.5 mm² / 22 16 AWG
Solid conductor; push-in termination	0.75 1.5 mm² / 20 16 AWG
Stranded conductor	0.25 1 mm² / 22 18 AWG
Fine-stranded conductor	0.25 1.5 mm² / 22 16 AWG
Fine-stranded conductor; with insulated ferrule	0.25 0.75 mm² / 22 20 AWG
Fine-stranded conductor; with uninsulated ferrule	0.25 0.75 mm² / 22 20 AWG
Fine-stranded conductor; with ferrule; push-in termination	0.75 mm² / 20 AWG
Strip length	9 mm / 0.35 inch
Pole No.	4
Conductor entry direction to mating direction	0°

### Physical data

Pin spacing	4.4 mm / 0.173 inch
Width	19.2 mm / 0.756 inch
Height	11.7 mm / 0.461 inch
Depth	34.1 mm / 1.343 inch

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KGDo you have any questions about our products?Hansastr. 27We are always happy to take your call at +49 (571) 887-44222.32423 MindenPhone: +49571 887-0 | Fax: +49571 887-169Email: info.de@wago.com | Web: www.wago.comEmail: info.de@wago.com | Web: www.wago.com



### Mechanical data

Application	Measurement and regulation technology
Coding	В
Marking	1234
Potentialkennzeichnung	1234
Mating force of a plug-in connection	approx. 20 70 N (depending on pole number)
Retention force of a plug-in connection	Locked: > 80 N
Unmating force of a plug-in connection	Unlocked: approx. 20 70 N (depending on pole number)
Number of mating cycles	200, without resistive load
Protection class	IP20; IP40 when mated with strain relief housing

### **Plug-in connection**

Contact type (pluggable connector)	Male connector/plug
Connector (connection type)	for conductor
Mismating protection	Yes
Note on mismating protection	All WINSTA <sup>®</sup> components are 100% protected against mismating when: a.) plugging different numbers of poles b.) plugging while rotated 180 c.) plugging while laterally staggered d.) plugging one pole
Locking lever	Can be retrofitted
Locking of plug-in connection	locking lever
Hinweis zur Verriegelung	All connectors for mounted installations (snap-in versions for lighting fixtures or devices, all types of PCB and distribution connectors) are factory-equipped with locking levers to ensure plugs and sockets are securely locked. Additional locking levers are only required for flying leads (plug/socket).

### Material data

Color	gray
Insulation material	Polyamide (PA66)
Clamping spring material	Chrome nickel spring steel (CrNi)
Contact material	Copper or copper alloy (surface-treated)
Fire load	0.099 MJ
Weight	4.6 g

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com



### **Environmental requirements**

Processing temperature	-5 +40 °C
Continuous operating temperature	-35 +85 ℃
Note on continuous operating temperature	Insulating parts for temperatures ≤ 105 °C

### **Commercial data**

Product Group	20 (WINSTA)
PU (SPU)	50 Stück
Packaging type	box
Country of origin	PL
GTIN	4055143523660
Customs tariff number	85366990990

### Approvals / Certificates

### **Country specific Approvals**

Logo	Approval	Additional Approval Text	Certificate name
	CB DEKRA Certification B.V.	IEC 61984	NL-64351
KENA	CB DEKRA Certification B.V.	EN 61984	71-112993
KEMA	KEMA/KEUR DEKRA Certification B.V.	EN 60320	2148952.04

#### Ship Approvals

Logo	Approval	Additional Approval Text	Certificate name
	DNV GL Det Norske Veritas, Germanischer Lloyd	-	TAE00001Z6
THE AMELIAL SCHOOL	<b>LR</b> Lloyds Register	EN 61535	08/20047 (E2)

#### **UL-Approvals**

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KGDo you have any questions about our products?Hansastr. 27We are always happy to take your call at +49 (571) 887-44222.32423 MindenPhone: +49571 887-0 | Fax: +49571 887-169Email: info.de@wago.com | Web: www.wago.comUse a state of the state of t

www.wago.com/890-254



Logo	Approval	Additional Approval Text	Certificate name
81	<b>cURus</b> Underwriters Laboratories Inc.	UL 1977	E45171



# Counterpart

<b>Item no.890-1631</b> T-distribution connector; 4-pole; Cod. B; 1 input; 2 outputs; 2 locking levers; gray	www.wago.com/890-1631
 Item no.890-1681 h-distribution connector; 4-pole; Cod. B; 1 input; 2 outputs; outputs on one side; 2 locking levers; gray	www.wago.com/890-1681
 <b>Item no.890-1731</b> T-distribution connector; 4-pole; Cod. B; 1 input; 2 outputs; 3 locking levers; for flying leads; gray	www.wago.com/890-1731
 Item no.890-1734 3-way distribution connector; 4-pole; Cod. B; 1 input; 3 outputs; gray	www.wago.com/890-1734
Item no.890-1781 h-distribution connector; 4-pole; Cod. B; 1 input; 2 outputs; outputs on one side; 3 locking levers; for flying leads; gray	www.wago.com/890-1781
 Item no.890-244 Socket; 4-pole; Cod. B; 1,50 mm²; gray	www.wago.com/890-244
 <b>Item no.890-744</b> Snap-in socket; 4-pole; Cod. B; 1,50 mm²; gray	www.wago.com/890-744
 <b>Item no.890-844</b> Socket for PCBs; straight; 4-pole; Cod. B; gray	www.wago.com/890-844
 <b>Item no.890-844/011-000</b> Socket for PCBs; angled; 4-pole; Cod. B; gray	www.wago.com/890-844 /011-000
<b>Item no.891-8994/005-103</b> pre-assembled interconnecting cable; Eca; Socket/plug; 4-pole; Cod. B; Control cable 4 x 1.0 mm <sup>2</sup> ; 1 m; 1,00 mm <sup>2</sup> ; gray	www.wago.com/891-8994 /005-103
<b>Item no.891-8994/105-103</b> pre-assembled connecting cable; Eca; Socket/open-ended; 4-pole; Cod. B; Control cable 4 x 1.0 mm <sup>2</sup> ; 1 m; 1,00 mm <sup>2</sup> ; gray	www.wago.com/891-8994 /105-103

# **Required accessories**

Strain relief

ltem no.: 890-504	www.wago.com/890-504	
Strain relief housing; 4-pole; with locking clip; for 1 cable; 6.5 … 10.5 mm; 45 mm; black	www.wago.com/890-504	
Item no.: 890-514		
Strain relief housing; 4-pole; with locking clip; for 1 cable; 6.5 10.5 mm; 45 mm; white	www.wago.com/890-51	

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com

www.wago.com/890-254



www.wago.com/897-2003

Locking	device
---------	--------

www.wago.com/890-111
/000 404
www.wago.com/890-101
www.wago.com/890-121
www.wago.com/890-131

### **Optional accessories**

#### Cover

#### Other

	1	-	
1		1	

# Item no.: 897-2003

Protective cap; Type2; for sockets and plugs; PVC; red

#### Tool

Operat	ting tool	
/	Item no.: 210-719	www.wago.com/210-719
	Operating tool; Blade: 2.5 x 0.4 mm; with a partially insulated shaft	www.wago.com/210-719

# Downloads

## Documentation

### **Bid Text**

890-254 doc - Datei	Jun 8, 2015	doc 24.1 kB	Download
890-254 X81 - Datei	Feb 19, 2019	xml 3.0 kB	Download

### CAD/CAE-Data

### CAE data

WSCAD Universe 890-254	URL	Download
ZUKEN Portal 890-254	URL	Download

Subject to changes. Please also observe the further product documentation!


WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com




CAD data		
2D/3D Models 890-254	URL	Download
Environmental Product Compliance		
Compliance Search		
Environmental Product Compliance 890-254	URL	Download
Plug; 4-pole; 1,50 mm²; gray		

### Installation Notes

**Conductor termination** 






1. Strip length, outer insulation = 30 mm (2-pole), 37 mm (3-pole), 45 mm (4- and 5-pole)

2. Strip length = 9 mm

3. Extended ground conductor = 8 mm

To terminate fine-stranded conductors, open the clamping unit via screwdriver – 2.5 mm blade width – and insert a stripped conductor until it hits the backstop. Terminate solid conductors by simply pushing them in.



To terminate fine-stranded conductors, open clamping units via operating tool (890-382) and insert stripped conductors until they hit backstop.


Terminate solid conductors by simply pushing them in.

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com

www.wago.com/890-254






To terminate fine-stranded conductors, open clamping units via operating tool (890-383) and insert stripped conductors until they hit backstop.

Terminate solid conductors by simply pushing them in.

### Installation







Push down strain relief clamp by hand.



Push down strain relief clamp with 2.5 mm screwdriver alternately on both sides.



Latch the top of the strain relief housing.

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com





The printed marking of the connector is clearly visible in the openings of the strain relief housing.

#### **Mismating protection**



B-coded connectors (shown in gray) not only

differ in color, but also in their design, making them incompatible with other coded

connectors.

B-coded connectors with different colors can be plugged together.

### Important note:

Different colors and/or pole markings are used for circuit identification. Only connectors of the same color and same pole marking must be plugged together.

## **Product family**

### WINSTA® MINI

Show all products from the family

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com