# 1N4148WSFL-G

**Vishay Semiconductors** 

www.vishay.com

# **Small Signal Fast Switching Diode**

**FEATURES** 

Silicon epitaxial planar diode

www.vishay.com/doc?99912


• Base P/N-G3 - green, commercial grade

For definitions of compliance please see

• Fast switching diodes

• Material categorization:





2 = Anode

22611

### **MARKING** (example only)



22610

Bar = cathode marking XY = type code

### MECHANICAL DATA

Case: SOD-323 FL

Weight: approx. 4.5 mg

Packaging codes/options:

GS08/3K per 7" reel (8 mm tape), 18K/box

PARTS TABLE					
PART	ORDERING CODE	TYPE MARKING	INTERNAL CONSTRUCTION	REMARKS	
1N4148WSFL-G	1N4148WSFL-G3-08	AH	Single diode	Tape and reel	

<b>ABSOLUTE MAXIMUM RATINGS</b> (T <sub>amb</sub> = 25 °C, unless otherwise specified)					
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT	
Reverse voltage		V <sub>R</sub>	75	V	
Repetitive peak reverse voltage		V <sub>RRM</sub>	100		
Average rectified current half wave rectification with resistive load <sup>(1)</sup>	f ≥ 50 Hz	f ≥ 50 Hz I <sub>F(AV)</sub> 15		mA	
Surge forward current	t < 1 s and $T_j = 25 \text{ °C}$	I <sub>FSM</sub>	350		
Power dissipation <sup>(1)</sup>		P <sub>tot</sub>	250	mW	

<b>THERMAL CHARACTERISTICS</b> (T <sub>amb</sub> = 25 °C, unless otherwise specified)					
PARAMETER	TEST CONDITION	SYMBOL	YMBOL VALUE		
Thermal resistance junction to ambient air <sup>(1)</sup>		R <sub>thJA</sub>	500	K/W	
Junction temperature		Tj	150		
Storage temperature range		T <sub>stg</sub>	- 65 to + 150	°C	
Operating temperature range		T <sub>op</sub>	- 55 to + 150		

#### Note

<sup>(1)</sup> Device mounted on FR-4 PCB, landing pad according to footprint recommendation in datasheet drawing

Rev. 1.0, 24-Oct-13

1



RoHS

COMPLIANT

HALOGEN

GREEN (5-2008)



www.vishay.com

## Vishay Semiconductors

<b>ELECTRICAL CHARACTERISTICS</b> (T <sub>amb</sub> = 25 °C, unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Forward voltage	I <sub>F</sub> = 10 mA	V <sub>F</sub>			1000	mV
	I <sub>F</sub> = 100 mA	V <sub>F</sub>			1200	
Leakage current	V <sub>R</sub> = 20 V	I <sub>R</sub>			25	nA
	V <sub>R</sub> = 75 V	I <sub>R</sub>			5	μA
	V <sub>R</sub> = 100 V	I <sub>R</sub>			100	
	$V_{R} = 20 \text{ V}, \text{ T}_{j} = 150 ^{\circ}\text{C}$	I <sub>R</sub>			50	
Diode capacitance	$V_F = V_R = 0 V$	CD			4	pF
Reverse recovery time	$I_F = 10 \text{ mA}, i_R = 1 \text{ mA}, V_R = 6 \text{ V}, \\ R_L = 100 \ \Omega$	t <sub>rr</sub>			4	ns

### **TYPICAL CHARACTERISTICS** (T<sub>amb</sub> = 25 °C, unless otherwise specified)




Fig. 1 - Forward Characteristics




Fig. 2 - Dynamic Forward Resistance vs. Forward Current




Fig. 3 - Admissible Power Dissipation vs. Ambient Temperature




Fig. 4 - Relative Capacitance vs. Reverse Voltage

Rev. 1.0, 24-Oct-13

2

Document Number: 85886

For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



## Vishay Semiconductors






Fig. 5 - Leakage Current vs. Junction Temperature





Fig. 6 - Admissible Repetitive Peak Forward Current vs. Pulse Duration




Vishay Semiconductors

### PACKAGE DIMENSIONS in millimeters (inches): SOD-323FL



foot print recommendation for reflow soldering:



Document no.:S8-V-3910.04-001 (4) Created - Date: 07.Feb. 2013 22699



Vishay

# Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.