Harvatek Surface Mount Photo Diode Data Sheet B17M1PD--H9B000114U1930

Official Product	HT Part No. B17M1PDH9B000114U1930 Customer Part No.			et No.
Tentative Product	*****	****		-
Specifications are subject advance notice. Proprieta rights reserved.	05/27/2019	Version 1.0	Page 1/14	

DISCLAIMER	3
LIFE SUPPORT POLICY	3
PRODUCT SPECIFICATIONS	4
ATTENTION: ELECTROSTATIC DISCHARGE (ESD) PROTECTION	4
LABEL SPECIFICATIONS	5
ELECTRO-OPTICAL CHARACTERISTICS	6
PACKAGE OUTLINE DIMENSION AND RECOMMENDED SOLDERING PATTERN FOR REFLOW Soldering Characteristics of B17M1PD	
PACKAGING	
TAPE DIMENSION REEL DIMENSION PACKING DRY PACK BAKING PRECAUTIONS	11 11 12 12
REFLOW SOLDERING	13
REWORKING CLEANING CAUTIONS OF PICK AND PLACE REVISE HISTORY	13 14

Official Product	HT Part No. B17M1PDH9B000114U1930	Customer Part No.	Data Sheet No.	
Tentative Product	*****	*****		-
Specifications are subje advance notice. Proprieta rights reserved.	05/27/2019	Version 1.0	Page 2/14	

DISCLAIMER

HARVATEK reserves the right to make changes without further notice to any products herein to improve reliability, function or design. HARVATEK does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights, nor the rights of others.

Life Support Policy

HARVATEK's products are not authorized for use as critical components in life support devices or systems without the express written approval of the President of HARVATEK or HARVATEK INTERNATIONAL. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.

2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Official Product HT Part No. B17M1PDH9B000114U1930		Customer Part No.	Data She	et No.
Tentative Product	*****	****		-
Specifications are subje advance notice. Proprieta rights reserved.	05/27/2019	Version 1.0	Page 3/14	

Product Specifications

ltem	Specification	Material	Quantity
Spectral Bandwidth	700nm~1100nm		
λ _D	@ V _R =5V / T _S = 25°C		
Peak Sensitivity	940nm		
λ _P	@ V _R =5V / T _S = 25°C		
Collector Light Current	0.5~3.0 uA		
Ic	@Ee = 1mW/cm ² ; λ_P =940nm, V _R =5V		
Resin	Black	Ероху	
Carrier tape	EIA 481-1A specs	Conductive black tape	
Reel	EIA 481-1A specs	Conductive black	
Label	HT standard	Paper	
Packing bag	220x240mm	Aluminum laminated bag/ no-zipper	One reel per bag
Carton	HT standard	Paper	Non-specified
Other and			

Others:

Each immediate box consists of 5 reels. The 5 reels may not necessarily have the same lot number or the same bin

combinations of Iv, CIE and Vf. Each reel has a label identifying its specification; the immediate box consists of a product label as well.

Note : This is shipped test conditions

%Remarks: This product should be operated in forward bias. If a reverse voltage is continuously applied to the product,

such operation can cause migration resulting in LED damage.

ATTENTION: Electrostatic Discharge (ESD) protection




The symbol to the left denotes that ESD precaution is needed. ESD protection for GaP and AlGaAs based chips and Silicon semiconductor is necessary even though they are relatively safe in the presence of low static-electric discharge. Parts built with AlInGaP, GaN, or/and InGaN based chips are **STATIC SENSITIVE**

devices. ESD precaution must be taken during design and assembly.

If manual work or processing is needed, please ensure the device is adequately protected from ESD during the process.


Official Product HT Part No. B17M1PDH9B000114U1930	Customer Part No.	Data Sheet No.	
Tentative Product ***********	****		•
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.	05/27/2019	Version 1.0	Page 4/14

Label Specifications



■Harvatek P/N:





Lot No.:

1	2	3	4	5	6	7	8	9	10
E	1	Α	1	Α	2	2	L	1	2
Cod	e 1 2	Code 3	Code 4	Code 5	Code 6	Code 7	Code 8	Code 9	Code 10
		Mfg. Year	Mfg. Month	Mfg. Date	Consecuti	ve number	Special code		e
		2010-A		1:A					
		2011-B		2:B					
		2012-C	1:Jan.	3:C					
			2:Feb.						
(atomal Ta	anine Carda	2018-I/J		26:Z	01	77		000~ZZZ	
internal i ra	acing Code	2019-K	A:Oct.	27:7	01-	-ZZ		000~222	
			B:Nov.	28:8					
		2022-N	C:Dec.	29:9					
		2023-P	10.0000000000	30:3					
		200		31:4					

Official Product HT Part No. B17M1PDH9B000114U1930		Customer Part No.	Data Sheet No.	
Tentative Product	*****	****		-
Specifications are subje advance notice. Proprieta rights reserved.	05/27/2019	Version 1.0	Page 5/14	

Absolute Maximum Rating at $25^\circ\!\!\mathbb{C}$

Symbol	Parameters	Ratings	Units	Notes
Vr	Reverse Voltage	32	V	
T _{opr}	Operating Temperature	-40 ~ +85	°C	
T _{stg}	Storage Temperature	-40 ~ +100	°C	
T _{sol}	Soldering Temperature	260	°C	1
Pto	Total Power Dissipation	150	mW	

Notes:

1. Soldering time \leq 5 seconds.

Electro-Optical Characteristics

Symbol	Parameters	Test conditions	Min	Тур	Max	Units	Notes
$\lambda_{0.5}$	Range Of Spectral Bandwidth		700	-	1100	nm	
λ_{P}	Wavelength Of Peak Sensitivity		-	940	-	nm	
Vbr	Reverse Breakdown Voltage	I _R =100µA E _e =0mW/cm²	32	-	-	V	
Voc	Open-Circuit Voltage	λ _P =940nm	-	0.42	-	V	
lsc	Short-Circuit Current	E _e =1mW/cm ²	-	8.5	-	uA	
lo	Collector Dark Current	V _R =10V E _e =0mW/cm²	-	-	10	nA	
١L	Reverse Light Current	E_e =1mW/cm ² λ_P =940nm, V _R =5V	0.5	-	3.0	uA	2
tr	Rise Time	V _R =5V	-	6	-		3
t _f	Fall Time	$R_L=1k\Omega$	-	6	-	ns	3
Ст	Transition Capacitance	E₀=0mW/cm² f=1MHz, Vʀ=5V		5		pF	


Official Product HT Part No. B17M1PDH9B000114U1930		Customer Part No.	Data Sheet No.	
Tentative Product	*****	****		-
	ct to changes for improvement without ry data, drawings, company confidential all	05/27/2019	Version 1.0	Page 6/14

Notes:

2. IL Bin Rank : :


Bin Code	A5C
Min	0.5
Max	3.0

3. Test circuit : :




Switching Time

Package Outline Dimension and Recommended Soldering Pattern for Reflow Soldering



Official Product	HT Part No. B17M1PDH9B000114U1930	Customer Part No.	Data Sheet No.	
Tentative Product	******	*****		-
	ct to changes for improvement without ry data, drawings, company confidential all	05/27/2019	Version 1.0	Page 7/14

Characteristics of B17M1PD




Official Product	HT Part No. B17M1PDH9B000114U1930	Customer Part No.	Data Sheet No.	
Tentative Product	*****	****		-
	ct to changes for improvement without ry data, drawings, company confidential all	05/27/2019	Version 1.0	Page 8/14

Precaution for Use


- 1. The chips should not be used directly in any type of fluid such as water, oil, organic solvent, etc.
- 2. When the LEDs are illuminating, the maximum ambient temperature should be first considered before operation.
- 3. LEDs must be stored in a clean environment. A sealed container with a nitrogen atmosphere is necessary if the storage period is over 3 months after shipping.
- 4. The LEDs must be used within 4 weeks after unpacked. Unused products must be repacked in an anti-electrostatic package, folded to close any opening and then stored in a dry and cool space.
- 5. The appearance and specifications of the products may be modified for improvement without further notice.
- 6. The LEDs are sensitive to the static electricity and surge. It is strongly recommended to use a grounded wrist band and anti-electrostatic glove when handling the LEDs.If a voltage over the absolute maximum rating is applied to LEDs, it will damage LEDs.Damaged LEDs will show some abnormal characteristics such as remarkable increase of leak current, lower turn-on voltage and getting unlit at low current.

Official Product	HT Part No. B17M1PDH9B000114U1930	Customer Part No.	Data Sheet No.	
Tentative Product	******	****		-
	ct to changes for improvement without ry data, drawings, company confidential all	05/27/2019	Version 1.0	Page 9/14

Packaging Tape Dimension




Dim. A	Dim. B	Dim. C	Q'ty/Reel
2.30±0.10	1.45±0.10	0.95±0.10	4K
			Unit: mm



Official Product	HT Part No. B17M1PDH9B000114U1930	Customer Part No.	Data Sheet No.	
Tentative Product	*****	*****		-
	ct to changes for improvement without ry data, drawings, company confidential all	05/27/2019	Version 1.0	Page 10/14

Reel Dimension



5 or 10 boxes per carton is available depending on shipment quantity.


Official Product HT Part No. B17M1PDH9B000114U1930	Customer Part No.	Data Sheet No.	
Tentative Product ***********	****		-
Specifications are subject to changes for improvement without advance notice. Proprietary data, drawings, company confidential all rights reserved.	05/27/2019	Version 1.0	Page 11/14

Dry Pack

All SMD optical devices are **MOISTURE SENSITIVE**. Avoid exposure to moisture at all times during transportation or storage. Every reel is packaged in a moisture protected anti-static bag. Each bag is properly sealed prior to shipment.

A humidity indicator will be included in the moisture protected anti-static bag prior to shipment.

The packaging sequence is as follows:



Baking

Baking before soldering is recommended when the package has been unsealed for 4 weeks. The conditions are as followings:

- 1. $60\pm3^{\circ}C\times(12\sim24hrs)$ and <5% RH, taped reel type.
- 2. 100±3°C×(45min~1hr), bulk type.
- 3. $130\pm3^{\circ}C\times(15\min-30\min)$, bulk type.

Precautions

- 1. Avoid exposure to moisture at all times during transportation or storage.
- 2. Anti-Static precaution must be taken when handling GaN, InGaN, and AlInGaP products.
- 3. It is suggested to connect the unit with a current limiting resistor of the proper size. Avoid applying a reverse voltage beyond the specified limit.
- 4. Avoid operation beyond the limits as specified by the absolute maximum ratings.
- 5. Avoid direct contact with the surface through which the LED emits light.
- 6. If possible, assemble the unit in a clean room or dust-free environment.

Official Product	HT Part No. B17M1PDH9B000114U1930	Customer Part No.	Data Sheet No.	
Tentative Product	*****	****		-
	ct to changes for improvement without ry data, drawings, company confidential all	05/27/2019	Version 1.0	Page 12/14

SMD Type Photo Diode B17M1PD--H9B000114U1930


HARVATEK

Reflow Soldering

Recommend soldering paste specifications:

- 1. Operating temp.: Above 220°C ,60sec
- 2. Peak temp.:260°C Max.,10sec Max.
- 3. Reflow soldering should not be done more than two times.
- 4. Never take next process until the component is cooled down to room temperature after reflow.
- 5. The recommended reflow soldering profile (measuring on the surface of the LED terminal) is following:

Lead-free Solder Profile



Reworking

- Rework should be completed within 5 seconds under 260° C.
- The iron tip must not come in contact with the copper foil.
- Twin-head type is preferred.

Cleaning

Following are cleaning procedures after soldering:

- An alcohol-based solvent such as isopropyl alcohol (IPA) is recommended.
- Temperature x Time should be 50 $^\circ C$ x 30sec. or <30 $^\circ C$ x 3min
- Ultra sonic cleaning: < 15W/ bath; bath volume ≤ 1liter
- Curing: 100°C max, <3min

Official Product	HT Part No. B17M1PDH9B000114U1930	Customer Part No.	Data Sheet No.	
Tentative Product	*****	****		-
	ct to changes for improvement without ry data, drawings, company confidential all	05/27/2019	Version 1.0	Page 13/14

Cautions of Pick and Place

- Avoid stress on the resin at elevated temperature.
- Avoid rubbing or scraping the resin by any object.
- Electric-static may cause damage to the component. Please ensure that the equipment is properly grounded. Use of an ionizer fan is recommended.

Revise History

Rev.	Descriptions	Date	Page
Preliminary	-	01/03/2019	-
V1.0	-	05/27/2019	-

Official Product	HT Part No. B17M1PDH9B000114U1930	Customer Part No.	Data Sheet No.	
Tentative Product	*****	****		-
	t to changes for improvement without y data, drawings, company confidential all	05/27/2019	Version 1.0	Page 14/14