


15 Watts • 50 Volts • 128us, 10% 960-1215MHz



## **ELECTRICAL CHARACTERISTICS @ 25°C**

Symbol	Characteristics	Test Conditions	Min	Тур	Max	Units
P <sub>OUT</sub>	Output Power	P <sub>IN</sub> =0.32W, Freq=960,1090,1215 MHz	15	19		W
G <sub>P</sub>	Power Gain	P <sub>IN</sub> =0.32W, Freq=960,1090,1215 MHz	17.5	18.1		dB
$\eta_D$	Drain Efficiency	P <sub>IN</sub> =0.32W, Freq=960,1090,1215 MHz	60	65		%
Dr	Droop	P <sub>IN</sub> =0.32W, Freq=960,1090,1215 MHz		0.1	0.5	dB
VSWR-T	Load Mismatch Tolerance	P <sub>IN</sub> =0.32W, Freq=1090MHz			5:1	

• Bias Condition:  $V_{DD}$ =+50V, Idq=10mA constant current ( $V_{GS}$ = -2.0 ~ -4.5V typical)

## FUNCTIONAL CHARACTERISTICS @ 25°C

I <sub>D(Off)</sub>	Drain leakage current	$V_{GS} = -8V, V_{D} = 50V$		1.0	mA
I <sub>G(Off)</sub>	Gate leakage current	$V_{GS} = -8V, V_D = 0V$		0.2	mA

#### Export Classification: EAR-99


Specifications are subject to change. Consult www.microsemi.com for local sales and technical support contacts.




15 Watts • 50 Volts • 128us, 10% 960-1215MHz

#### **TYPICAL BROAD BAND PERFORMACE DATA – 128us, 10% PULSING**

Frequency	P <sub>iN</sub> (mW)	Р <sub>оит</sub> (W)	Ι <sub>D</sub> (mA)	IRL (dB)	η <sub>D</sub> (%)	G <sub>P</sub> (dB)	Droop (dB)
960 MHz	320	20.5	68	-9.3	71	18.1	0.2
1090 MHz	320	20.9	76	-9.2	63	18.2	0.2
1215 MHz	320	18.2	78	-13.5	62	18.2	0.3








15 Watts • 50 Volts • 128us, 10% 960-1215MHz

# **Transistor Test Fixture Overall Dimension**




Dimensions in inches.

Test Fixture available upon request



15 Watts • 50 Volts • 128us, 10% 960-1215MHz

### **55-QQ PACKAGE DIMENSION**



Dim	Millimeter	Tol	Inches	Tol
А	13.970	0.250	0.550	0.010
В	4.570	0.250	0.160	0.010
С	3.860	0.330	0.152	0.013
D	1.270	0.130	0.050	0.005
E	1.020	0.130	0.040	0.005
F	1.700	0.130	0.067	0.005
G	0.130	0.025	0.005	0.001
н	8.130	0.250	0.320	0.010
l I	45°	5°	45°	5°
J	5.080	0.250	0.200	0.010
ĸ	2.54 DIA	0.130	.100 DIA	0.005
L	1.270	0.130	0.050	0.005
м	9.530	0.130	0.375	0.005


PIN 1: DRAIN PIN 2: SOURCE PIN 3: GATE





15 Watts • 50 Volts • 128us, 10% 960-1215MHz

**55-QQP PACKAGE DIMENSION** 



Dim	Millimeter	Tol	Inches	Tol
Α	5.84	.25	.230	.010
В	4.06	.25	.160	.010
С	3.17	.05	.125	.002
D	1.27	.13	.050	.005
E	1.02	.13	.040	.005
F	1.57	.13	.062	.005
G	.130	.02	.005	.001
Н	8.12	.25	.320	.010
l.	45°	5°	45°	5°
J	5.08	.25	.200	.010
К	1.40	.13	.055	.005


PIN 1: DRAIN PIN 2: SOURCE PIN 3: GATE





15 Watts • 50 Volts • 128us, 10% 960-1215MHz

### 55-78029 CASE OUTLINE OVERALL PALLET DIMENSION



Dimensions: Length=1.200" x Width=0.600" x Height=0.150"



15 Watts • 50 Volts • 128us, 10% 960-1215MHz

Microsemi makes no warranty, representation, or guarantee regarding the information contained herein or the suitability of its products and services for any particular purpose, nor does Microsemi assume any liability whatsoever arising out of the application or use of any product or circuit. The products sold hereunder and any other products sold by Microsemi have been subject to limited testing and should not be used in conjunction with mission-critical equipment or applications. Any performance specifications are believed to be reliable but are not verified, and Buyer must conduct and complete all performance and other testing of the products, alone and together with, or installed in, any end-products. Buyer shall not rely on any data and performance specifications or parameters provided by Microsemi. It is the Buyer's responsibility to independently determine suitability of any products and to test and verify the same. The information provided by Microsemi hereunder is provided "as is, where is" and with all faults, and the entire risk associated with such information is entirely with the Buyer. Microsemi does not grant, explicitly or implicitly, to any party any patent rights, licenses, or any other IP rights, whether with regard to such information itself or anything described by such information provided in this document is proprietary to Microsemi, and Microsemi reserves the right to make any changes to the information in this document or to any products and services at any time without notice.

Microsemi Corporation (Nasdaq: MSCC) offers a comprehensive portfolio of semiconductor and system solutions for aerospace & defense, communications, data center and industrial markets. Products include high-performance and radiation-hardened analog mixed-signal integrated circuits, FPGAs, SoCs and ASICs; power management products; timing and synchronization devices and precise time solutions, setting the world's standard for time; voice processing devices; RF solutions; discrete components; enterprise storage and communication solutions, security technologies and scalable anti-tamper products; Ethernet solutions; Power-over-Ethernet ICs and midspans; as well as custom design capabilities and services. Microsemi is headquartered in Aliso Viejo, Calif., and has approximately 4,800 employees globally. Learn more at www.microsemi.com.

©2016 Microsemi Corporation. All rights reserved. Microsemi and the Microsemi logo are registered trademarks of Microsemi Corporation. All other trademarks and service marks are the property of their respective owners.

**Revision History** 

Revision Level / Date	Para. Affected	Description
Rev 1 / 12 Dec 2014	Initial	First release