

## Part Number: 87833-0433



 Status:
 Contact Molex

 Series:
 87833

 Category:
 PCB Headers

 Overview:
 Milli-Grid™

Series image - Reference only

#### Mates With Part(s):

50394 Wire-to-Board Terminals, 51110 Wire-to-Board Crimp Housing, 87568 Wire-to-Board IDT Housing, 79107 Board-to-Board Top Entry Through Hole Receptacle, 79108 Board-to-Board FFC/FPC Top Entry Through Hole Receptacle

#### **Part Detail**

	G	er	ne	ra	ı
--	---	----	----	----	---

StatusContact MolexCategoryPCB HeadersSeries87833ApplicationSignal, Wire-to-Board

Application Signal, wire-to-Board

Comments Contact Molex for application in automotive industry

 Overview
 Milli-Grid™

 Product Name
 Milli-Grid™

### Physical

Breakaway No Circuits (Loaded) 4 4 Circuits (maximum) Color - Resin Black Durability (mating cycles max) 100 First Mate / Last Break No 94V-0 Flammability Glow-Wire Compliant Nο Guide to Mating Part No Keying to Mating Part None Lock to Mating Part Yes Material - Metal Phosphor Bronze Material - Plating Mating Gold Material - Plating Termination Tin Material - Resin Nylon Number of Rows Orientation

Right Angle PC Tail Length 2 16mm PCB Locator No PCB Retention None PCB Thickness - Recommended 1.60mm Packaging Type Tube Pitch - Mating Interface 2.00mm Pitch - Termination Interface 2.00mm Plating min - Mating 0.381µm Plating min - Termination 1.905µm Polarized to PCB No Shrouded Fully Stackable No Surface Mount Compatible (SMC) -55°C to +105°C Temperature Range - Operating

Termination Interface: Style Through Hole

(Please review the Product Specification for specific details.)

# (Please review the Product Specification for specific details.) Current - Maximum per Contact 2A

Current - Maximum per Contact 2A Voltage - Maximum 125V

Agency Certification

CSA LR19980 UL E29179

Reference - Drawing Numbers

Product Specification Sales Drawing PS-87831-027 SD-87833-037

# **Application Tooling**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application

Check our list of old tooling that used to be available for this part