

Multilayer Ceramic Chip Capacitor

NOVACAP + SYFER + VOLTRONICS							
Part Number:	2220YA250562ł	(STSYX	Description:	2220 250Vac (Y2), 305Vac (X1), 50/60Hz / 1000Vdc 5.6nF ±10% X7R (2R1) to AEC- Q200			
Approval	Approval IEC/EN60384-14:2013+A1			~			
Specifications: UL60384-14, CAN/CSA E60384-14:14				17			
			<	I.			
Certification:	TÜV R60156291 / ID1111	239246					
Classification:	UL/cUL E228790-20210208 on: IEC/EN 60384-14:2013+A1 Class Y2 / X1		12 - 14 - 13				
	UL/cUL FOWX2, FOWX8		Component	مر Marking and Certification Bodies:			
Material Group I : CTI >= 600			SYX C Image: Signal state of the state o				
Mechanical Specification							
Size Code	Size Code			2220			
Length (L1) in mm (")			5.7 ± 0.40 (0.225 ± 0.016)				
Width (W) in mm (")			5.0 ± 0.40 (0.197 ± 0.016)				
Thickness (T) in mm (Thickness (T) in mm (")			2.0 Max (0.08 Max)			
Minimum Termination	Band (L2,L3) in mm (")		0.25 (0.010)				
Maximum Termination	n Band (L2,L3) in mm (")		1.00 (0.040)				
Minimum Band Gap (L4) in mm (")		4.0 (0.158)				
Termination Material			FlexiCap™ Polymer termination, Nickel barrier, Sn Plated Solder (RoHS compliant)				
Solderability			IEC-60068-2-58				
Packaging	Packaging			7" Reel Horizontal Orientation, 500 per reel			
General Electrical Specification							
Rated Voltage	Rated Voltage			Class Y2 (250Vac), Class X1 (305Vac), 50/60Hz, 5kV impulse			
Humidity Grade	Humidity Grade			Grade III (IEC/EN60384-14:2013 Annex 1)			
Maximum DC Working Voltage			1000Vdc certified / (2500Vdc outside scope of any specification)				
Nominal Capacitance Value			5.6nF				
Capacitance Tolerance			±10%				
Tangent of Loss Angle (Tan δ)			≤0.025				
Capacitance and Tan δ Test Conditions			1.0Vrms @ 1kHz				
Voltage Proof		100% test: 4000Vdc 1s min / 5s max AQL test: 4000Vdc / 3000Vac 60s min / 5kV 1.2x50µs impulse					
(50mA max charging current for DC tests) Min Insulation Resistance (IR)		100.00GOhm @ 100Vdc					
Dielectric Classification		X7R (2R1) to AEC-Q200					
Rated Temperature Range			-55°C / +125°C				
Maximum Capacitance Change over Temperature Range			No DC Voltage ±15%				
			Rated DC Voltage -				
Climatic Category (IEC)			55/125/56				
Ageing Characteristic			<2% per decade				
Knowles Precisi	on Devices - Sales			rmed valid on the date generated, the latest published data			
	e-sales@knowles.com	for this part may differ a	and is available at http://ww	ww.knowlescapacitors.com or by contacting us.			
		© The information contained on this drawing is confidential and may not be copied in whole or part in any form or disclosed to a third party without the consent of Knowles and any customer mentioned within this					
USA: KPD-NA-sales@knowles.com							
		specification.		20210902 215230030UTC			



Multilayer Ceramic Chip Capacitor

NOVACAP + SYFER + VOLTRONICS							
Part Number: 2220YA250562	KSTSYX	Description:	2220 250Vac (Y2), 305Vac (X1), 50/60Hz / 1000Vdc 5.6nF ±10% X7R (2R1) to AEC- Q200				
Environmental							
RoHS Compliant to 2011/65/EC as amend	ed by 2015/863/EU	Compliant					
REACH Compliant		211 compliant					
California Proposition 65		No exposure risk					
Board Layout							
Knowles' conventional 2-terminal chip capacitors can generally be mounted using pad designs in accordance with international specification IPC-7351, Generic Requirements for Surface Mount Design and Land Pattern Standards, but there are some other factors that have been shown to reduce mechanical stress, such as reducing the pad width to less than the chip width. In addition, the position of the chip on the board should be considered. Some high voltage parts may require modifications to the board layout and/or the addition of a conformal coating to prevent flashover. Refer to application note AN0043 for further information.			IPC-7351 pad design 2220 C 5.30mm 0.209" Y 1.50mm 0.059" X 5.40mm 0.213" X 5.40mm 0.213"				
Packaging							
Tape packaging information for tape-au Tape and reel packing of surface mour capacitors for automatic placement are with IEC60286-3.	nting chip		Product identifying label Plastic carrier tape Top tape 8 or 12mm 178mm (7") or nominal 330mm (13") dia. reel				
Soldering							
Reflow solder in accordance with IPC- Recommended reflow profile as laid de IPC/JEDEC J-STD-020. Wave soldering is also possible, but ca taken for case sizes 1210 and larger a thickness >1.0mm. Trials are encourage Hand soldering is not recommended a	own in are must be ind component ged. ind can lead to	Temperature	T_p T_L T_L T_L T_L T_L T_L T_s T_{s}				
component damage through thermal shock.							
Application notes with mounting and handling guidance are available on request.							
Compex DLI	Johanson MFG	Novacap	Syfer Voltronics				
Knowles Precision Devices - Sales This datasheet is for a standard item and is confirmed valid on the date generated, the late for this part may differ and is available at http://www.knowlescapacitors.com or by contact Asia: KPD-Asia-sales@knowles.com Image: This datasheet is for a standard item and is confirmed valid on the date generated, the late for this part may differ and is available at http://www.knowlescapacitors.com or by contact Image: Contact of the part may differ and is available at http://www.knowlescapacitors.com Image: Contact of the part may differ and is available at http://www.knowlescapacitors.com Image: Contact of the part may differ and is contained on this drawing is Image: Contact of the part may differ and is contained on this drawing is Image: Contact of the part may differ and is contained on this drawing is Image: Contact of the part may differ and is							
USA: KPD-NA-sales@knowles.com www.knowlescapacitors.com	any form or disclosed to a t	e copied in whole or part in hird party without the consent comer mentioned within this	ıt				