



SCHEMATIC
VIEW FROM BASE END
FUSE RECOMMENDED BUT NOT SUPPLIED

SPECIFICATIONS

WIRING	INPUT		OUTPUT				SHAFT ROTATION FOR VOLTAGE INCREASE	TERMINAL CONNECTIONS FOR INCREASING VOLTAGE AS VIEWED FROM BASE END		
	VOLTS	HERTZ	VOLTS	CONSTANT CURRENT LOAD		CONSTANT IMPEDANCE LOAD		INPUT	OUTPUT	
				MAX. AMPS	MAX. KVA	MAX. AMPS				MAX. KVA
SINGLE PHASE	240	50/60	0-240	10	2.40	13	3.12	CW	2-4	4-3
			0-280	10	2.80	—	—	CCW	2-4	2-3
	120	50/60	0-280	10	1.20	—	—	CW	1-4	4-3
			0-280	10	1.20	—	—	CCW	2-5	2-3

UNLESS OTHERWISE SPECIFIED, TOLERANCE IS ±
FRACTIONS DECIMALS HOLE ANGLES DRAFT
XX .06

ALL DIMENSIONS APPLY AFTER PLATING

TITLE: **SPECIFICATION CONTROL DRAWING**
VARIABLE TRANSFORMER
TYPE: 2520 C

STACO ENERGY PRODUCTS CO.
DAYTON, OHIO U.S.A.

CAT. NO.	DRAWN BY	DATE	FIRST USED ON	CUSTOMER APPROVAL	DATE
DO NOT SCALE DWG.	CHECKER	DATE	WEIGHT APPROX	DWG. SIZE	DWG. NO.
CODE IDENT. NO. 83008	ENGINEER	DATE	SCALE	C	031-5502

The information and design disclosed herein was originated by and is the property of STACO ENERGY PRODUCTS CO., which reserves all patent, proprietary, design, manufacturing, reproduction, use and sale rights thereto, and to any article disclosed therein, except to the extent rights are expressly granted to others. The foregoing does not apply to vendor proprietary parts.