




www.vishay.com

Vishay Semiconductors

Schottky Rectifier, 2 x 30 A







PRODUCT SUMMARY							
Package	TO-220AB						
I _{F(AV)}	2 x 30 A						
V _R	35 V, 40 V, 45 V						
V _F at I _F	0.53 V						
I _{RM} max.	250 mA at 125 °C						
T _J max.	150 °C						
Diode variation	Common cathode						
E _{AS}	20 mJ						

FEATURES

- 150 °C T_J operation
- · Low forward voltage drop
- High frequency operation





- Compliant to RoHS Directive 2002/95/EC
- Designed and qualified according to JEDEC-JESD47
- Halogen-free according to IEC 61249-2-21 definition (-N3 only)

DESCRIPTION

This center tap Schottky rectifier has been optimized for low reverse leakage at high temperature. The proprietary barrier technology allows for reliable operation up to 150 °C junction temperature. Typical applications are in switching power supplies, converters, freewheeling diodes, and reverse battery protection.

MAJOR RATINGS AND CHARACTERISTICS							
SYMBOL	CHARACTERISTICS	VALUES	UNITS				
I _{F(AV)}	Rectangular waveform (per device)	60	Α				
V _{RRM}		35 to 45	V				
I _{FRM}	T _C = 113 °C (per leg)	60	^				
I _{FSM}	t _p = 5 μs sine	1500	A				
V _F	30 A _{pk} , T _J = 125 °C	0.53	V				
T _J	Range	- 65 to 150	°C				

VOLTAGE RAT	NGS										
PARAMETER	SYMBOL	VS- 60CTQ035PbF	VS- 60CTQ035-N3	VS- 60CTQ040PbF	VS- 60CTQ040-N3	VS- 60CTQ045PbF	VS- 60CTQ045-N3	UNITS			
Maximum DC reverse voltage	V_{R}										
Maximum working peak reverse voltage	V _{RWM}	35	35	40	40	45	45	V			

ABSOLUTE MAXIMUM RATINGS								
PARAMETER		SYMBOL	TEST COND	ITIONS	VALUES	UNITS		
Maximum average per leg forward current per device			50 % duty cycle at T _C = 113 °C	` rootongular wayafarm	30			
		I _{F(AV)}	50 % duty cycle at 1 _C = 113 C	, rectangular wavelonn	60			
Peak repetitive forward current per leg		I _{FRM}	Rated V _R , square wave, 20 kHz, T _C = 113 °C		60	А		
Maximum peak one cycle non-repetitive surge current per leg		l=	5 μs sine or 3 μs rect. pulse	Following any rated load condition and with rated	1500			
		I _{FSM}	10 ms sine or 6 ms rect. pulse	V _{RRM} applied	300			
Non-repetitive avalanche energy per leg E _{AS}		E _{AS}	T _J = 25 °C, I _{AS} = 3 A, L = 4.40 mH		20	mJ		
Repetitive avalanche current per	leg	I _{AR}	Current decaying linearly to zer Frequency limited by T _J maxim		3	Α		

Revision: 29-Aug-11 Document Number: 94239



VS-60CTQ...PbF Series, VS-60CTQ...-N3 Series

Vishay Semiconductors

ELECTRICAL SPECIFICATIONS								
PARAMETER	SYMBOL	TEST CONDITIONS			MAX.	UNITS		
		30 A	T _{.1} = 25 °C	0.51	0.56			
Maximum forward voltage drop	V (1)	60 A	1j=25 C	0.66	0.72	V		
	V _{FM} ⁽¹⁾	30 A	T 105 °C	0.48	0.53			
		60 A	T _J = 125 °C	0.68	0.75			
Maximum instantaneous reverse current		T _J = 25 °C	Rated DC voltage	0.33	2	mΛ		
Maximum instantaneous reverse current	I _{RM}	T _J = 125 °C	Hated DC voltage	145	250	mA		
Maximum junction capacitance	C _T	$V_R = 5 V_{DC}$ (test signal range 100 kHz to 1 MHz) 25 °C			000	pF		
Typical series inductance	L _S	Measured from top of terminal to mounting plane			.0	nΗ		
Maximum voltage rate of change	dV/dt	Rated V _R	10 000		V/µs			

Note

 $^{^{(1)}\,}$ Pulse width < 300 $\mu s,$ duty cycle < 2 %

THERMAL - MECHANICAL SPECIFICATIONS								
PARAMETER	8	SYMBOL	TEST CONDITIONS	VALUES	UNITS			
Maximum junction temperature rar	nge	T_J		- 65 to 150	°C			
Maximum storage temperature ran	nge	T _{Stg}		- 65 to 175	C			
Maximum thermal resistance, junction to case per leg		R _{thJC}	DC operation	1.2	°C/W			
Typical thermal resistance, case to heatsink		R _{thCS}	Mounting surface, smooth and greased	0.50	C/VV			
Approximate weight				2	g			
Approximate weight				0.07	OZ.			
minimum			Non-lubricated threads	6 (5)	kgf · cm			
Mounting torque m	aximum		Non-lubricated tiffeads	12 (10)	(lbf \cdot in)			
				60CTQ035				
Marking device			Case style TO-220AB	60CT	Q040			
				60CTQ045				

www.vishay.com

Vishay Semiconductors




Fig. 1 - Maximum Forward Voltage Drop Characteristics




Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage




Fig. 4 - Maximum Thermal Impedance Z_{thJC} Characteristics

www.vishay.com

Vishay Semiconductors




Fig. 5 - Maximum Allowable Case Temperature vs. Average Forward Current




Fig. 6 - Forward Power Loss Characteristics




Fig. 7 - Maximum Non-Repetitive Surge Current (Per Leg)


Note

Formula used: $T_C = T_J - (Pd + Pd_{REV}) \times R_{thJC}$; $Pd = Forward power loss = I_{F(AV)} \times V_{FM} at (I_{F(AV)}/D)$ (see fig. 6); $Pd_{REV} = Inverse power loss = V_{R1} \times I_R (1 - D)$; I_R at $V_{R1} = 80 \%$ rated V_R

VS-60CTQ...PbF Series, VS-60CTQ...-N3 Series

Vishay Semiconductors

ORDERING INFORMATION TABLE



1 - Vishay Semiconductors product

2 - Current rating (60 = 60 A)

Circuit configuration

C = Common cathode

4 - Package

T = TO-220

5 - Schottky "Q" series

035 = 35 V

Voltage ratings

040 = 40 V 045 = 45 V

7 - Environmental digit

0 " (

• PbF = Lead (Pb)-free and RoHS compliant

• -N3 = Halogen-free, RoHS compliant, and totally lead (Pb)-free

ORDERING INFO	RMATION (Example)		
PREFERRED P/N	QUANTITY PER T/R	MINIMUM ORDER QUANTITY	PACKAGING DESCRIPTION
VS-60CTQ035PbF	50	1000	Antistatic plastic tube
VS-60CTQ035-N3	50	1000	Antistatic plastic tube
VS-60CTQ040PbF	50	1000	Antistatic plastic tube
VS-60CTQ040-N3	50	1000	Antistatic plastic tube
VS-60CTQ045PbF	50	1000	Antistatic plastic tube
VS-60CTQ045-N3	50	1000	Antistatic plastic tube


	LINKS TO RELAT	ED DOCUMENTS
Dimensions		www.vishay.com/doc?95222
Part marking information	TO-220AB PbF	www.vishay.com/doc?95225
	TO-220AB -N3	www.vishay.com/doc?95028



Vishay Semiconductors

TO-220AB

DIMENSIONS in millimeters and inches



Diodes

- 1. Anode/open 2. - Cathode
- 3. Anode

Conforms to JEDEC outline TO-220AB

MILLIMETERS

MILLIM	IETERS	INC	INCHES			
MIN.	MAX.	MIN.	MAX.	NOTES		
4.25	4.65	0.167	0.183			
1.14	1.40	0.045	0.055			
2.56	2.92	0.101	0.115			
0.69	1.01	0.027	0.040			
0.38	0.97	0.015	0.038	4		
1.20	1.73	0.047	0.068			
1.14	1.73	0.045	0.068	4		
0.36	0.61	0.014	0.024			
0.36	0.56	0.014	0.022	4		
14.85	15.25	0.585	0.600	3		
8.38	9.02	0.330	0.355			
11.68	12.88	0.460	0.507	6		
	MIN. 4.25 1.14 2.56 0.69 0.38 1.20 1.14 0.36 0.36 14.85 8.38	4.25 4.65 1.14 1.40 2.56 2.92 0.69 1.01 0.38 0.97 1.20 1.73 1.14 1.73 0.36 0.61 0.36 0.56 14.85 15.25 8.38 9.02	MIN. MAX. MIN. 4.25 4.65 0.167 1.14 1.40 0.045 2.56 2.92 0.101 0.69 1.01 0.027 0.38 0.97 0.015 1.20 1.73 0.047 1.14 1.73 0.045 0.36 0.61 0.014 0.36 0.56 0.014 14.85 15.25 0.585 8.38 9.02 0.330	MIN. MAX. MIN. MAX. 4.25 4.65 0.167 0.183 1.14 1.40 0.045 0.055 2.56 2.92 0.101 0.115 0.69 1.01 0.027 0.040 0.38 0.97 0.015 0.038 1.20 1.73 0.047 0.068 1.14 1.73 0.045 0.068 0.36 0.61 0.014 0.024 0.36 0.56 0.014 0.022 14.85 15.25 0.585 0.600 8.38 9.02 0.330 0.355		

SYMBOL	IVIILLIIV	IEIENO	INC	NOTES	
STIVIBOL	MIN.	MAX.	MIN.	MAX.	NOTES
E	10.11	10.51	0.398	0.414	3, 6
E1	6.86	8.89	0.270	0.350	6
E2	-	0.76	-	0.030	7
е	2.41	2.67	0.095	0.105	
e1	4.88	5.28	0.192	0.208	
H1	6.09	6.48	0.240	0.255	6, 7
L	13.52	14.02	0.532	0.552	
L1	3.32	3.82	0.131	0.150	2
ØΡ	3.54	3.73	0.139	0.147	
Q	2.60	3.00	0.102	0.118	
θ	90° t	o 93°	90° t	o 93°	

INCHES

- (1) Dimensioning and tolerancing as per ASME Y14.5M-1994
- (2) Lead dimension and finish uncontrolled in L1
- (3) Dimension D, D1 and E do not include mold flash. Mold flash shall not exceed 0.127 mm (0.005") per side. These dimensions are measured at the outermost extremes of the plastic body
- (4) Dimension b1, b3 and c1 apply to base metal only
- (5) Controlling dimensions: inches
- Thermal pad contour optional within dimensions E, H1, D2 and
- $^{(7)}$ Dimensions E2 x H1 define a zone where stamping and singulation irregularities are allowed
- Outline conforms to JEDEC TO-220, except A2 (maximum) and D2 (minimum) where dimensions are derived from the actual package outline

Lead tip



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.