

SPECIFICATION SHEET

| SPECIFICATION SHEET NO. | N0310-DBS207S000S20A |
|-------------------------|---|
| DATE | Mar. 10, 2021 |
| REVISION | AO |
| DESCRIPITION | SMD Single Phase Glass Passivated Bridge Rectifier, DBS series, |
| | DB207S Type 4 Pads, |
| | Reverse Voltage 1000V Max. Forward Current 2.0A Max. |
| | Operating Temp. Range -55°C ~+150°C, |
| | Package in Tape/Reel, 1000pcs/Reel |
| | RoHS/RoHS III compliant |
| CUSTOMER | |
| CUSTOMER PART NUMBER | |
| CROSS REF. PART NUMBER | |
| ORIGINAL PART NUMBER | MDD DB207S |
| PART CODE | DBS207S000S20A |

| ٧ | ΈN | IDC | R | AP | PR | OV | Ε |
|---|----|-----|---|----|----|----|---|
|---|----|-----|---|----|----|----|---|

Issued/Checked/Approved








DATE: March 10, 2021

| CUSTOMER APPROVE | |
|------------------|--|
| | |
| | |
| | |
| DATE: | |
| | |



SMD BRIDGE RECTIFER DBS SERIES

MAIN FEATURE





- Reliable low cost construction utilizing molded plastic technique
- Small size simple installation
- · High forward surge current capability
- High temperature soldering guaranteed.
- 260 °C/10 seconds, at 5 lbs (2.3kg) tension

APPLICATION

• For printed circuit board

PART CODE GUIDE



| DBS | 2075000 | S | 20A |
|-----|---------|---|-----|
| 1 | 2 | 3 | 4 |

- 1) DBS: SMD Single Phase Glass Passivated Bridge Rectifier, 4 Pads, DBS series
- 2) 207S000: Type code for original part number DB207S
- 3) S: Package code, Tape/reel, 1000pcs/reel.
- 4) 20A: Specification code for Reverse Voltage 1000V Max. Forward Current 2.0A Max.

MORE ITEMS AVAILABLE

| DBS101S000S105 | DBS102S000S110 | DBS103S000S120 | DBS104S000S140 | DBS105S000S160 |
|----------------|----------------|----------------|----------------|----------------|
| DBS106S000S180 | DBS107S000S10A | | | |
| DBS151S000S150 | DBS152S000S151 | DBS153S000S152 | DBS154S000S154 | DBS155S000S156 |
| DBS156S000S158 | DBS157S000S15A | | | |
| DBS201S000S205 | DBS202S000S210 | DBS203S000S220 | DBS204S000S240 | DBS205S000S260 |
| DBS206S000S280 | DBS207S000S20A | | | |
| | | | | |


SMD BRIDGE RECTIFER DBS SERIES


DIMENSION (Unit: Inch/mm)

Image for reference





Marking: DB207S






DBS







SMD BRIDGE RECTIFER DBS SERIES

MECHANICAL DATA

| Case | Terminals | Polarity | Mounting Position | Weight per piece |
|-------------------------------|---|------------------------------------|----------------------|-----------------------------|
| JEDEC DBS molded plastic body | Solder plated, Solderable per MIL-STD-750, Method 2026 | Polarity symbol marking on case | Any | 0.020 Ounce, 0.622 grams |

MAX. RATING & CHARACTERISTICS

| Parameter | Parameter | | | VALUE | | UNITS |
|--|----------------------|-------|------|---------|-------|-------|
| | | | Min. | Typical | Max. | |
| Repetitive peak reverse voltage | V RRM | | | 1000 | Volts | |
| RMS voltage | | V RMS | | | 700 | Volts |
| DC blocking voltage | | V DC | | | 1000 | Volts |
| Average forward output rectified current Tc= 40°C | rent | I AV | | | 2.0 | А |
| Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method) | | I FSM | | 60 | | А |
| Instantaneous forward voltage at 2.0 | Α | VF | | | 1.10 | Volts |
| DC reverse current at rated DC | TA=25°C | l R | | | 10 | μΑ |
| blocking voltage | TA=100°C | | | | 500 | μΑ |
| Junction capacitance | Junction capacitance | | | - | | pF |
| Thermal resistance | R QJA | | - | | °C/W | |
| Operating junction temperature range | | TJ | -55 | | +150 | |
| Storage temperature range | | Т ѕтб | -55 | | +150 | °C |

Note

1. Ratings at 25 C ambient temperature unless otherwise specified. Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.



SMD BRIDGE RECTIFER DBS SERIES


RELIABILITY

| Number | Experiment Items | Experiment Method And Conditions | Reference Documents | |
|--------|---------------------------------------|--|---------------------------------|--|
| 1 | Solder Resistance Test | Test 260°C± 5°C for 10 ± 2 sec. Immerse body into solder 1/16" ± 1/32" | MIL-STD-750D METHOD-2031.2 | |
| 2 | Solderability Test | 230°C ±5°C for 5 sec. | MIL-STD-750D METHOD-2026.1 0 | |
| 3 | Pull Test | 1 kg in axial lead direction for 10 sec. | MIL-STD-750D METHOD-2036.4 | |
| 4 | Bend Test | 0.5Kg Weight Applied To Each Lead, Bending Arcs 90 °C ± 5 °C For 3 Times | MIL-STD-750D METHOD-2036.4 | |
| 5 | High Temperature Reverse Bias Test | TA=100°C for 1000 Hours at VR=80% Rated VR | MIL-STD-750D METHOD-1038.4 | |
| 6 | Forward Operation Life Test | TA=25°C Rated Average Rectified Current | MIL-STD-750D METHOD-1027.3 | |
| 7 | Intermittent Operation Life Test | On state: 5 min with rated IRMS Power Off state: 5 min with Cool Forced Air. On and off for 1000 cycles. | MIL-STD-750D METHOD-1036.3 | |
| 8 | Pressure Cooker Test | 15 PSIG, TA=121°C, 4 hours | MIL-S-19500 APPENOIXC | |
| 9 | Temperature Cycling Test | -55°C~+125°C; 30 Minutes For Dwelled Time 5 minutes for transferred time. Total: 10 cycles. | MIL-STD-750D METHOD-1051.7 | |
| 10 | Thermal Shock Test | 0°C for 5 minutes., 100°C for 5minutes, Total: 10 cycles | MIL-STD-750D METHOD-1056.7 | |
| 11 | Forward Surge Test | 8.3ms Single Sale Sine-wave One Surge. | MIL-STD-750D METHOD-4066.4 | |
| 12 | Humidity Test | Ta=65°C, RH=98% for 1000 hours. | MIL-STD-750D METHOD-1021.3 | |
| 13 | High Temperature Storage life Test | 150°C for 1000 Hours | MIL-STD-750D METHOD-1031.5 | |



SMD BRIDGE RECTIFER DBS SERIES

SUGGESTED REFLOW PROFILE (For Reference Only)



- Recommended peak temperature is over 245°C, If peak temperature is below 245 °C, you may adjust the
 following parameters; time length of peak temperature (longer), time length of soldering (longer), thickness of
 solder paste (thicker)
- · Welding shall not exceed 2 times
- Remark: lead free solder paste (96.5 sn/3.0 Ag/0.5Cu)




AVERAGE FORWARD CURRENT(A)

INSTANTANEOUS REVERSE CURRENT(*A)


PART CODE: DBS207S000S20A


SMD BRIDGE RECTIFER DBS SERIES

RATINGS AND CHARACTERISTIC CURVES (For Reference Only)









PERCENT OF RATED PEAK REVERSE VOLTAGE. (%)





FIG. 3-TYPICAL JUNCTION CAPACITANCE PER BRIDGE ELEMENT






SMD BRIDGE RECTIFER DBS SERIES

TAPE/REEL (Unit: mm)

All Devices are packed in accordance with EIA standard RS-481-A and specifications.




| ltem | Symbol | Tolerance | DBS |
|--------------------------|--------|-----------|--------|
| Carrier width | А | 0.1 | 2.8 |
| Carrier Length | В | 0.1 | 5.33 |
| Carrier Depth | С | 0.1 | 2.36 |
| Sprocket hole | d | 0.05 | 1.50 |
| 13"Reel outside diameter | D | 2.0 | 330.00 |
| 13"Reel inner diameter | D1 | Min. | 50.00 |
| 7"Reel outside diameter | D | - | - |
| 7"Reel inner diameter | D1 | - | - |
| Feed hole diameter | D2 | 0.5 | 13.00 |
| Sprocket hole position | E | 0.1 | 1.75 |
| Punch hole position | F | 0.1 | 5.50 |
| Punch hole pitch | Р | 0.1 | 4.00 |
| Sprocket hole pitch | PO | 0.1 | 4.00 |
| Embossment center | P1 | 0.1 | 2.0 |
| Overall tape thickness | Т | 0.1 | 0.28 |
| Tape width | W | 0.3 | 12.00 |
| Reel width | W1 | 1.0 | 18.0 |



SMD BRIDGE RECTIFER DBS SERIES

PACKAGE

| Case Code | Reel Size | MPQ (pcs) | Component Spacing (mm) | Qty. Per Box (pcs) | Inner Box L*W*H (mm) | Reel Size (mm) | Carton size L*W*H (mm) | Qty. Per Carton (pcs) | G. W (kg) |
|--------------|--------------|--------------|------------------------------|--------------------------|----------------------------|----------------------|------------------------------|--------------------------------|--------------|
| DBS | 13" | 2,000 | | 4,000 | 190*190*41 | 330 | 320*320*280 | 10,000 | 6.90 |
| | | | | | | | | | |
| | | | | | | | | | |



DISCLAIMER

NextGen Component, Inc. reserves the right to make changes to the product(s) and or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information