


Vishay Semiconductors

HEXFRED[®] Ultrafast Soft Recovery Diode, 8 A







PRODUCT SUMMARY							
Package	TO-220AC						
I _{F(AV)}	8 A						
V _R	1200 V						
V _F at I _F	2.4 V						
t _{rr} typ.	28 ns						
T _J max.	150 °C						
Diode variation	Single die						

FEATURES

- Ultrafast and ultrasoft recovery
- Very low I_{RRM} and Q_{rr}
- Designed and qualified according to JEDEC®-JESD47
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>



FREE

BENEFITS

- Reduced RFI and EMI
- · Reduced power loss in diode and switching transistor
- Higher frequency operation
- Reduced snubbing
- Reduced parts count

DESCRIPTION

VS-HFA08TB120... is a state of the art ultrafast recovery diode. Employing the latest in epitaxial construction and advanced processing techniques it features a superb combination of characteristics which result in performance which is unsurpassed by any rectifier previously available. With basic ratings of 1200 V and 8 A continuous current, the VS-HFA08TB120... is especially well suited for use as the companion diode for IGBTs and MOSFETs. In addition to ultrafast recovery time, the HEXFRED® product line features extremely low values of peak recovery current (IRBM) and does not exhibit any tendency to "snap-off" during the tb portion of recovery. The HEXFRED features combine to offer designers a rectifier with lower noise and significantly lower switching losses in both the diode and the switching transistor. These HEXFRED advantages can help to significantly reduce snubbing, component count and heatsink sizes. The HEXFRED VS-HFA08TB120... is ideally suited for applications in power supplies and power conversion systems (such as inverters), motor drives, and mumany other similar applications where high speed, high efficiency is needed.

ABSOLUTE MAXIMUM RATINGS									
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS					
Cathode to anode voltage	V _R		1200	V					
Maximum continuous forward current	I _F	T _C = 100 °C	8						
Single pulse forward current	I _{FSM}		130	А					
Maximum repetitive forward current	I _{FRM}		32						
Maximum neuror discipation	D-	T _C = 25 °C	73.5	W					
Maximum power dissipation	PD	T _C = 100 °C	29	vv					
Operating junction and storage temperature range	T _J , T _{Stg}		-55 to +150	°C					

Revision: 10-Jul-15

Document Number: 94045

For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>

1



Vishay Semiconductors

ELECTRIACL SPECIFICATIONS (T _J = 25 °C unless otherwise specified)									
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS			
Cathode to anode breakdown voltage	V _{BR}	I _R = 100 μA	1200	-	-				
Maximum forward voltage	V _{FM}	I _F = 8.0 A	-	2.6	3.3	V			
		I _F = 16 A	-	3.4	4.3				
		I _F = 8.0 A, T _J = 125 °C	-	2.4	3.1				
Maximum reverse		$V_{R} = V_{R}$ rated	-	0.31	10				
leakage current	IRM	T_J = 125 °C, V_R = 0.8 x V_R rated	-	135	1000	μA			
Junction capacitance	CT	V _R = 200 V	-	11	20	pF			
Series inductance	L _S	Measured lead to lead 5 mm from package body	-	8.0	-	nH			

DYNAMIC RECOVERY CHARACTERISTICS ($T_J = 25$ °C unless otherwise specified)									
PARAMETER	SYMBOL	TEST CO	NDITIONS	MIN.	TYP.	MAX.	UNITS		
Reverse recovery time	t _{rr}	I _F = 1.0 A, dI _F /dt = 200	A/ μ s, V _R = 30 V	-	28	-	ns		
	t _{rr1}	T _J = 25 °C		-	63	95			
	t _{rr2}	T _J = 125 °C		-	106	160			
Peak recovery current	I _{RRM1}	T _J = 25 °C		-	4.5	8.0	- A nC - A/μs		
Feak recovery current	I _{RRM2}	T _J = 125 °C	l _F = 8.0 A dl _F /dt = 200 A/μs	-	6.2	11			
	Q _{rr1}	T _J = 25 °C	$V_{\rm R} = 200 \text{V}$	-	140	380			
Reverse recovery charge	Q _{rr2}	T _J = 125 °C		-	335	880			
Peak rate of recovery current during $t_{\rm b}$	dl _{(rec)M} /dt1	T _J = 25 °C		-	133	-			
	dl _{(rec)M} /dt2	T _J = 125 °C]	-	85	-			

THERMAL - MECHANICAL SPECIFICATIONS										
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS				
Lead temperature	T _{lead}	0.063" from case (1.6 mm) for 10 s	-	-	300	°C				
Thermal resistance, junction to case	R _{thJC}		-	-	1.7					
Thermal resistance, junction to ambient	R _{thJA}	Typical socket mount	-	-	40	K/W				
Thermal resistance, case to heatsink	R _{thCS}	Mounting surface, flat, smooth and greased	-	0.25	-					
Weight			-	6.0	-	g				
vveignt			-	0.21	-	oz.				
Mounting torque			6.0 (5.0)	-	12 (10)	kgf · cm (lbf · in)				
Marking device		Case style TO-220AC	HFA08TB120							

Revision: 10-Jul-15



Vishay Semiconductors




Fig. 1 - Maximum Forward Voltage Drop Characteristics




Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage





Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage





 Revision: 10-Jul-15
 3
 Document Number: 94045

 For technical questions within your region: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com
 THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



Vishay Semiconductors




Fig. 5 - Typical Reverse Recovery Time vs. dI_F/dt




Fig. 6 - Typical Recovery Current vs. dl_F/dt




Fig. 7 - Typical Stored Charge vs. dl_F/dt




Fig. 8 - Typical dl_{(rec)M}/dt vs. dl_F/dt

 Revision: 10-Jul-15
 4
 Document Number: 94045

 For technical questions within your region: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com
 DiodesEurope@vishay.com

 THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

I_{rr} (A)



Vishay Semiconductors




Fig. 9 - Reverse Recovery Parameter Test Circuit





Fig. 10 - Reverse Recovery Waveform and Definitions

www.vishay.com

VS-HFA08TB120PbF, VS-HFA08TB120-N3

Vishay Semiconductors

ORDERING INFORMATION TABLE



ORDERING INFORMATION (Example)									
PREFERRED P/N	QUANTITY PER T/R	MINIMUM ORDER QUANTITY	PACKAGING DESCRIPTION						
VS-HFA08TB120PbF	50	1000	Antistatic plastic tube						
VS-HFA08TB120-N3	50	1000	Antistatic plastic tube						

LINKS TO RELATED DOCUMENTS							
Dimensions www.vishay.com/doc?95221							
Part marking information	TO-220ACPbF	www.vishay.com/doc?95224					
	TO-220AC-N3	www.vishay.com/doc?95068					




Vishay Semiconductors


TO-220AC


plane

A-

DIMENSIONS in millimeters and inches









Diodes 1 + 2 - Cathode 3 - Anode

Conforms to JEDEC outline TO-220AC

SYMBOL	ABOL MILLIMETERS INCHES NOTES	NOTES		SYMBOL	MILLIN	IETERS	INC	HES	NOTES			
STMBOL	MIN.	MAX.	MIN.	MAX.	NOTES	STMBOL	MIN.	MAX.	MIN.	MAX.	NOTES	
А	4.25	4.65	0.167	0.183			E1	6.86	8.89	0.270	0.350	6
A1	1.14	1.40	0.045	0.055			E2	-	0.76	-	0.030	7
A2	2.56	2.92	0.101	0.115			е	2.41	2.67	0.095	0.105	
b	0.69	1.01	0.027	0.040			e1	4.88	5.28	0.192	0.208	
b1	0.38	0.97	0.015	0.038	4		H1	6.09	6.48	0.240	0.255	6, 7
b2	1.20	1.73	0.047	0.068			L	13.52	14.02	0.532	0.552	
b3	1.14	1.73	0.045	0.068	4		L1	3.32	3.82	0.131	0.150	2
С	0.36	0.61	0.014	0.024			L3	1.78	2.13	0.070	0.084	
c1	0.36	0.56	0.014	0.022	4		L4	0.76	1.27	0.030	0.050	2
D	14.85	15.25	0.585	0.600	3		ØΡ	3.54	3.73	0.139	0.147	
D1	8.38	9.02	0.330	0.355			Q	2.60	3.00	0.102	0.118	
D2	11.68	12.88	0.460	0.507	6		θ	90° t	o 93°	90° t	o 93°	
E	10.11	10.51	0.398	0.414	3, 6							

Notes

⁽¹⁾ Dimensioning and tolerancing as per ASME Y14.5M-1994

- ⁽²⁾ Lead dimension and finish uncontrolled in L1
- (3) Dimension D, D1 and E do not include mold flash. Mold flash shall not exceed 0.127 mm (0.005") per side. These dimensions are measured at the outermost extremes of the plastic body
- (4) Dimension b1, b3 and c1 apply to base metal only
- ⁽⁵⁾ Controlling dimension: inches
- ⁽⁶⁾ Thermal pad contour optional within dimensions E, H1, D2 and E1
- ⁽⁷⁾ Dimension E2 x H1 define a zone where stamping and singulation irregularities are allowed
- ⁽⁸⁾ Outline conforms to JEDEC TO-220, D2 (minimum) where dimensions are derived from the actual package outline



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.