## **Data Sheet**



## **CBN** cutter

Long-lasting high precision CBN endmill for mold steel. Applicable for working material Mold Steel HRC 50-68 finishing machining. Radius tolerance:  $\pm 0.005$  mm; Flute diameter tolerance:  $\pm 0/-0.01$  mm





## **Cutter specification**

- P/N: DK01002ZO
- Specification: D1R0.05XFL5-CBN
- Shank diameter: 4mm
- Working material: Mold steel HRC 50-68
- Radius tolerance: ±0.005mm
- Flute diameter tolerance: +0/ -0.010mm
- Total length: 50mm

## **Recommend cutting parameter**

- Working material: Mold steel
- Machining type: Fine finishing
- Rpm: 40000
- Feed rate: 1000mm/min
- Cutting depth (Ap): 0.01mm
- Cutting width (Ae): 0.4mm