# 4-Channel ESD/EMI Filter **Array Plus 4-Channel ESD Array for USB**

### **Product Description**

The CM1401-03 is a multichannel array with four low-pass filter + ESD channels and four ESD-only channels. The CM1401-03 reduces EMI/RFI emissions on a data port and protects against ESD on a USB port. Each EMI/RFI channel integrates a high quality pi-style filter (C-R-C) that provides greater than 30 dB attenuation in the 800-2700 MHz range relative to the pass band attenuation. These pi-style filters are bidirectional, controlling EMI both to and from a data port connector.

The CM1401-03 provides a high-level of ESD protection on all eight channels for sensitive electronic components that may be subjected to electrostatic discharge (ESD). The input pins safely dissipate ESD strikes of ±15 kV, exceeding the maximum requirement of the IEC 61000-4-2 international standard. Using the MIL-STD-883 (Method 3015) specification for Human Body Model (HBM) ESD, the device provides protection for contact discharges to greater than ±30 kV.

The CM1401-03 is particularly well suited for portable electronics (e.g., cellular telephones, PDAs, notebook computers) because of its small package footprint and low weight.

The CM1401-03 incorporates OptiGuard™ coating for improved reliability at assembly and comes in a space-saving, low-profile Chip Scale Package with RoHS-compliant lead-free finishing.

#### **Features**

- Functionally and Pin-Compatible with CSPEMI307A Device
- OptiGuard<sup>™</sup> Coated for Improved Reliability at Assembly
- Four Channels of Combined EMI/RFI Filtering + ESD Protection
- Four Additional Channels of ESD-Only Protection
- 40 dB Absolute Attenuation (Typical) at 1 GHz
- 35 dB Attenuation (Typical) at 1 GHz Relative to Pass Band
- ±15 kV ESD Protection on All Channels (IEC 61000-4-2 Level 4, Contact Discharge)
- ±30 kV ESD Protection on All Channels (HBM)
- 15-Bump, 2.960 mm X 1.330 mm Footprint
- Chip Scale Package (CSP) Features Extremely Low Lead Inductance for Optimum Filter and ESD Performance
- These Devices are Pb-Free and are RoHS Compliant

#### **Applications**

- EMI Filtering and ESD Protection for Both Data and I/O Ports
- Outer Four Channels Provide ESD Protection for USB Lines and Other I/O Port Applications
- Wireless Handsets



### ON Semiconductor®

http://onsemi.com



**CP SUFFIX** CASE 567BS

#### **MARKING DIAGRAM**

N013 M=

N013 = CM1401-03CP = Date Code = Pb-Free Package

(Note: Microdot may be in either location)


#### **ORDERING INFORMATION**

Device	Package	Shipping <sup>†</sup>
CM1401-03CP	l	3500/Tape & Reel
	(Pb-Free)	

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

- Notebooks
- Desktop PCs

#### **BLOCK DIAGRAM**




<sup>\*</sup>See Package/Pinout Diagram for expanded pin information.


**Table 1. PIN DESCRIPTIONS** 

15-bump CSP Package				
Pin	Name	Description		
A1	ESD_1	ESD Channel 1		
A2	FILTER + ESD_1	Filter + ESD Channel 1		
АЗ	FILTER + ESD_2	Filter + ESD Channel 2		
A4	FILTER + ESD_3	Filter + ESD Channel 3		
A5	FILTER + ESD_4	Filter + ESD Channel 4		
A6	ESD_2	ESD Channel 2		
B1-B3	GND	Device Ground		
C1	ESD_3	ESD Channel 3		
C2	FILTER + ESD_1	Filter + ESD Channel 1		
C3	FILTER + ESD_2	Filter + ESD Channel 2		
C4	FILTER + ESD_3	Filter + ESD Channel 3		
C5	FILTER + ESD_4	Filter + ESD Channel 4		
C6	ESD_4	ESD Channel 4		

### PACKAGE / PINOUT DIAGRAMS



Bottom View (Bumps Up View)



CM1401-03 CSP Package

### **SPECIFICATIONS**

**Table 2. ABSOLUTE MAXIMUM RATINGS** 

Parameter	Rating	Units
Storage Temperature Range	-65 to +150	°C
DC Power per Resistor	100	mW
DC Package Power Rating	600	mW

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

**Table 3. STANDARD OPERATING CONDITIONS** 

Parameter	Rating	Units
Operating Temperature Range	-40 to +85	°C

Table 4. ELECTRICAL OPERATING CHARACTERISTICS (Note 1)

Symbol	Parameter	Conditions	Min	Тур	Max	Units
R	Resistance		80	100	120	Ω
С	Capacitance	At 2.5 V DC	24	30	36	pF
TCR	Temperature Coefficient of Resistance			1200		ppm/°C
TCC	Temperature Coefficient of Capacitance	At 2.5 V DC		-300		ppm/°C
$V_{DIODE}$	Diode Voltage (reverse bias)	I <sub>DIODE</sub> = 10 μA		6.0		V
I <sub>LEAK</sub>	Diode Leakage Current (reverse bias)	V <sub>DIODE</sub> = 3.3 V			100	nA
V <sub>SIG</sub>	Signal Voltage Positive Clamp Negative Clamp	I <sub>LOAD</sub> = 10 mA	5.6 -1.5	6.8 -0.8	9.0 -0.4	٧
V <sub>ESD</sub>	In-system ESD Withstand Voltage a) Human Body Model, MIL-STD-883, Method 3015 b) Contact Discharge per IEC 61000-4-2 Level 4	(Note 2)	±30 ±15			kV
V <sub>CL</sub>	Clamping Voltage during ESD Discharge MIL-STD-883 (Method 3015), 8 kV Positive Transients Negative Transients	(Notes 2 and 3)		+10 -5		V
f <sub>C</sub>	Cut-off Frequency $Z_{SOURCE}$ = 50 $\Omega$ , $Z_{LOAD}$ = 50 $\Omega$	R = 100 Ω, C = 30 pF		58		MHz

T<sub>A</sub> = 25°C unless otherwise specified.
 ESD applied to input and output pins with respect to GND, one at a time.
 Clamping voltage is measured at the opposite side of the EMI filter to the ESD pin. For example, if ESD is applied to Pin A2, then clamping voltage is measured at Pin C2.

### PERFORMANCE INFORMATION

# Typical Filter Performance ( $T_A$ = 25°C, DC Bias = 0 V, 50 $\Omega$ Environment)




Figure 1. Insertion Loss vs. Frequency (A2-C2 to GND B2)




Figure 2. Insertion Loss vs. Frequency (A3-C3 to GND B2)

### PERFORMANCE INFORMATION (Cont'd)

### Typical Filter Performance ( $T_A = 25^{\circ}C$ , DC Bias = 0 V, 50 $\Omega$ Environment)




Figure 3. Insertion Loss vs. Frequency (A4-C4 to GND B2)




Figure 4. Insertion Loss vs. Frequency (A5-C5 to GND B2)

# PERFORMANCE INFORMATION (Cont'd)

# Typical Filter Performance (T<sub>A</sub> = 25 $^{\circ}$ C, 50 $\Omega$ Environment)




Figure 5. Comparison of Filter Response Curves for CM1401-03CS with DC Bias

### **PERFORMANCE INFORMATION (Cont'd)**




Figure 6. Filter Capacitance vs. Input Voltage over Temperature (normalized to capacitance at 2.5 VDC and 25°C)




Figure 7. Resistance vs. Temperature (normalized to resistance at 25°C)

### **APPLICATION INFORMATION**

Table 5. PRINTED CIRCUIT BOARD RECOMMENDATIONS

Parameter	Value		
Pad Size on PCB	0.240 mm		
Pad Shape	Round		
Pad Definition	Non-Solder Mask defined pads		
Solder Mask Opening	0.290 mm Round		
Solder Stencil Thickness	0.125 – 0.150 mm		
Solder Stencil Aperture Opening (laser cut, 5% tapered walls)	0.300 mm Round		
Solder Flux Ratio	50/50 by volume		
Solder Paste Type	No Clean		
Pad Protective Finish	OSP (Entek Cu Plus 106A)		
Tolerance – Edge To Corner Ball	±50 μm		
Solder Ball Side Coplanarity	±20 μm		
Maximum Dwell Time Above Liquidous (183°C)	60 seconds		
Maximum Soldering Temperature for Lead-free Devices using a Lead-free Solder Paste	260°C		




Figure 8. Recommended Non-Solder Mask Defined Pad Illustration





Figure 9. Lead-free (SnAgCu) Solder Ball Reflow Profile

#### PACKAGE DIMENSIONS

### WLCSP15, 2.96x1.33 CASE 567BS-01 ISSUE O



 $\textit{OptiGuard}^{\,\scriptscriptstyle{\text{TM}}}$  is a trademark of Semiconductor Components Industries, LLC (SCILLC).

ON Semiconductor and a registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

#### **PUBLICATION ORDERING INFORMATION**

# LITERATURE FULFILLMENT: Literature Distribution Center for ON Semiconductor

P.O. Box 5163, Denver, Colorado 80217 USA
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81–3–5773–3850 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative