


## Schottky Rectifier, 2 x 7.5 A


**TO-220AB**


### FEATURES

- 150 °C  $T_J$  operation
- Center tap TO-220 package
- Low forward voltage drop
- High frequency operation
- High purity, high temperature epoxy encapsulation for enhanced mechanical strength and moisture resistance
- Guard ring for enhanced ruggedness and long term reliability
- Designed and qualified for industrial level

### DESCRIPTION

The 15CTQ... center tap Schottky rectifier series has been optimized for very low forward voltage drop, with moderate leakage. The proprietary barrier technology allows for reliable operation up to 150 °C junction temperature. Typical applications are in switching power supplies, converters, freewheeling diodes, and reverse battery protection.

### PRODUCT SUMMARY

|             |            |
|-------------|------------|
| $I_{F(AV)}$ | 2 x 7.5 A  |
| $V_R$       | 35 to 45 V |

### MAJOR RATINGS AND CHARACTERISTICS

| SYMBOL      | CHARACTERISTICS                        | VALUES      | UNITS |
|-------------|--|-------------|-------|
| $I_{F(AV)}$ | Rectangular waveform                   | 15          | A     |
| $V_{RRM}$   | Range                                  | 35 to 45    | V     |
| $I_{FSM}$   | $t_p = 5 \mu s$ sine                   | 810         | A     |
| $V_F$       | 7.5 Apk, $T_J = 125^\circ C$ (per leg) | 0.51        | V     |
| $T_J$       | Range                                  | - 55 to 150 | °C    |

### VOLTAGE RATINGS

| PARAMETER                            | SYMBOL    | 15CTQ035 | 15CTQ040 | 15CTQ045 | UNITS |
|--------------------------------------|-----------|----------|----------|----------|-------|
| Maximum DC reverse voltage           | $V_R$     | 35       | 40       | 45       | V     |
| Maximum working peak reverse voltage | $V_{RWM}$ |          |          |          |       |

### ABSOLUTE MAXIMUM RATINGS

| PARAMETER  | SYMBOL      | TEST CONDITIONS   | VALUES  | UNITS |
|--|-------------|---|---|-------|
| Maximum average forward current<br>See fig. 5                                | $I_{F(AV)}$ | 50 % duty cycle at $T_C = 123^\circ C$ , rectangular waveform   | 15  | A     |
| Maximum peak one cycle<br>non-repetitive surge current per leg<br>See fig. 7 | $I_{FSM}$   | 5 $\mu s$ sine or 3 $\mu s$ rect. pulse   | Following any rated load<br>condition and with rated<br>$V_{RRM}$ applied | 810   |
|  |             | 10 ms sine or 6 ms rect. pulse  |   |       |
| Non-repetitive avalanche energy per leg                                      | $E_{AS}$    | $T_J = 25^\circ C$ , $I_{AS} = 1.20$ A, $L = 11.10$ mH  | 10  | mJ    |
| Repetitive avalanche current per leg   | $I_{AR}$    | Current decaying linearly to zero in 1 $\mu s$<br>Frequency limited by $T_J$ maximum $V_A = 1.5 \times V_R$ typical | 1.5   | A     |

| ELECTRICAL SPECIFICATIONS                             |                |  |                                   |        |            |
|---|----------------|--|-----------------------------------|--------|------------|
| PARAMETER   | SYMBOL         | TEST CONDITIONS  |                                   | VALUES | UNITS      |
| Maximum forward voltage drop per leg<br>See fig. 1    | $V_{FM}^{(1)}$ | 7.5 A  | $T_J = 25\text{ }^\circ\text{C}$  | 0.55   | V          |
|   |                | 15 A   |                                   | 0.70   |            |
|   |                | 7.5 A  | $T_J = 125\text{ }^\circ\text{C}$ | 0.51   |            |
|   |                | 15 A   |                                   | 0.65   |            |
| Maximum reverse leakage current per leg<br>See fig. 2 | $I_{RM}^{(1)}$ | $T_J = 25\text{ }^\circ\text{C}$   | $V_R = \text{Rated } V_R$         | 0.8    | mA         |
|   |                | $T_J = 125\text{ }^\circ\text{C}$  |                                   | 32     |            |
| Maximum junction capacitance per leg                  | $C_T$          | $V_R = 5 V_{DC}$ (test signal range 100 kHz to 1 MHz) $25\text{ }^\circ\text{C}$ |                                   | 400    | pF         |
| Typical series inductance per leg                     | $L_S$          | Measured lead to lead 5 mm from package body                                     |                                   | 8.0    | nH         |
| Maximum voltage rate of change                        | dV/dt          | Rated $V_R$  |                                   | 10 000 | V/ $\mu$ s |

**Note**

(1) Pulse width < 300  $\mu$ s, duty cycle < 2 %

| THERMAL - MECHANICAL SPECIFICATIONS                      |                |                                      |  |             |                        |
|--|----------------|--------------------------------------|--|-------------|------------------------|
| PARAMETER  | SYMBOL         | TEST CONDITIONS                      |  | VALUES      | UNITS                  |
| Maximum junction and storage temperature range           | $T_J, T_{Stg}$ |                                      |  | - 55 to 150 | $^\circ\text{C}$       |
| Maximum thermal resistance, junction to case per leg     | $R_{thJC}$     | DC operation<br>See fig. 4           |  | 3.50        | $^\circ\text{C/W}$     |
| Maximum thermal resistance, junction to case per package |                | DC operation                         |  | 1.75        |                        |
| Typical thermal resistance, case to heatsink             | $R_{thCS}$     | Mounting surface, smooth and greased |  | 0.50        |                        |
| Approximate weight                                       |                |                                      |  | 2           | g                      |
|  |                |                                      |  | 0.07        | oz.                    |
| Mounting torque  | minimum        |                                      |  | 6 (5)       | kgf · cm<br>(lbf · in) |
|  | maximum        |                                      |  | 12 (10)     |                        |
| Marking device   |                | Case style TO-220AB                  |  | 15CTQ035    |                        |
|  |                |                                      |  | 15CTQ040    |                        |
|  |                |                                      |  | 15CTQ045    |                        |




Fig. 1 - Maximum Forward Voltage Drop Characteristics (Per Leg)




Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage (Per Leg)




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage (Per Leg)




Fig. 4 - Maximum Thermal Impedance  $Z_{thJC}$  Characteristics (Per Leg)




Fig. 5 - Maximum Allowable Case Temperature vs. Average Forward Current (Per Leg)




Fig. 6 - Forward Power Loss Characteristics (Per Leg)




Fig. 7 - Maximum Non-Repetitive Surge Current (Per Leg)





Fig. 8 - Unclamped Inductive Test Circuit



### ORDERING INFORMATION TABLE



Tube standard pack quantity: 50 pieces

| LINKS TO RELATED DOCUMENTS |   |
|----------------------------|---|
| Dimensions                 | <a href="http://www.vishay.com/doc?95222">http://www.vishay.com/doc?95222</a> |
| Part marking information   | <a href="http://www.vishay.com/doc?95225">http://www.vishay.com/doc?95225</a> |



## Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.