

Cable marking flags - MM-WML-FLAG 6 (20X10)R C1 WH/B - 1116143

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable marking flags, Roll, white/black, unlabeled, can be labeled with: THERMOMARK GO, mounting type: adhesive, lettering field size: 20 x 10 mm, Number of individual labels: 145

Product Description


MM-WML-Flag polyolefin self-adhesive labels are available as prepunched material for wire marking. There are both horizontal and vertical versions.

Your advantages

- ✓ The pre-punched geometry enables easy and convenient use
- ✓ Thanks to the innovative material composition, each label can be printed which results in zero wastage
- ✓ Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon
- ✓ No visible difference between retrospective marking and existing markings created with a desktop roll printer
- ✓ The self-adhesive cable marking flag can be printed on both sides
- ✓ The material is cUL certified
- ✓ High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing



Key Commercial Data

Packing unit	1 pc
GTIN	 4 063151 040444
GTIN	4063151040444
Custom tariff number	96121010
Country of origin	China

Technical data

Dimensions

Length (b)	20 mm
Width (a)	50 mm

Cable marking flags - MM-WML-FLAG 6 (20X10)R C1 WH/B - 1116143

Technical data

Dimensions

Cable diameter	≤ 6 mm
----------------	--------

Ambient conditions

Ambient temperature (operation)	-40 °C ... 60 °C
---------------------------------	------------------

General

Color	white/black
Type	Label
Components	free from silicone, halogen, and cadmium
Material	Polyolefine
Number of individual labels	145
Marking mounting type	adhesive

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27400401
eCl@ss 11.0	27281102
eCl@ss 9.0	27400401

Approvals

Approvals

Approvals

cULus Recognized

Ex Approvals

Approval details

cULus Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	MH48542
------------------	---	---	---------

