

RAFIX 22 FS⁺, compact emergency stop, illuminated, reset by rotating, Mushroom head red, illuminable



fields of application

- > Measurement-control-regulation
- > Electrical engineering
- Mechanical and system engineering
- > Vehicle construction
- > Handheld terminals
- > Industrial robots

special features

- > Emergency stop with compact design
- Low installation depth 9.2 mm (PCB) or 27 mm (QC)
- Connection types: printed circuit board connection (PCB) or plug-in connection (QC)
- PCB switching elements minimize mounting errors
- Switching elements with silver contacts (max. 250 V/4 A) or gold contacts (max. 35 V/100 mA)
- > Degree of protection: IP 65 at the front



description

RAFIX control devices are defined at RAFI as modular elements, consisting of an actuating element, if necessary a coupling and an individual contact or lighting unit.

Actuating elements (such as pushbuttons, emergency stop actuators, etc.) have the intended tactility, reset and function only when assembled with the appropriate switching elements.

The emergency stop buttons correspond to IEC 60 947 and VDE 0113 Part 1. Thanks to a forcibly actuated mechanical motion sequence, they are dupe-proof in accordance with DIN EN ISO 13850. In order to prevent unintentional actuation, a tactile feedback must be overcome. The key switch locks into the pressed position.

The design of the actuator protects the emergency stop button from interlocking. This means that an initiated emergency stop procedure cannot be interrupted by jamming objects.

Only use with the emergency stop switching element.

With the illuminated versions, only the arrows are illuminated.

technical data

>

>	general	
	Disassembly possible	no
	Color of mushroom	red
	Property of bezel / mushroom	opaque

The information in this data sheet only contains general descriptions and / or performance features, which may not apply precisely as described to the respective application, and which my change due to further product enhancements. The technical data, illustrations and other information about our products are the mere results of individual technical testing. These descriptions and other product features are only binding if they expressly agreed upon at the time of the conclusion of a binding contract. In all other cases, we reserve the right to make technical changes as well as changes of availability. Pictures and other graphic illustrations are approximations only. All product names may be trademarks or brand names of the RAFI Group or any other sub-supplier of RAFI. The use of such by any third parties for their own purposes may infringe the rights of the respective entity holding those rights.

RAFI GmbH & Co. KG

technical data sheet

9.30.273.031/2300

	Collar color	yellow
	Collar shape	round
	Operating temperature, min.	-25 °C
	Storage temperature, min.	-40 °C
	Operating temperature, max.	70 °C
	Storage temperature, max.	80 °C
	illuminated	Yes
	Packaging	Box
	Packaging unit	54 pcs.
	Operating life	50,000 cycles
	B10	72,000 cycles
	B10d	144,000 cycles
	Degree of protection, front side, according to DIN EN 60529	IP65
	UL Enclosure Type Rating front	type 1
	side	type 4X
	Environment resistance	IEC 60068-2-14
		IEC 60068-2-30
		IEC 60068-2-33
		IEC 60068-2-78
	Salt-spray resistance according to	IEC 60068-2-11
	standard	F 4
	MOQ order	54 pcs.
	RoHS compliant	Yes
	REACH compliant	Yes
>	mounting diameters	
	• • • • •	
	Mounting hole	22.3 mm
	Mounting depth	9.2 mm
	Mounting depth Installation height	9.2 mm 25.9 mm
	Mounting depth Installation height Grid, min.	9.2 mm 25.9 mm 35 x 35 mm
	Mounting depth Installation height Grid, min. Outside dimension, length	9.2 mm 25.9 mm 35 x 35 mm 29.8 mm
	Mounting depth Installation height Grid, min. Outside dimension, length Outside dimension, width	9.2 mm 25.9 mm 35 x 35 mm 29.8 mm 29.8 mm
	Mounting depth Installation height Grid, min. Outside dimension, length Outside dimension, width Outside dimension, height	9.2 mm 25.9 mm 35 x 35 mm 29.8 mm 29.8 mm 35 mm
	Mounting depth Installation height Grid, min. Outside dimension, length Outside dimension, width Outside dimension, height Collar dimension	9.2 mm 25.9 mm 35 x 35 mm 29.8 mm 29.8 mm
>	Mounting depth Installation height Grid, min. Outside dimension, length Outside dimension, width Outside dimension, height Collar dimension mechanical data	9.2 mm 25.9 mm 35 x 35 mm 29.8 mm 29.8 mm 35 mm Ø 29,8 mm
>	Mounting depth Installation height Grid, min. Outside dimension, length Outside dimension, width Outside dimension, height Collar dimension mechanical data Actuation function	9.2 mm 25.9 mm 35 x 35 mm 29.8 mm 29.8 mm 35 mm ø 29,8 mm
>	Mounting depth Installation height Grid, min. Outside dimension, length Outside dimension, width Outside dimension, height Collar dimension mechanical data Actuation function Operating force, max.	9.2 mm 25.9 mm 35 x 35 mm 29.8 mm 35 mm ø 29,8 mm latching 100 N
>	Mounting depth Installation height Grid, min. Outside dimension, length Outside dimension, width Outside dimension, height Collar dimension mechanical data Actuation function Operating force, max. Resetting	9.2 mm 25.9 mm 35 x 35 mm 29.8 mm 29.8 mm 35 mm ø 29,8 mm latching 100 N by rotating
>	Mounting depth Installation height Grid, min. Outside dimension, length Outside dimension, width Outside dimension, height Collar dimension mechanical data Actuation function Operating force, max.	9.2 mm 25.9 mm 35 x 35 mm 29.8 mm 35 mm ø 29,8 mm latching 100 N

RAFI

direct links

> RAFI eCatalog

RAFI GmbH & Co. KG


technical data sheet






drawings

System drawing



System drawing



The information in this data sheet only contains general descriptions and / or performance features, which may not apply precisely as described to the respective application, and which my change due to further product enhancements. The technical data, illustrations and other information about our products are the mere results of individual technical testing. These descriptions and other product features are only binding if they expressly agreed upon at the time of the conclusion of a binding contract. In all other cases, we reserve the right to make technical changes as well as changes of availability. Pictures and other graphic illustrations are approximations only. All product names may be trademarks or brand names of the RAFI Group or any other sub-supplier of RAFI. The use of such by any third parties for their own purposes may infringe the rights of the respective entity holding those rights. **date**: Jul 25, 2022 **page**: 3/5


RAFI GmbH & Co. KG

technical data sheet






Mounting hole drawing



acc. to IEC 60947-5-1

front panel drawing



RAFI GmbH & Co. KG

technical data sheet 9.30.273.031/2300



mounting

RAFIX 16, RAFIX 22 FS⁺, RAFIX 22 FSR, RAFIX 22 QR

Betriebsanleitung Not-Halt-Befehlsgeräte

Operating Instructions EMERGENCY STOP **Control Units**

D 1. Sicherheitshinweise Vor Inbetriebnahme bitte Betriebsanleitung sorofältig lesen

<u>^</u>: Nor-Halt-Befehlsgeräte erfüllen eine Personenschutz-Funktion. Unsachgemäßer Einbau, sach-widrige Anwendung oder Manipulationen können zu schweren Verletzungen von Personen führen!

- \wedge Not-Halt-Befehlsgeräte dürfen nicht umgangen, entfernt oder auf andere Weise unwirksam gemacht werden!
 - Vor Beginn der Installation Anlage und Gerät spannungsfrei schalten! Vor Erst-Inbetriebnahme der Maschine oder Anlage Not-Halt-Befehlsgerät durch Testbetätigung auf korrekte Montage und Funktion überprüfen.
- \wedge
- ⚠
- Not-Halt-Befehlsgeräte mit sichtbaren Beschädigungen sind unverzüglich auszutauschen. \wedge Not-Halt-Funktion darf nicht als Ersatz für Schutzmaßnahmen oder andere Sicherheitsfunk
- tionen verwendet werden. Not-Halt-Funktion darf die Wirksamkeit von Schutzreinrichtungen oder von Einrichtungen mit <u>A</u>
 - anderen Sicherheitsfunktionen nicht beeinträchtigen.

(B) 1. Safety instructions

- Please read the operating instructions carefully prior to use.
 EMERGENCY STOP control units are designed to protect persons. Inappropriate installation,
 improper use or inadmissible manipulation may result in severe injuries!
- improper use or inadmissible manipulation may result in severe injurius: EMERGENCY STOP control units must never be bypassed, removed or disabled in any other wayl
- Disconnect the power supply to the machinery and device prior to installation!
 - Operate the EMERGENCY STOP control unit to test and verify proper installation and function prior to initial start-up of the machine or line.

 - The emergency stop function must not be been about the emergency stop functions. The emergency stop function is not to be used for safety measures or safety functions. The emergency stop function must not compromise the effectiveness of safety devices or devices with other safety functions.

Consignes de sécurité

- Il faut soigneusement lire le mode d'emploi avant la mise en service. Les auxiliaires de commande d'ARRÊT D'URGENCE remplissent une fonction de protection per sonnelle. Un montage inapproprié, une application contre-indiquée ou une manipulation peuvent
- auser des blessures corporelles graves! Lest interdit de ponter, d'enlever ou de rendre inopérants les auxiliaires de commande d'ARRÊT
- URGENCE! Avant d'entamer l'installation il faut mettre l'installation et l'appareil hors tension!
- AVant de Brieffer installation induit neuer installation et apparair nos ensurant Avant la première mise en service de la machine ou de l'installation, contrôler l'auxiliaire de commande d'ARRÊT D'URGENCE quant au montage et à un fonctionnement corrects. Les auxiliaires de commande d'ARRÊT D'URGENCE présentant des dommages visibles sont à
- remplacer sans tarder.
- La fonction d'arrêt d'urgence ne peut pas être utilisée en remplacement de mesures de protec-
- La fonction d'arte d'urgence ne peut pas ene dunace en emplacement de mesures de por tion ou d'autres fonctions de sécurité. La fonction d'arte d'urgence ne peut pas entraver l'efficacité de dispositifs de sécurité ou dispositifs possédant d'autres fonctions de sécurité

D 2. Allgemeine Beschreibung und bestimmungsgemäße Verwendung

- Not-Halt-Befehlsgeräte sind elektromechanische Schaltgeräte zum Schutz von Personen. Sie dienen der schnellen Abschaltung um Maschinen, Fahrzeuge und Anlagen in einen sicheren Zu-stand zu bringen, um Gefahren und Schäden für Mensch und Maschine zu vermeiden oder zu verringern.
- Für die Inbetriebnahme, den Einsatz und technischen Überprüfungen gelten im speziellen folgen-de Vorschriften:
- Die Maschinenrichtlinie 2006/42/EG
- Die Sicherheitsvorschriften sowie
 Die Unfallverhütungsvorschriften / Sicherheitsregeln
- Hersteller und Benutzer von Maschinen, an denen Not-Halt-Befehlsgeräte eingesetzt werden, tra-
- gen die Verantwortung für die Beachtung der Betriebsanleitung, wie auch für die Einhaltung der für sie geltenden Sicherheitsvorschriften und -regeln.
- Für den Einbau und Betrieb von Not-Halt-Befehlsgeräten müssen zur bestimmungsgemäßen werden: Sind verlieb von rochtart-Befehlsgeräten müssen zur bestimmungsgemäßen Verwendung folgende Anforderungen beachtet und eine Gefahrenbewertung durchgeführt werden:
- EN ISO 13849-1:2015 - EN ISO 13850:2015 - EN 60204-1/A1:2009 EN ISO 13849-2:2012

(GB) 2. General description and intended use

EMERGENCY STOP control units are electromechanical switching devices designed to protect persons. They are used for instant disconnection to achieve a safe status of machines, vehicles or other equipment in order to avoid or reduce risks or damage to man and machine. The following standards and regulations apply to their start-up, use and technical inspections, without limitation:

- Machinery Directive 2006/42/EC
- Safety standards
 Accident prevention regulations / rules for safety

Manufacturers and users of machines provided with EMERGENCY STOP control units are respon sible for ensuring that the operating instructions are observed and the applicable safety standards and rules complied with.

For the installation and operation of EMERGENCY STOP control devices in line with the intended

Pol Itel Histanauorano operation of Enziperatori of construction and the matter use, the following requirements must be observed and a risk assessment must be performed – EN ISO 13849-12015 – EN ISO 13850:2015 – EN ISO 13849-22012 – EN 60204-1/A1:2009

- Mode d'emploi auxiliaires de commande d'ARRÊT D'URGENCE (F) 2. Description générale et application conforme aux prescriptions
 - Les auxiliaires de commande d'ARRÊT D'URGENCE sont des appareils de commutation élec-tromécaniques pour protéger des personnes. Ils servent à couper rapidement les machines, les véhicules et les installations, à les amener dans un état de sécurité fiable pour éviter ou diminuer
 - les risques de dommages corporels et de dégâts matériels. Pour la mise en service, l'utilisation et les contrôles techniques, il faut respecter les prescriptions suivantes:
 - La directive sur les machines selon la norme 2006/42/EG
 - Les règlements de sécurité ainsi que
 - Les instructions sur la prévention des accidents / règlements de sécurité
 - C'est aux fabricants et utilisateurs de machines où des auxiliaires de commande d'ARRÊT D'URGENCE sont utilisés, qu'incombe la responsabilité du respect du mode d'emploi ainsi que des prescriptions et règlements de sécurité en vigueur.
 - bour l'instalation et l'exploitation de dispositifs d'ARRÊT D'URGENCE, les exigences suivantes doivent être respectées et une évaluation des risques doit être menée en vue d'une utilisation en bonne et due forme:
 - EN ISO 13849-1:2015 - EN ISO 13850-2015
 - EN ISO 13849-2:2012 - EN 60204-1/A1:2009

D 3. Produktbeschreibung

- Aufbau: Die Not-Halt-Befehlsgeräte bestehen aus einer Kombination von Betätigern mit einem oder mehreren Schaltelementen. Die Not-Halt-Befehlsgeräte gibt es als Einbauversion oder in
- einem Gehäuse verbaut. Die Betätigung erfolgt durch Drücken, die Entriegelung erfolgt je nach Variante entweder durch: - Drehbewegung nach links oder nach rechts
- Ziehen entgegen der Betätigungsrichtung
 "Aktiv/Inaktiv"-Varianten: "Aktiv": beleuchtet, rot, Not-Halt Funktion gegeben; "Inaktiv": unbe-leuchtet, transparent, keine Not-Halt Funktion.

(GB) 3. Product description

Design: An EMERGENCY STOP button is an assembly of actuator combined with one or more contact blocks. EMERGENCY STOP buttons are available either as a panel mounting version installed in a separate housing.

- They are operated by pressing. Unlatching is done by one of two methods

- Furning clockwise or counter clockwise
 Pulling against the direction of operation
 "Aktiv/Inaktiv"-Variants: "Aktiv": illuminated red, Emergency Stop function given; "Inaktiv": not illuminated, transparent, no Emergency Stop function

(F) 3. Description de produit

Structure: Les boutons-pousoirs d'ARRÊT D'URGENCE sont composés d'une combinaison d'actionneurs ou de plusieurs éléments de commutation. Les boutons-poussoirs d'ARRÊT D'URGENCE sont disponibles en version intégrable ou installés dans un boîtier

L'actionnement s'effectue par appui sur ces derniers. Selon la variante, le déverrouillage s'effectue soit par:

- Un mouvement de rotation, soit vers la gauche, soit à droite

- Soit en tirant dans la direction opposée de la direction d'actionnement "Aktiv/Inaktiv"-Variantes: "Aktiv": lit rouge, d'arrêt d'urgence fonction donné; "Inaktiv": pas lit, transparent, pas de d'arrêt d'urgence fonction.

Produkt Product Produit	Einbau Ømm Mounting Ømm Montage Ømm	Betätiger Actuator Actionneur	Schaltelement Contact block Elément de commutation
RAFIX 16	Ø 16,2	1.30.074.xxx/xxxx 9.30.074.xxx/xxxx	1.20.123.xxx/xxxx
RAFIX 16 F	23,1	1.30.094.xxx/xxxx	9.20.123.xxx/xxxx
	Ø 22,3	9.30.094.xxx/xxxx	
RAFIX 22 QR	Ø 22,3	1.30.243.xxx/xxxx 9.30.243.xxx/xxxx	5.00.100.xxx/xxxx 1.20.124.xxx/xxxx 1.20.125.xxx/xxxx 9.20.124.xxx/xxxx 9.20.125.xxx/xxxx
RAFIX 22 FS	Ø 22,3	1.30.253.xxx/xxxx 9.30.253.xxx/xxxx	1.20.126.xxx/xxxx 9.20.126.xxx/xxxx
RAFIX 22 FS ⁺	Ø 22,3	1.30.273.xxx/xxxx 9.30.273.xxx/xxxx	1.20.126.xxx/xxxx 9.20.126.xxx/xxxx
RAFIX 22 FSR	Ø 22,3	1.30.283.xxx/xxxx 9.30.283.xxx/xxxx	1.20.126.xxx/xxxx 9.20.126.xxx/xxxx

D Tabelle 3.1 Weitere technische Daten sind dem Katalog zu entnehmen

(B) Table 3.1 For additional technical data, please refer to the catalogue

F Tableau 3.1 Pour les autres caractéristiques techniques, voir catalogue

The information in this data sheet only contains general descriptions and / or performance features, which may not apply precisely as described to the respective application, and which my change due to further product enhancements. The technical data, illustrations and other information about our products are the mere results of individual technical testing. These descriptions and other product features are only binding if they expressly agreed upon at the time of the conclusion of a binding contract. In all other cases, we reserve the right to make technical changes as well as changes of availability. Pictures and other graphic illustrations are approximations only. All product names may be trademarks or brand names of the RAFI Group or any other sub-supplier of RAFI. The use of such by any third parties for their own purposes may infringe the rights of the respective entity holding those rights. date: Jul 25, 2022 $\ page:$ 5/5

RAFI GmbH & Co. KG

Ravensburger Str. 128-134 88276 Berg / Ravensburg Germany . www.rafi-group.com info.headquarters@rafi-group.com

		١
<u> </u>	-	[
	-	
~		ķ
/!\	-	,
\wedge	-	-
		(
F	1	. '
\sim		I
$\mathbf{\Lambda}$	-	l

⚠

