

### **Features**

- ESD Protection for 1 line with Unidirectional
- Provide ESD protection for the protected line to IEC 61000-4-2 (ESD) ±30kV (air), ±30kV (contact)
   IEC 61000-4-4 (EFT) ±80A (5/50ns)
   IEC 61000-4-5 (Lightning) 12A (8/20μs)
- Suitable for, 7.0V and below, operating voltage applications
- 0402 small DFN package saves board space
- Protect one I/O line or one power line
- Fast turn-on and low clamping voltage
- Solid-state silicon-avalanche and active circuit triggering technology
- Green part

### **Applications**

- Power Supply Protection
- Power Management
- USB Vbus Protection
- Industrial Application
- Portable Devices
- Hand Held Portable Applications
- Data and I/O lines protection
- Cellular Handsets and Accessories
- Notebooks, desktops, and servers
- Peripherals

### **Description**


AZ4107-01F is a design which includes a unidirectional ESD rated clamping cell to protect one power line, or one control line, or one low speed data line in an electronic system. The AZ4107-01F has been specifically designed to protect sensitive components which are connected to power and control lines from

over-voltage damage caused by Electrostatic Discharging (ESD), Electrical Fast Transients (EFT), Lightning, and Cable Discharge Event (CDE).

AZ4107-01F is a unique design which includes proprietary clamping cell in a single package. During transient conditions, the proprietary clamping cell prevents over-voltage on the power line or control/data lines, protecting any downstream components.

AZ4107-01F may be used to meet the ESD immunity requirements of IEC 61000-4-2, Level 4 (±15kV air, ±8kV contact discharge).

## Circuit Diagram / Pin Configuration





### **SPECIFICATIONS**

ABSOLUTE MAXIMUM RATINGS				
PARAMETER	SYMBOL	RATING	UNITS	
Peak Pulse Current (tp=8/20μs)	I <sub>PP</sub>	12	А	
Operating Supply Voltage (pin-1 to pin-2)	$V_{DC}$	7.7	V	
ESD per IEC 61000-4-2 (Air)	V <sub>ESD-1</sub>	±30	kV	
ESD per IEC 61000-4-2 (Contact)	$V_{ESD-2}$	±30		
Lead Soldering Temperature	T <sub>SOL</sub>	260 (10 sec.)	°C	
Operating Temperature	T <sub>OP</sub>	-55 to +85	°C	
Storage Temperature	T <sub>STO</sub>	-55 to +150	°C	


ELECTRICAL CHARACTERISTICS						
PARAMETER	SYMBOL	CONDITIONS	MINI	TYP	MAX	UNITS
Reverse	$V_{RWM}$	Pin 1 to nin 2 T_25 °C			7.0	V
Stand-Off Voltage	V RWM	Pin-1 to pin-2, T=25 °C.			7.0	V
Reverse Leakage	1	V <sub>RWM</sub> = 7V, T=25 °C, pin-1 to			0.1	
Current	l <sub>Leak</sub>	pin-2.			0.1	μΑ
Reverse						
Breakdown	$V_{BV}$	$I_{BV} = 1$ mA, T=25 °C, pin-1 to pin-2.	8		10.5	V
Voltage						
Forward Voltage	$V_{F}$	$I_F = 15$ mA, T=25 °C, pin-2 to pin-1.	0.6		1.2	V
Surge Clamping Voltage	$V_{CL ext{-surge}}$	I <sub>PP</sub> =5A, tp=8/20μs, T=25 °C, pin-1 to pin-2.		9.2		V
ESD Clamping Voltage (Note 1)	V <sub>clamp</sub>	IEC 61000-4-2 +8kV (I <sub>TLP</sub> = 16A), Contact mode, T=25 °C, pin-1 to pin-2.		10		V
ESD Dynamic		IEC 61000-4-2 0~+8kV, T= 25 °C,				
Turn-on	R <sub>dynamic</sub>	Contact mode, pin-1 to pin-2.		0.1		Ω
Resistance						
Channel Input	$C_{IN}$	$V_R = 0V$ , $f = 1MHz$ , $T=25$ °C, pin-1		160	200	рF
Capacitance	- 114	to pin-2.			=55	F .


Note 1: ESD Clamping Voltage was measured by Transmission Line Pulsing (TLP) System.


TLP conditions:  $Z_0$ = 50 $\Omega$ ,  $t_p$ = 100ns,  $t_r$ = 1ns.




### **Typical Characteristics**













# Mechanical Details DFN1006P2X PACKAGE DIAGRAMS








### **PACKAGE DIMENSIONS**

Symbol	Millin	neters	Inches		
	min	max	min	max	
Α	0.95	1.05	0.037	0.041	
В	0.55	0.65	0.022	0.026	
С	0.41	0.55	0.016	0.022	
D	0.45		0.018		
E	0.20	0.30	0.008	0.012	
F	0.45	0.55	0.018	0.022	


### LAND LAYOUT



#### Notes:

This LAND LAYOUT is for reference purposes only. Please consult your manufacturing partners to ensure your company's PCB design guidelines are met.

### **MARKING CODE**



**Top View** 

k = Device Code

Part Number	Marking Code		
AZ4107-01F.R7GR (Green Part)	k		

Note. Green means Pb-free, RoHS, and Halogen free compliant.

4



**Ordering Information** 

PN#	Material	Type	Reel size	MOQ	MOQ/internal box	MOQ/carton
AZ4107-01F.R7GR	Green	T/R	7 inch	12,000/reel	4  reels = 48,000/box	6 boxes = 288,000/carton

**Revision History** 

Revision	Modification Description
Revision 2015/04/27	Preliminary Release.
Revision 2017/05/15	Formal Release.