

SPECIFICATION SHEET


| | 00211 0004020000001 |
|-------------------------|---|
| SPECIFICATION SHEET NO. | Q0211- CR0402PC0RS001 |
| | |
| DATE | Feb. 11, 2023 |
| | A1 |
| REVISION | AI |
| DESCRIPITION | Thick Film Chip Resistors, 0402 (1005 Metric), CR02 Series, |
| | Dimension L1.00*W0.50*H0.35mm, 2 Terminations |
| | |
| | Tolerance: Jumper, Resistance 0ohm, Dissipation Max. 1/16W @ 70°C |
| | Temperature Coefficient Rate (TCR) : -200~+400ppm/°C |
| | Operating Temp. Range -55°C ~+155°C |
| | Package in Tape/Reel, 10,000pcs/Reel |
| | RoHS/RoHS III compliant and HF |
| CUSTOMER | |
| CUSTOMER PART NUMBER | |
| CROSS REF. PART NUMBER | |
| ORIGINAL PART NUMBER | Aillen CR02PC0R |
| PART CODE | CR0402PC0RS001 |

| VENDOR APPROVE | | | |
|-------------------------|---------------------------------------|---|----------------------|
| Issued/Checked/Approved | Component Component Mandy Xu | Comporte Comporte Comporte Caller Comporte Compo | Jack Jack Jack |
| DATE: Feb. 11, 2023 | | | |
| | | | |
| CUSTOMER APPROVE | | | |
| | | | |

DATE:

2/11/2023

1



THICK FILM CHIP RESISTORS CR02 SERIES

DESCRIPTION

The resistors are constructed in a high grade ceramic body (aluminum oxide). Internal metal electrodes are added at each end and connected by a resistive paste that is applied to the top surface of the substrate. The composition of the paste is adjusted to give the approximate resistance required and the value is trimmed to within tolerance by laser cutting of this resistive layer. The resistive layer is covered with a protective coat. Finally, the two external end terminations are added. For ease of soldering the outer layer of these end terminations is a Tin (lead free) alloy.

MAIN FEATURE

- High Reliability And Stability
- Reduced Size Of Final Equipment
- Lower Assembly Costs
- Higher Component And Equipment Reliability
- RoHS III Compliant And Halogen Free Products

APPLICATION

- Consumer Electrical Equipment
- EDP, Computer Application
- Telecom Application

PART CODE GUIDE

| CODE GUI | Request For Quotation | | | | |
|----------|-----------------------|---|---|----|------|
| CR | 0402 | Р | С | OR | S001 |
| 1 | 2 | 3 | Д | 5 | 6 |

1) CR: Product code for Thick Film Chip Resistors

2) 0402: Size Code, 0402 (1005 Metric), CR02 Series, Dimensions L1.00*W0.50*H0.35mm

3) P: Resistance Range Tolerance Code, P: Jumper; B: +/-0.1%; D: +/-0.5%; F: +/-1%; J: +/-5%

4) C: Package Code, A: 4Kpcs/7"Reel; B:5kpcs/7"Reel; C:10kpcs/7"Reel; M:15kpcs/7"Reel; D:10kpcs/10"Reel; E:20kpcs/10"Reel; D:10kpcs/10"Reel; D:10kpcs/10"Ree

5) OR: Resistance value code. OR: 0ohm; 1R2: 1.2ohm; 15R: 15ohm; 20R: 20ohm; 39R: 39ohm; 51R: 51ohm; 240R: 240ohm;

390R: 390ohm; 1K:1Kohm; 10K: 10Kohm; 15K: 15 Kohm;10K5: 10.5Kohm; 1K21: 1.21Kohm; 4K7: 4.7Kohm; 100K: 100Kohm;

226K: 226Kohm; 1M: 1.0Mohm; 1M2: 1.2Mohm

6) S001: Internal control code, digits and letter; Blank: N/A

2/11/2023

NextGen Components, Inc.



RFC





THICK FILM CHIP RESISTORS CR02 SERIES

DIMENSION (Unit: mm)

Image for reference




General Marking: Blank

CR02 series


Resistors Construction

For Reference



| Item | Dimension | | |
|------|-----------|--|--|
| L | 1.00±0.05 | | |
| w | 0.50±0.05 | | |
| т | 0.35±0.05 | | |
| Тb | 0.25±0.10 | | |
| Τt | 0.20±0.10 | | |





| ltem | Dimension | |
|------|-----------|--|
| W | 0.50~0.60 | |
| L | 1.40~1.60 | |
| D | 0.40~0.60 | |

2/11/2023

NextGen Components, Inc.

D,



THICK FILM CHIP RESISTORS CR02 SERIES

GENERAL ELECTRONICAL CHARACTERISTICS

| | Item | Unit | Symbol | Characteristic | Condition |
|------------------------|----------------------|--------|--------|-------------------------------------|-------------|
| Pro | Product Name | | CR | Thick Film Chip Resistors | |
| Size | | | 0402 | CR02 Series, L1.00*W0.50*H0.35mm | |
| Resis | stance Range | Ω | | 0 | |
| Resista | Resistance Tolerance | | Р | Jumper | |
| TCR | 10MΩ≥ R>10Ω | ppm/°C | | ≤ ±100 | |
| | R≤10Ω | | | -200~+400 | |
| Max | . Dissipation | W | | 1/16 | @ Tamb=70°C |
| Operati | ng Temperature | °C | | -55 ~+155 | |
| Max. Operation Voltage | | V | | 50 | @DC or RMS |
| Max. Ov | verload Voltage | V | | 100 | @DC or RMS |

Note

1) This is the maximum voltage that may be continuously supplied to the resistor element, see "IEC publication 60115-8"

2) Max. Operation Voltage : So called RCWV (Rated Continuous Working Voltage) is determined by

RCWV = $\sqrt{Rated Power \times Resistance Value}$ or Max. RCWV listed above, whichever is lower.

3) Test condition for jumper (0 Ω)

| Item | Unit | Symbol | Characteristic | Condition |
|-----------------------|------|--------|----------------|-----------|
| Power Rating At 70°C | W | | 1/16 | |
| Max. Resistance | mΩ | | 50 | |
| Rated Current | А | | 1.0 | |
| Peak Current | А | | 2.0 | |
| Operating Temperature | °C | | -55 ~+155 | |



THICK FILM CHIP RESISTORS CR02 SERIES

PRODUCT CHARACTERIZATION

Standard values of nominal resistance are taken from the E24 & E96 series for resistors with a tolerance Of +/-0.1%, +/-0.5%, +/-1% & +/-5%, The values of the E24/E96 series are in accordance with "IEC publication 60063"

DERATING

The power that the resistor can dissipate depends on the operating temperature; see Fig.1




Fig 1 Maximum dissipation in percentage of rated power as a function of the ambient temperature for CR06, CR03, CR03, CR02

MOUNTING

Due to their rectangular shapes and small tolerances, Surface Mountable Resistors are suitable for handling by automatic placement systems. Chip placement can be on ceramic substrates and printed-circuit boards (PCBs). Electrical connection to the circuit is by individual soldering condition. The end terminations guarantee a reliable contact.

STORAGE AND HANDLING CONDITIONS

1) Products are recommended to be used up within two years since operation date as ensured shelf life. Check solderability in case shelf life extension is needed.

2) To store products with following condition: Temperature : 5 to 40°C Humidity: 20 to 70% relative humidity

3) Don't store products in a corrosive environment such as sulfide, chloride gas, or acid. It may cause oxidization of electrode, which easily be resulted in poor soldering b.To store products on the shelf and avoid exposure to moisture. Don't expose products to excessive shock, vibration, direct sunlight and so on.

2/11/2023



THICK FILM CHIP RESISTORS CR02 SERIES

REFLOW SOLDERING CONDITION

The robust construction of chip resistors allows them to be completely immersed in a solder bath of 260 °C for 10 seconds. Therefore, it is possible to mount Surface Mount Resistors on one side of a PCB and other discrete components on the reverse (mixed PCBs). Surface Mount Resistors are tested for solderability at 235 °C during 2 seconds. The test condition for no leaching is 260°C for 30 seconds. Typical examples of soldering processes that provide reliable joints without any damage are given in Fig 2.




Fig 2. Infrared soldering profile for Chip Resistors

TEST AND REQUIREMENTS

Essentially all tests are carried out according to the schedule of IEC publication 115-8, category LCT/UCT/56(rated temperature range: Lower Category Temperature, Upper Category Temperature; damp heat, long term, 56 days). The testing also meets the requirements specified by EIA, EIAJ and JIS. The tests are carried out in accordance with IEC publication 68, "Recommended basic climatic and mechanical robustness testing procedure for electronic components" and under standard atmospheric conditions according to IEC 60068-1, subclause 5.3. Unless otherwise specified, the following value supplied Temperature: 15 °C to 35 °C. Relative humidity: 45% to 75%. Air pressure: 86kPa to 106 kPa (860 mbar to 1060 mbar). All soldering tests are performed with midly activated flux.

2/11/2023



THICK FILM CHIP RESISTORS CR02 SERIES

TEST AND REQUIREMENT (JIS C 5201-1: 1998)

| TEST | PROCEDURE / TEST METHOD | REQUIREME | NT |
|-----------------------|---|------------------------|----------|
| | | Resistor | Ω0 |
| Electrical | - DC resistance values measurement | Within the | <50mΩ |
| Characteristics | - Temperature Coefficient of Resistance (T.C.R) | specified tolerance | |
| JISC5201-1: 1998 | Natural resistance change per change in degree | Refer to "QUICK | |
| Clause 4.8 | centigrade. $\frac{R_2 - R_1}{R_1(t_2 - t_1)} \times 10^6 \text{ (ppm/°C)}$ | REFERENCE DATA" | |
| | t1 : 20°C+5°C-1°C; t2 : -55°C or +155°C | | |
| | R1 : Resistance at reference temperature | | |
| | (20°C+5°C/- 1°C) | | |
| | R2: Resistance at test temperature (-55°C or +155°C) | | |
| Resistance To | Un-mounted chips completely immersed for 10±1 | ±5%: ΔR/R max. | <50mΩ |
| Soldering Heat(R.S.H) | second in a SAC solder bath at 260°C±5°C | ±(1%+0.05Ω); | |
| JISC5201-1:1998 | | ±1%: ΔR/R max. | |
| Clause 4.18 | | ±(0.5%+0.05Ω) | |
| | | no visible damage | |
| Solderability | Un-mounted chips completely immersed for 2±0.5 | 95% coverage min., g | good |
| JISC5201-1: 1998 | second in a SAC solder bath at 235°C±5°C | tinning and no visible | e damage |
| Clause 4.17 | | | |
| Temperature cycling | 30 minutes at -55°C±3°C, 2~3 minutes at 20°C+5°C- | ±5%: ΔR/R max. | <50mΩ |
| JISC5201-1: 1998 | 1°C, 30 minutes at +125°C±3°C, 2~3 minutes at | ±(1%+0.05Ω); | |
| Clause 4.19 | 20°C+5°C1°C, total 5 continuous cycles | ±1%: ΔR/R max. | |
| | | ±(0.5%+0.05Ω) | |
| | | no visible damage | |
| High Temperature | 1000+48/-0 hours; without load in a temperature | ±5%: ΔR/R max. | <50mΩ |
| Exposure | chamber controlled 155 3 C | ±(2%+0.1Ω); | |
| MIL-STD-202 | | ±1%: ΔR/R max. | |
| method 108 | | ±(1%+0.1Ω) | |
| | | no visible damage | |


2/11/2023



THICK FILM CHIP RESISTORS CR02 SERIES

TEST AND REQUIREMENT (JIS C 5201-1: 1998)


| TEST | PROCEDURE / TEST METHOD | REQUIREME | NT |
|--|---|--|-------|
| | | Resistor | 0Ω |
| Bending strength JISC5201-1: 1998 | Resistors mounted on a 90mm glass epoxy resin PCB(FR4), bending once 3mm for 10sec, 5mm for | ±5%: ΔR/R max. ±(1%+0.05Ω); | <50mΩ |
| Clause 4.33 | CR02 | ±1%: ΔR/R max. ±(1%+0.05Ω) no visible damage | |
| Adhesion JISC5201-1: 1998 Clause 4.32 | Pressurizing force: 5N, Test time: 10±1sec | No remarkable dama removal of the termin | |
| Short Time Overload (STOL) JISC5201-1: 1998 Clause 4.13 | 2.5 times RCWV or max. overload voltage, for 5seconds | ±5%: ΔR/R max. ±(2%+0.05Ω); ±1%: ΔR/R max. ±(1%+0.05Ω) no visible damage | <50mΩ |
| Load life in Humidity JISC5201-1: 1998 Clause 4.24 | 1000 +48/-0 hours, loaded with RCWV or Vmax in humidity chamber controller at 40 C 2 C and 90~95% relative humidity, 1.5hours on and 0.5 hours off | ±5%: ΔR/R max. ±(2%+0.1Ω); ±1%: ΔR/R max. ±(1%+0.1Ω) no visible damage | <50mΩ |
| Load life (endurance) JISC5201-1: 1998 Clause 4.25 | 1000 +48/-0 hours, loaded with RCWV or Vmax in chamber controller 70±2ºC, 1.5 hours on and 0.5 Hours off | ±5%: ΔR/R max. ±(3%+0.1Ω); ±1%: ΔR/R max. ±(1%+0.1Ω) no visible damage | <50mΩ |
| Insulation Resistance JISC5201-1: 1998 Clause 4.6 | Apply the maximum overload voltage (DC) for 1minute | R ≥ 10GΩ | |
| Dielectric Withstand Voltage JISC5201-1: 1998 | Apply the maximum overload voltage (AC) for 1 minute | No breakdown or flas | hover |
| Clause 4.7 | | | 8 |



THICK FILM CHIP RESISTORS CR02 SERIES


REEL DIMENSION (Unit: mm)

7": 10,000Ppcs/Reel



| Code | Dimension 7" | Dimension 10" | Dimension 13" |
|------|-----------------|------------------|------------------|
| Α | 178.0+/-2.0 | 254.0+/-2.0 | 330.0+/-2.0 |
| В | 60.0 +/-1.0 | 100 +/-1.00 | 100+/-1.00 |
| С | 13.0+/-0.20 | 13.0+/-0.20 | 13.0+/-0.20 |
| Т | 9.00+/-0.50 | 9.00+/-0.50 | 9.00+/-0.50 |

TAPE DIMENSION (Unit: mm)



| Code | Dimension |
|------|------------|
| А | 1.20±0.10 |
| В | 0.70±0.10 |
| W | 8.00±0.30 |
| F | 3.50±0.20 |
| E | 1.75±0.10 |
| P 1 | 2.00±0. 10 |
| PO | 4.00±0.10 |
| ΦD | 1.50±0.10 |
| Т | 0.45±0.05 |

TAPING QUANTITY AND TAPE MATERIAL

| Таре | Paper Tape | | | | | Embossed Tape | Bulk Cassette | |
|-----------|------------|------------|-----|-------|------------|---------------|---------------|-------|
| | | 4 mm Pitch | | | 2 mm Pitch | ı | 4 mm Pitch | |
| Reel Size | 7″ | 10" | 13″ | 7" | 10" | 13" | 7" | |
| CR02 | - | - | - | 10000 | 20000 | 40000 | - | 50000 |




THICK FILM CHIP RESISTORS CR02 SERIES

PERFORMANCE OF TAPING

Strength of Carrier Tape and Top Cover Tape

Carrier Tape: When a tensile force 1.02kgf is applied in the direction of unreeling the tape, the tape shall withstand this force. Top cover Tape: When a tensile force 1.02kgf is applied to the tape, the tape shall withstand this force. Peel Force of Top Cover Tape

Unless otherwise specified, the peel force of top cover tape shall be 10.2 to 71.4 g f when the top cover tape is pulled at a speed of 300mm/min with the angle between the taped during peel and the direction of unreeling maintained at 165 to 180°as illustrated in Fig.



DISCLAIMER

NextGen Component, Inc. reserves the right to make changes to the product(s) and or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information

2/11/2023