

8W Isolated DC-DC Power Module

ATMV24V100V80MA1



Figure 1. Top View of ATMV24V100V80MA1



Figure 3. Side View

FEATURES

- Wide Input Power Voltage Range: 18V to 36V
- Output Voltage: 100V
- Max. Output Current: 80mA
- High Efficiency: 78%

 $@V_{\text{IN}} = 24V \ \& \ V_{\text{OUT}} = 100V \ \& \ I_{\text{OUT}} = 80 \text{mA}$

- Output Ripple Voltage: ±1% @20MHz
- Isolation Voltage: 1500VDC
- Output Short-Circuit Protection: Automatic Recovery
- Full Aluminum Housing for Complete Shielding
- Industry Standard DIP Package
- Operating Temperature Range: -40°C ~ +85°C
- 100 % Lead (Pb)-free and RoHS Compliant








Figure 4. Bottom View

APPLICATIONS

This power module, ATMV24V100V80MA1, is designed for achieving DC-DC conversion from low voltage to high voltage as a power supply source. It is widely used in scientific research and other fields including:


- Sustaining Ion Pumps
- Spectral Analysis
- Electrophoresis
- Particle Accelerator
- Capillary Electrophoresis
- Piezo Devices
- Photo Multiplier Tubes
- Avalanche Photo Diodes



DESCRIPTION

This Power Module is a medium voltage, isolated DC–DC converter with 2:1 input voltage range. With a wide operating temperature range, built in short-circuit protection, providing this unit with high reliability and long life.

NAMING PRINCIPLE



Naming Principle of ATMV24V100V80MA1

Table 1. Pin Names, Functions and Specifications.

No.	Name	Туре	Description		Тур.	Max.
1	$V_{\rm IN-}$	Input	Negative Input Voltage		0V	
2	$V_{\rm IN+}$	Input	Positive Input Voltage	18V	24V	36V
3	V_{OUT+}	Output	Positive Output Voltage			100V
4	NP		-			
5	V _{OUT-}	Output	Negative Output Voltage		0V	

SPECIFICATIONS

Table 2.

Parameter	Symbol	Test Conditions	Min.	Тур.	Max.	Unit/Note
Input Voltage	$V_{\rm IN}$		18	24	36	V
Input Quiescent Current	I_{IN_QC}	$I_{OUT} = 0mA$		27		mA
Input Current	\mathbf{I}_{IN}	$I_{OUT} = 80 \text{mA}$		400		mA
Leakage Current	I_L			2		mA
Output Voltage	V _{OUT}	$\begin{array}{l} V_{\rm IN}=18V\sim 36V\\ I_{\rm OUT}=0\sim 80 \text{mA} \end{array}$			100	V
Output Voltage Accuracy		$V_{IN} = 18V \sim 36V$		±2		%
Output Current Range	I _{OUTMAX}	$V_{IN} = 18V \sim 36V$	0		80	mA

1161 Ringwood Ct, #110, San Jose, CA 95131, U. S. A. Tel.: (408) 748-9100, Fax: (408) 770-9187

www.analogtechnologies.com

©Copyrights 2000-2021, Analog Technologies, Inc. All Rights Reserved. Updated on 12/7/2021 Email

8W Isolated DC-DC Power Module



ATMV24V100V80MA1

Parameter	Symbol	Test Conditions	Min.	Тур.	Max.	Unit/Note
Output Voltage Ripple	V _{OUT_RP}	Bandwidth = 20MHz		±1		%
Output Short-Circuit Protection Time	t _{sc}			≤60		S
Switching Frequency	f _{sw}	$V_{VPS} = 24V$ $I_{OUT} = 80mA$		125		kHz
Line Regulation	$\Delta V_{OUT} / \Delta V_{VPS}$	$V_{VPS} = 24V$ $I_{OUT} = 80mA$		±1		%
Load Regulation	ΔV _{ΟυΤ} /ΔΙ _{ΟυΤ}	$V_{VPS} = 24V$ Load change from 10% to 100%		±1		%
Isolation Voltage	V _{IS}			1500		VDC
Isolation Resistance		$V_{VPS} = 18V \sim 36V \\ V_{OUT} = 100V \\ V_{IS} = 1500VDC \\ I_{OUT} = 80mA \\ T_A = 25^{\circ}C \\ 70\%RH$		1000		MΩ
Isolation Capacitance				1		nF
Output Voltage Temperature Coefficient	TCV _{OUT} ⁽¹⁾	$V_{VPS} = 24V$ $I_{OUT} = 80mA$			0.03	%/°C
Cooling Method			Air Cooling			
Mean Time Between Failure	MTBF	MIL-HDBK-217F@25°C		1000		Kh
Operating Temperature Range	T _{opr}		-40		85	°C
Storage Temperature Range	T _{stg}		-40		105	°C
Maximum Soldering Temperature on Connection Pins	T _{sld}	Soldering Time:10s			300	°C
Case Temperature Rise	T _{cs}	$V_{VPS} = 24V$ $I_{OUT} = 80mA$		35		°C
Storage Relative Humidity Range	RH				95	%
Case Material			Aluminum			
External Dimensions			50.8×25.4×10.5 m		mm	
(Exclude Connection Pins)				2×1×0.41	-	inch
				25		g
Weight				0.055		lbs
				0.881		Oz

1161 Ringwood Ct, #110, San Jose, CA 95131, U. S. A. Tel.: (408) 748-9100, Fax: (408) 770-9187www.analogtechnologies.com©Copyrights 2000-2021, Analog Technologies, Inc. All Rights Reserved. Updated on 12/7/2021Email: staff@analogti.com/sales@analogti.com3



TYPICAL PERFORMANCE CHARACTERISTICS





Figure 5. Derating Curve

TYPICAL APPLICATIONS



F1	Input Time-delay Fuse				
F2 & F3	Output Time-delay Fuse, or Resettable Fuse (PTC)				
MOV	14D390K Input Voltage: 12VDC				
MOV	14D560K Input Voltage: 24VDC				
C1 9 C2	100µF/25V	V Input Voltage: 2VDC			
C1 & C2	47µF/50V	Input Voltage: 24VDC			
C3 & C4	$1.0\mu F \sim 10\mu F$ (High Frequency ESR)				
L1, L2 & L3	2.2µH ~ 10µH				

To further reduce the input and output ripple, the parameters of the LC filter can be appropriately increased, but it should be noted that the external capacitor at the output end should not be too large, and should be lower than the maximum capacitive load of the product.

OUTLINE DIMENSIONS




Figure 6. Outline Dimensions



Related Products

Product Model	Input	Voltage	Output Voltage	Output Current	Efficiency	MAX. Capacitive Load
	Тур.	Range	V	mA	%	μF
ATMV12V50V160MA1			50	160	78	100
ATMV12V100V80MA1		9 ~ 18	100	80	76	100
ATMV12V200V40MA1			200	40	75	68
ATMV12V300V20MA1	12		300	20	74	47
ATMV12V400V10MA1	12		400	10	73	33
ATMV12V500V8MA1			500	8	72	22
ATMV12V600V6.7MA1			600	6.7	70	10
ATMV12V700V4.3MA1			700	4.3	68	4.7
ATMV24V100V80MA1			100	80	78	100
ATMV24V200V40MA1		18 ~ 36	200	40	77	68
ATMV24V300V20MA1			300	20	75	47
ATMV24V400V10MA1	24		400	10	74	33
ATMV24V500V8MA1			500	8	73	22
ATMV24V600V6.7MA1			600	6.7	71	10
ATMV24V700V4.3MA1			700	4.3	70	4.7
ATMV12V50V80MA2		9 ~ 18	±50	±80	76	68
ATMV12V100V40MA2			±100	±40	75	68
ATMV12V150V20MA2	12		±150	±20	74	47
ATMV12V200V10MA2	12		±200	±10	73	33
ATMV12V250V8MA2			±250	±8.0	72	22
ATMV12V300V6.6MA2			±300	±6.6	70	10
ATMV24V50V80MA2		18 ~ 36	±50	±80	78	68
ATMV24V100V40MA2	24		±100	±40	77	68
ATMV24V150V20MA2			±150	±20	75	47
ATMV24V200V10MA2			±200	±10	74	33
ATMV24V250V8MA2			±250	±8.0	73	22
ATMV24V300V6.6MA2			±300	±6.6	71	10

1161 Ringwood Ct, #110, San Jose, CA 95131, U. S. A. Tel.: (408) 748-9100, Fax: (408) 770-9187 www.analogtechnologies.com

©Copyrights 2000-2021, Analog Technologies, Inc. All Rights Reserved. Updated on 12/7/2021 Email: staff@analogti.com/sales@analogti.com 6



ORDERING INFORMATION

Quantity	antity 1~9pcs 10~49pcs 50~99		50~99pcs	≥100pcs
ATMV24V100V80MA1	\$63	\$58	\$53	\$48

NOTICE

- 1. ATI warrants performance of its products for one year to the specifications applicable at the time of sale, except for those being damaged by excessive abuse. Products found not meeting the specifications within one year from the date of sale can be exchanged free of charge.
- 2. ATI reserves the right to make changes to its products or to discontinue any product or service without notice, and advise customers to obtain the latest version of relevant information to verify, before placing orders, that the information being relied on is current and complete.
- 3. All products are sold subject to the terms and conditions of sale supplied at the time of order acknowledgment, including those pertaining to warranty, patent infringement, and limitation of liability. Testing and other quality control techniques are utilized to the extent ATI deems necessary to support this warranty. Specific testing of all parameters of each device is not necessarily performed, except those mandated by government requirements.
- 4. Customers are responsible for their applications using ATI products. In order to minimize risks associated with the customers' applications, adequate design and operating safeguards must be provided by the customers to minimize inherent or procedural hazards. ATI assumes no liability for applications assistance or customer product design.
- 5. ATI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right of ATI covering or relating to any combination, machine, or process in which such products or services might be or are used. ATI's publication of information regarding any third party's products or services does not constitute ATI's approval, warranty or endorsement thereof.
- 6. IP (Intellectual Property) Ownership: ATI retains the ownership of full rights for special technologies and/or techniques embedded in its products, the designs for mechanics, optics, plus all modifications, improvements, and inventions made by ATI for its products and/or projects.