

Multilayer Ceramic Chip Capacitor

Part Number: 2220YA300223KJTS3X

2220 305Vac (X2) 50/60Hz / 1000Vdc 22nF ±10% X7R (2R1) **Description:**

IEC/EN60384-14:2013+A1 Approval


Specifications: UL60384-14, CAN/CSA E60384-14:14

TÜV R60153664 / ID1111233479 Certification:

UL/cUL E228790-20200928

IEC/EN 60384-14:2013+A1 Class X2 Classification:

UL/cUL FOWX2, FOWX8



Component Marking and Certification Bodies:





Material Group I: CTI >= 600

Mechanical Specification

Size Code 2220

Length (L1) in mm (") $5.7 \pm 0.40 \ (0.225 \pm 0.016)$ Width (W) in mm (") $5.0 \pm 0.40 (0.197 \pm 0.016)$

Thickness (T) in mm (") 2.54 Max (0.1 Max)

0.25 (0.010) Minimum Termination Band (L2,L3) in mm (") Maximum Termination Band (L2,L3) in mm (") 1.00 (0.040)

Minimum Band Gap (L4) in mm (") 4.0 (0.158)

FlexiCap™ Polymer termination, Nickel barrier, Sn Plated Solder **Termination Material**

(RoHS compliant) Solderability IEC-60068-2-58

7" Reel Horizontal Orientation, 500 per reel Packaging

General Electrical Specification

Rated Voltage

Class X2 (305Vac), 50/60Hz, 2.5kV impulse

Humidity Grade Not applicable Maximum DC Working Voltage 1000Vdc certified / (1500Vdc outside scope of any specification)

Nominal Capacitance Value 22nF

Capacitance Tolerance +10% ≤0.025 Tangent of Loss Angle (Tan δ)

Capacitance and Tan δ Test Conditions 1.0Vrms @ 1kHz

100% test: 3000Vdc 1s min / 5s max Voltage Proof

AQL test: 3225Vdc / 1505Vac 60s min / 2.5kV 1.2x50µs impulse (50mA max charging current for DC tests)

Min Insulation Resistance (IR)

45.45GOhm @ 100Vdc Dielectric Classification

X7R (2R1) -55°C / +125°C Rated Temperature Range

No DC Voltage ±15% Maximum Capacitance Change over Temperature Range Rated DC Voltage -

Climatic Category (IEC) 55/125/56 Ageing Characteristic <2% per decade

Knowles Precision Devices - Sales

Europe: KPD-Europe-sales@knowles.com Asia: KPD-Asia-sales@knowles.com

USA: KPD-NA-sales@knowles.com

www.knowlescapacitors.com

This datasheet is for a standard item and is confirmed valid on the date generated, the latest published data for this part may differ and is available at http://www.knowlescapacitors.com or by contacting us.

The information contained on this drawing is confidential and may not be copied in whole or part ir any form or disclosed to a third party without the consenof Knowles and any customer mentioned within this specification.

Data is correct to the best of our knowledge, errors and

Date: Thursday, September 02, 2021



Multilayer Ceramic Chip Capacitor

Part Number: 2220YA300223KJTS3X

Description: $^{2220~305\text{Vac}}_{\pm 10\%}$ X7R (2R1)

Environmental

RoHS Compliant to 2011/65/EC as amended by 2015/863/EU

Compliant

REACH Compliant

211 compliant

California Proposition 65

No exposure risk


Board Layout

Knowles' conventional 2-terminal chip capacitors generally be mounted using pad designs in accordance with international specification IPC-7351, Generic Requirements for Surface Mount Design and Land Pattern Standards, but there are some other factors that have been shown to reduce mechanical stress, such as reducing the pad width to less than the chip width. In addition, the position of the chip on the board should be considered.

Some high voltage parts may require modifications to the board layout and/or the addition of a conformal coating to prevent flashover. Refer to application note AN0043 for further information.

IPC-7351 pad design


	2220	
С	5.30mm	0.209"
Υ	1.50mm	0.059"
Х	5.40mm	0.213"



Packaging

Tape packaging information for tape-and-reel parts:

Tape and reel packing of surface mounting chip capacitors for automatic placement are in accordance with IEC60286-3.




Soldering

Reflow solder in accordance with IPC-A-610. Recommended reflow profile as laid down in IPC/JEDEC J-STD-020.

Wave soldering is also possible, but care must be taken for case sizes 1210 and larger and component thickness >1.0mm. Trials are encouraged.

Hand soldering is not recommended and can lead to component damage through thermal shock.

DLI



Application notes with mounting and handling guidance are available on request.

Johanson MFG

Knowles Precision Devices - Sales

Europe: KPD-Europe-sales@knowles.com

Compex

Asia: KPD-Asia-sales@knowles.com

USA: KPD-NA-sales@knowles.com

www.knowlescapacitors.com

Syfer

Voltronics

This datasheet is for a standard item and is confirmed valid on the date generated, the latest published data for this part may differ and is available at http://www.knowlescapacitors.com or by contacting us.

The information contained on this drawing is confidential and may not be copied in whole or part in any form or disclosed to a third party without the consenof Knowles and any customer mentioned within this specification.

Novacap

Data is correct to the best of our knowledge, errors and

omissions excepted.

Date: Thursday, September 02, 2021