

#### **Features**

- Small Surface Mounting Type
- Epoxy Meets UL 94 V-0 Flammability Rating
- Moisure Sensitivity Level 1
- Lead Free Finish/RoHS Compliant ("P" Suffix Designates RoHS Compliant. See Ordering Information)
- Halogen Free Available Upon Request By Adding Suffix "-HF"

# **Maximum Ratings**

- Operating Junction Temperature Range: 125°C
- Storage Temperature Range: -40°C to +125°C
- Thermal Resistance: 667°C/W Junction to Ambient


MCC Part Number	Device Marking	Maximum Recurrent Peak Reverse Voltage	Maximum DC Blocking Voltage
RB751S-40LP	5	40V	30V

### Electrical Characteristics @ 25°C Unless Otherwise Specified

Mean Rectifying Current	I <sub>O</sub>	30mA	
Peak Forward Surge Current	I <sub>FSM</sub>	150mA	
Forward Voltage	V <sub>F</sub>	0.37V(Max)	I <sub>F</sub> =1mA;
Reverse Current	I <sub>R</sub>	0.5μA(Max)	V <sub>R</sub> =30V


# 30 mA Schottky Rectifier 40 Volts

# SOD-882




DIMENSIONS							
DIM	INCHES		MM		NOTE		
DIIVI	MIN	MAX	MIN	MAX	NOTE		
Α	0.018	0.022	0.45	0.55			
В	0.000	0.003	0.01	0.07			
С	0.019 REF.		0.470 REF.				
D	0.037	0.041	0.95	1.05			
Е	0.022	0.026	0.55	0.65			
F	0.017	REF.	0.420	REF.			
G	0.011	0.015	0.27	0.37			
Н	0.001	REF.	0.030	REF.			
L	0.013	0.017	0.34	0.44			


#### Suggested Solder Pad Layout







## **Curve Characteristics**











## **Ordering Information**

Device	Packing	
Part Number-TP	Tape&Reel:10Kpcs/Reel	

Note: Adding "-HF" Suffix For Halogen Free, eg. Part Number-TP-HF

#### \*\*\*IMPORTANT NOTICE\*\*\*

**Micro Commercial Components Corp.** reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. **Micro Commercial Components Corp**. does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp**, and all the companies whose products are represented on our website, harmless against all damages.

#### \*\*\*LIFE SUPPORT\*\*\*

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

#### \*\*\*CUSTOMER AWARENESS\*\*\*

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.