
PRODUCT DATA DRAWING

REVISION HISTORY				
REV	DESCRIPTION	DATE	APPROVED	
01	PRELIMINARY	01/22		
02	PRELIMINARY	04/22	SEE PDM	



MATERIAL:

CONNECTORS: 2X 2.92mm MALE (SF1511-60069)

CABLE: FLEXIBLE Ø.047 CABLE (200-70-214)

SHRINK TUBING: M23053/5

PERFORMANCE:

IMPEDANCE: 50 OHMS FREQ. RANGE: DC TO 40 GHz.

MATERIAL:	SEE NOTES		
FINISH:	SEE NOTES		
SURFACE AR	^{EA:} N/A		
	PROPRIETARY		
IS THE SOLE P ANY REPRODU	FION CONTAINED IN THIS DRAW ROPERTY OF SV MICROWAVE, I ICTION IN PART OR AS A WHOLE WRITTEN PERMISSION OF		

DIMENSIONS ARE IN INCHES TOLERANCES:
FRACTIONAL: ±1/64 ANGULAR: X° ±1°0' X°X' +15'
DECIMAL: .X ±.030 .XX ±.010
.XXX ±.005
INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994

1) ALL DIMENSIONS ARE IN INCHES [MILLIMETERS]
2) ALL DIMENSIONS ARE AFTER PLATING.
3) BREAK CORNERS & EDGES. 1005 R. MAX.
4) CHAM. 1ST & LAST THREADS.
5) SURFACE ROUGHNESS 63-MIL-STD-10.
6) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC
WITHIN .005 T.I.R.
7) REMOVE ALL BURRS

UNLESS OTHERWISE SPECIFIED

PER ASME Y14.5M - 1994	7) REMOVE ALL BURRS	
THIRD ANGLE PROJECTION	DRAWN:	SRM 02/01/22
	CHECKED:	SEE PDM
\\ \tau_{1}	APPROVED:	SEE PDM



2.92mm MALE TO 2.92mm MALE Ø.047 CABLE ASSEMBLY

SIZE B	DWG. NO.	7015-1096	
SCALE: 6:1			SHEET 1 OF 1