EAO – Your Expert Partner for **Human Machine Interfaces**

84-5041.2B20 - Emergency-stop switch complete, foolproof EN IEC 60947-5-5

84-5041.2B20 - Emergency-stop switch complete, foolproof EN IEC 60947-5-5



Attention: The preview is based on a sample product. This can differ from your current configuration.

Mounting

Front

Front dimension Ø 32 mm Front shape round

Other Attributes

Weight 0.028 kg
Operating voltage 5 ... 30 V DC
Operation current 9.7 ... 12.4 mA

Operating-/Indication part

Lens material Plastic
Lens colour red
Lens profile Mushroom
Lens optics opaque

IP-Rating

Front protection IP 65

Connection Method

Terminal Plug 2.8 x 0.5 mm

Actuator

Switching action Maintained

Switching element

Switching voltage 250 V AC/DC

Switching current 5 A

Switching system Slow-make switching element

Contacts 2 NC Contact material Gold

Illumination

LED colour Single-LED red

Function


Emergency stop switch

e a o

EAO – Your Expert Partner for **Human Machine Interfaces**


84-5041.2B20 - Emergency-stop switch complete, foolproof EN IEC 60947-5-5

Dimensions




P = Plug-in terminal 2.8 x 0.5 mm


Mounting cut-outs



Wiring diagram



Component layout



Additional information

Twist to unlock clockwise

Position indication ring black

Application as per DIN EN ISO 13850 and EN 60204-1

Standard version: Flat ribbon-cable length 300 mm or plug-in

terminal 2.8 x 0.5 mm

Other options on request: Customisation of flat ribbon-cable and

connectors

Luminosity and wave length variations caused by LED

manufacturing processes may cause slight differences regarding the illumination

Legend

Contacts: NC = Normally closed, NO = Normally open