### **Features**

- 20W Dimmable AC-DC LED Power Supply
- 350mA, 500mA, 700mA or 1050mA Outputs ENEC, UL, RCM and CB Certified

### **LED DRIVER**

- Deep Dimming to 0% \* Active Power Factor Correction >0.95
- 3.75kVAC Isolation
- Output Connector to avoid miswiring
- 5 Year Warranty

•

### Description

,

The RACT20 series is a constant current dimmable AC/DC source for driving high power LED applications. The phase angle dimming function works with leading or trailing edge dimmers. This driver is suitable for indoor LED lighting systems and powers 5-15 high power LEDs or single LED arrays from 350mA up to 1A.

Se	lection	Guide	

Part Number	Input Voltage (VAC)	Output Current (mA)	Output Voltage (VDC)	Dimming Control	Efficiency typ. (%)	Max. # LEDs
RACT20-350	230	350	30-56	Triac	82	15 x 1W
RACT20-500	20	<b>5</b> 9 <b>=</b> (			82	D 2 x 1W
RACT20-700	230	700	15-28	Triac	81	8 x 2W, 8+8 x 1W
RACT20-1050	230	1050	Z-1 3	Triac	81	5 x 3W, 5+5 x 2W
RACT20-350-US	115	350	30-56	Triac	82	15 x 1W
RACT20-500-US	115	500	01-39		32	12 x 1W
RACT20-700-US	115	700	1.5-28	That	N <b>P</b> <sub>01</sub>	8 x 2W, 8+8 x 1W
RACT20-1050-US	115	1050	12-18	Triac	81	5 x 3W, 5+5 x 2W

<b>Decifications</b> (typical at 25°C, nomina	al input voltage, rated	output current unless otherwise	specified)
Input Voltage Range	RACT20-xxxx		180-264VAC
	RACT20-xxxx-US		90-135VAC
Rated Power			20W max
Output Current Accuracy			±5% max
Input Current	115VAC		0.4A max
	230VAC		0.2A max
Input Frequency Range			47-63H
Power Factor	Full Load		>0.95
THD	Full Load, 115VAC		8% max
	Full Load, 230VAC		11% max
Leakage Current			<0.75m/
Open Circuit Voltage	350mA		60VDC max
(No Load Vout)	500mA		44VDC max
	700mA		33VDC max
	1050mA		22VDC max
Output Ripple and Noise	350mA, 500mA		4.5Vp-p max
	700mA, 1050 mA		4.0Vp-p max
Short Circuit Protection		Hiccup mode,	Auto recover
Overtemperature Protection	ç	$95^{\circ}C \pm 10^{\circ}C$ (RT1) Hiccup mode,	Auto recover
Isolation Voltage		3.75kV	AC / 1 minut
Efficiency at Full Load		see s	election guid
Dimming	nming AC phase-cut dimming, work with leading/trailing edge dimmers		
Operating Temperature Range	Ambient Temperature	e -30	0°C to +50°(
(free air convection, according to CE/UL)	Case Temperature		85°C max
Operating Temperature Range	Ambient Temperature	e -3	0°C to +50°
(free air convection, according to ENEC)	Case Temperature		80°C max
		continued	l on next pag

LIGHTLINE AC/DC-Converter with 5 year Warranty

## RECOM

# 20W Triac Dimmable **LED** Driver




**UL-8750** certified UL-60950-1 certified **European Version only:** ENEC 61347 certified



\* only US-Versions

# **Derating-Graph**

(Ambient Temperature)



**Refer to Application Notes** 

www.recom-power.com

L-33

## **LIGHTLINE** DC/DC-Converter

# RACT20 Series

Specifications (typical at 25	°C, nominal input voltage, rated output current unless otherwise spec	cified)
Storage Temperature		-40°C to +85°C
Relative Humidity		95% RH
EMC	design refer to EN55022	Class B
IP Rating	IP Rating suitable for indoor LED lighting system	IP20
Design Lifetime	25°C ambient	>70 x 10 <sup>3</sup> hours in operation
Package Weight		145g
Packing Quantity		1 pc.
PCB Material		Plastic Resin with Fibreglass (UL94V-0)
Case Material		Plastic
Connections	AC Input	
		Screw Terminal
	LED Output	Screw Terminal
	LED Output	5.5mm Socket with 2mm Pin
		(suiteable matching plug Switchcraft S760 or simila
Standards	ENEC Lamp Controlgear	EN61347-2-13:2006
		EN61347-1:2008
	Electrical Lighting, EMC Emissions	EN55015:2006 + A2:2009
	Limits for Harmonics Emissions	EN 61000-3-2:2006 + A2:2009
	EMC Compatability: Flicker and Voltage Variations	EN 61000-3-3:2006
	Electrical Lighting: EMC Immunity	EN 61547:2009
	RCM (21377)	AS/NZS 61347.1:2002, IEC 61347-2-13
	FCC	FCC15B
Certifications	LED Lighting Safety (E340696)	UL8750
	Information Technology Equipment - Safety	UL60950-1
		CAN/CSA C22.2 No. 60950-1-07
	PSE	J61347-1(H20), J61347-2-13(H21), J55015(H20)

**RACT20** 


\*The triac dimmer must be capable of dimming down to zero

#### Note:


All LED Drivers may not be used without a load. They must be switched on the primary side only. Noncompliance may damage the LED or reduce its lifetime.

### Characteristics












# RACT20 Series

#### **Characteristics**

Condition	Circuit Breaker	Circuit Breaker Current				
	Тур	10A	16A	20A	25A	
115VAC, 10hm 90° phase angle	С	47	68	84	105	
230VAC, 10hm	В	36	57	69	85	
90° phase angle	С	57	87	109	134	
277VAC, 10hm	В	41	65	80	98	
90° phase angle	С	65	99	125	154	

### Maximum Number of LED drivers per circuit breakers

### Package Style and Pinning



RACT20

Pin

Shell

Tolerance XX = +/-1mmXX.X = \*/-0.5mm LED+

LED-