MATERIALS & SPECIFICATIONS

INSULATOR:

POLYPHENYLENE SULFIDE (PPS) PER MIL-M-24519, TYPE GST 40F.

CONTACT:

BERYLLIUM COPPER PER ASTM B194, C17200. GOLD PLATED PER ASTM B488, (HARD GOLD) TYPE II CODE C CLASS 1.27.

TERMINATION:

SOLDER COATED WITH SN63A PER J-STD-006 OR AMS-P-81728.

LATCH BOX:

BERYLLIUM COPPER PER ASTM B194 NICKEL PLATE PER SAE-AMS-2404.

CURRENT CAPACITY:

3 AMP MAX.

CONTACT RESISTANCE:

26 MILLIOHMS (65mV) MAX @ 2.5 AMPS.

PERFORMANCE:

PRODUCT FAMILY TESTED TO AND PASSED THE PERFORMANCE SPECIFICATIONS OF TABLE VII OF MIL-DTL-83513.

PART NO. A 2 4 0 0 1 - 0 1 2 REV ECO 102048


DATE 11-03-15


APP

TI M





ACTUAL SIZE





SUGGESTED PAD LAYOUT





NOTE:

DIMENSIONS IN [] ARE IN MILLIMETERS UNLESS OTHERWISE NOTED AND ARE FOR REFERENCE ONLY

	THIRD ANGLE⊕ ←	THIS DRAWING CONTA	INS CONFIDENTIAL AND	PROPRIETARY INFORMATION WHICH IS THE PROPERTY OF	ī	
PS	-TOLERANCES-	OMNETICS CONNECTOR CORP. THIS DOCUMENT MAY NOT, IN WHOLE OR IN PART, BE DUPLICATED, OR DISCLOSED FOR ANY PURPOSE. WITHOUT WRITTEN PERMISSION FROM OMNETICS CONNECTOR CORP.				
	UNLESS OTHERWISE NOTED		DATE	TITLE		
	DIMENSIONS IN INCHES	DETM DEL	00 00 00	TITLE:		

-	DFTM. DEL	09-26-02	11
	CHK'D.	DATE	
	APP'D.	DATE	

2 PL DEC± .01

3 PL DEC± .005

ANGLES ± 1°

4 PL DEC± .0005

(12) PIN MALE CONNECTOR W/LATCH

CTOR CORPORATION A 24001-012

7260 COMMERCE CIRCLE EAST MINNEAPOLIS. MN 55432 WWW.OMNETICS.COM

CAGE CODE 6 1 8 7 3 DWG NO.

SHEET 1 OF 1 REV SCALE: 3:1

Ε