

Diode EMCON 4 High Power Chip

FEATURES:

٠

•

1200V EMCON 4 technology •

small temperature coefficient

soft, fast switching • low reverse recovery charge

This chip is used for:

medium / high power modules •



Applications:

medium / high power drives •

Chip Type	V _R	I _F	Die Size	Package
IDC40D120T6H	1200V	75A	6.30 x 6.30 mm ²	sawn on foil

MECHANICAL PARAMETER:

Raster size	6.30 x 6.30				
Area total / active	39.69 / 29.98	mm ²			
Anode pad size	5.346 x 5.346]			
Thickness	120	μm			
Wafer size	150	mm			
Flat position	180	deg			
Max. possible chips per wafer	· 367 pcs				
Passivation frontside	Photoimide				
Pad metall	3200 nm AlSiCu				
Backside metall	Ni Ag –system suitable for epoxy and soft solder die bonding				
Die bond	electrically conductive glue or solder				
Wire bond	Al, ≤500µm				
Reject ink dot size	Ø 0.65mm; max 1.2mm				
Recommended storage environment	store in original container, in dry nitrogen, < 6 month at an ambient temperature of 23°C				



Maximum Ratings

Parameter	Symbol Condition		Value	Unit	
Repetitive peak reverse voltage	V _{RRM}		1200	V	
Continuous forward current limited by	I _F		1)		
T _{jmax}	7F			A	
Maximum repetitive forward current	I _{FRM}		150		
limited by T _{jmax}	1 F K M		100		
Maximum junction and storage temperature	T _{vj,max} , T _{stg}		-40+175	°C	
Reverse bias safe operating area ²⁾ (RBSOA)	$I_{\rm F,max}$ = 150A, $V_{\rm R,max}$ = 1200V, $T_{\rm vj,op} \le 150^{\circ}{\rm C}$, $P_{\rm max}$ = tbd kW				

¹⁾ depending on thermal properties of assembly

²⁾ not subject to production test - verified by design/characterisation

Parameter	Symbol	Condi	Value			Unit		
	Symbol Condition			min.	Тур.	max.	onic	
Reverse leakage current	I _R	V _R =1200V	<i>T_j</i> =25 ° <i>C</i>			14	μA	
Cathode-Anode breakdown Voltage	V _{Br}	I _R =0.25mA	<i>T_j</i> =25°C	1200			V	
Forward voltage drop	V _F	I _F =75A	<i>T_j</i> =25 ° <i>C</i>	1.55	1.9	2.25	V	

Static Electrical Characteristics (tested on wafer), Ti=25 °C


Dynamic Electrical Characteristics inductive load (not subject to production test - verified by design/characterization)

Parameter	Symbol	Conditions		Value ²⁾			Unit
Falameter	Symbol			min.	Тур.	max.	
Peak reverse recovery current	/ _{RM}	$I_{F}=A$ di/dt=A/ms $V_{R}=V$ $V_{GE}=-15V$	$T_j = 25 \ ^\circ C$ $T_j = 125 \ ^\circ C$ $T_j = 150 \ ^\circ C$		tbd		А
Reverse recovery charge	Q _r	$I_{F}=A$ di/dt=A/ms $V_{R}=V$ $V_{GE}=-15V$	$T_j = 25 \ ^{\circ}C$ $T_j = 125 \ ^{\circ}C$ $T_j = 150 \ ^{\circ}C$		tbd		μC
Reverse recovery energy	E _{rec}	$I_{F}=A$ di/dt=A/ms $V_{R}=V$ $V_{GE}=-15V$	$T_j = 25 \ ^{\circ}C$ $T_j = 125 \ ^{\circ}C$ $T_j = 150 \ ^{\circ}C$		tbd		mJ

²⁾ values also influenced by parasitic L- and C- in measurement and package.



CHIP DRAWING:





FURTHER ELECTRICAL CHARACTERISTICS:

This chip data sheet refers to the device data sheet

tbd

Description:

AQL 0,65 for visual inspection according to failure catalog

Electrostatic Discharge Sensitive Device according to MIL-STD 883

Test-Normen Villach/Prüffeld

Published by Infineon Technologies AG 81726 Munich, Germany © Infineon Technologies AG 2007 All Rights Reserved

Attention please!

The information herein is given to describe certain components and shall not be considered as warranted characteristics.

Terms of delivery and rights to technical change reserved.

We hereby disclaim any and all warranties, including but not limited to warranties of non-infringement, regarding circuits, descriptions and charts stated herein.

Infineon Technologies is an approved CECC manufacturer.

Information

For further information on technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies Office in Germany or our Infineon Technologies Representatives world-wide (see address list).

Warnings

Due to technical requirements components may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies Office.

Infineon Technologies components may only be used in life-support devices or systems with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system, or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body, or to support and / or maintain and sustain and / or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.